

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333405-940

Luminaire Tested: **S125DIW-S850D470U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333405-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S850D470U940-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4496.4 lumens
Efficiency: N/A
Efficacy: 119.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333405-940

CATALOG NUMBER: S125DIW-S850D470U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333405-940

CATALOG NUMBER: S125DIW-S850D470U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	68
1	102	97	93	90	96	92	88	85	82	79	77	72	70	69	64	62	61	57
2	93	85	78	73	87	80	75	70	72	67	63	64	60	57	56	54	51	48
3	84	75	67	61	79	71	64	58	63	58	53	56	52	48	50	47	44	40
4	77	66	58	52	73	63	55	50	56	50	45	50	45	41	45	41	38	35
5	71	59	51	44	67	56	48	43	50	44	39	45	40	36	40	36	33	30
6	66	53	45	39	62	50	43	37	45	39	34	41	36	32	36	32	29	26
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	26	23
8	56	44	36	30	53	42	34	29	38	31	27	34	29	25	31	26	23	21
9	53	40	32	27	50	38	31	26	35	29	24	31	26	23	28	24	21	19
10	49	37	29	24	46	35	28	24	32	26	22	29	24	20	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7559	7559	7559
5°	7577	7505	7553
10°	7531	7452	7494
15°	7449	7362	7393
20°	7332	7236	7249
25°	7207	7088	7081
30°	7052	6927	6893
35°	6885	6754	6659
40°	6715	6566	6473
45°	6530	6395	6268
50°	6327	6187	6002
55°	6132	5954	5788
60°	5898	5717	5515
65°	5619	5434	5251
70°	5351	5108	4932
75°	4876	4716	4551
80°	4340	4273	4169
85°	3772	3846	3631



TEST NUMBER: P333405-940

CATALOG NUMBER: S125DIW-S850D470U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.4	2.5
10°-20°	311.8	6.9
20°-30°	460.3	10.2
30°-40°	537.2	11.9
40°-50°	539.5	12.0
50°-60°	473.6	10.5
60°-70°	352.9	7.8
70°-80°	201.8	4.5
80°-90°	59.8	1.3
90°-100°	34.8	0.8
100°-110°	102.7	2.3
110°-120°	174.0	3.9
120°-130°	229.0	5.1
130°-140°	256.6	5.7
140°-150°	251.5	5.6
150°-160°	211.2	4.7
160°-170°	140.4	3.1
170°-180°	49.1	1.1
0°-30°	882.5	19.6
0°-40°	1419.6	31.6
0°-60°	2432.7	54.1
0°-90°	3047.2	67.8
90°-120°	311.5	6.9
90°-150°	1048.5	23.3
90°-180°	1449.0	32.2
0°-180°	4496.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1170	1170	1170	1170	1170	
5°	1169	1166	1158	1165	1165	111
15°	1114	1111	1101	1106	1106	314
25°	1011	1006	995	996	994	465
35°	873	869	857	852	845	546
45°	715	711	700	690	686	551
55°	545	541	529	521	514	486
65°	368	365	356	348	344	365
75°	195	193	189	186	182	208
85°	51	52	52	51	49	57
90°	0	4	6	8	10	4
95°	26	27	31	34	35	28
105°	92	94	97	99	100	98
115°	174	176	177	176	176	172
125°	254	257	257	256	256	228
135°	331	333	333	333	332	255
145°	401	402	403	403	402	250
155°	458	458	459	460	458	211
165°	498	498	498	499	497	141
175°	518	517	516	519	516	49
180°	519	519	519	519	519	



TEST NUMBER: P333405-940

CATALOG NUMBER: S125DIW-S850D470U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5
2.5°	1173.6	1173.0	1172.6	1172.1	1171.5	1170.5	1168.9	1167.2	1165.6	1164.0	1165.6
5°	1168.8	1168.3	1167.9	1167.5	1167.1	1165.8	1163.8	1161.7	1159.7	1157.6	1159.5
7.5°	1158.0	1157.6	1157.2	1156.7	1156.4	1155.0	1152.7	1150.5	1148.3	1145.9	1147.7
10°	1148.3	1148.0	1147.5	1147.1	1146.7	1145.4	1143.1	1140.9	1138.6	1136.3	1138.0
12.5°	1136.5	1135.8	1135.1	1134.3	1133.5	1132.1	1130.1	1127.9	1125.8	1123.7	1125.1
15°	1114.1	1113.5	1112.9	1112.2	1111.6	1110.2	1108.0	1105.6	1103.4	1101.1	1102.2
17.5°	1088.3	1087.4	1086.5	1085.7	1084.8	1083.1	1080.8	1078.4	1076.0	1073.7	1075.0
20°	1066.8	1066.5	1066.0	1065.6	1065.2	1063.6	1061.0	1058.3	1055.6	1052.9	1054.4
22.5°	1045.4	1044.6	1043.9	1043.1	1042.4	1040.8	1038.3	1035.7	1033.2	1030.7	1031.7
25°	1011.3	1010.3	1009.2	1008.2	1007.2	1005.3	1002.6	1000.0	997.3	994.6	995.1
27.5°	971.4	970.9	970.3	969.6	969.0	967.3	964.6	961.8	959.0	956.3	956.4
30°	945.6	944.9	944.3	943.7	943.1	941.2	938.2	935.0	931.9	928.9	928.4
32.5°	917.4	916.4	915.5	914.5	913.6	911.8	909.0	906.2	903.5	900.7	900.0
35°	873.3	872.4	871.6	870.8	870.0	868.2	865.3	862.4	859.5	856.7	855.6
37.5°	827.6	826.5	825.5	824.5	823.4	821.5	818.9	816.1	813.4	810.7	809.1
40°	796.5	795.4	794.4	793.4	792.3	790.4	787.5	784.6	781.8	778.8	777.0
42.5°	763.1	762.2	761.3	760.5	759.6	757.8	754.9	752.0	749.1	746.3	744.6
45°	715.0	714.1	713.3	712.5	711.7	710.0	707.6	705.1	702.6	700.2	697.7
47.5°	663.1	663.2	663.2	663.2	663.3	661.8	658.8	655.9	652.9	650.0	647.4
50°	629.7	629.1	628.5	627.9	627.3	625.7	623.3	620.8	618.3	615.8	613.1
52.5°	595.7	595.2	594.8	594.3	593.9	592.3	589.7	587.0	584.4	581.8	579.4
55°	544.6	543.9	543.3	542.7	542.1	540.3	537.4	534.6	531.6	528.8	526.9
57.5°	490.6	490.4	490.0	489.6	489.4	487.9	485.5	483.1	480.6	478.2	475.8
60°	456.6	455.8	455.0	454.1	453.3	451.7	449.4	447.2	445.0	442.6	440.6
62.5°	421.0	420.4	419.7	419.0	418.4	417.1	415.2	413.2	411.3	409.3	407.2
65°	367.7	367.2	366.8	366.4	366.0	364.7	362.4	360.2	357.8	355.6	353.7
67.5°	316.0	315.1	314.2	313.3	312.5	311.2	309.6	307.9	306.2	304.5	302.9
70°	283.4	282.3	281.3	280.3	279.3	277.9	276.0	274.1	272.2	270.5	269.2
72.5°	247.8	247.1	246.4	245.8	245.0	244.1	242.9	241.7	240.5	239.3	237.9
75°	195.4	195.0	194.6	194.2	193.8	193.1	192.0	191.0	189.9	189.0	188.3
77.5°	147.0	146.9	146.8	146.6	146.4	146.1	145.4	144.9	144.3	143.7	143.4
80°	116.7	116.7	116.7	116.7	116.7	116.5	116.1	115.7	115.2	114.9	114.7
82.5°	90.0	89.7	89.3	89.0	88.7	88.5	88.4	88.4	88.3	88.2	87.8
85°	50.9	51.2	51.4	51.5	51.7	51.9	51.9	51.9	51.9	51.9	51.6
87.5°	20.1	20.2	20.3	20.5	20.7	20.7	20.7	20.6	20.6	20.6	20.7
90°	0.4	1.2	1.9	2.6	3.3	3.9	4.5	5.2	5.8	6.5	7.0
92.5°	9.8	10.3	10.8	11.3	11.8	12.4	13.2	14.0	14.7	15.5	16.1
95°	26.3	26.5	26.7	26.8	27.0	27.6	28.4	29.3	30.2	31.1	31.7
97.5°	43.6	43.7	43.8	43.9	44.0	44.6	45.8	47.1	48.3	49.6	50.1
100°	56.6	56.6	56.6	56.6	56.6	57.2	58.3	59.5	60.6	61.8	62.7
102.5°	70.4	70.8	71.2	71.6	72.0	72.4	73.0	73.6	74.2	74.7	75.6
105°	92.1	92.6	93.0	93.5	94.0	94.4	95.0	95.5	96.0	96.6	97.1
107.5°	116.1	116.5	117.0	117.4	117.9	118.3	118.7	119.1	119.6	119.9	120.2
110°	132.6	133.0	133.5	133.9	134.4	134.7	135.0	135.3	135.5	135.8	136.1



TEST NUMBER: P333405-940

CATALOG NUMBER: S125DIW-S850D470U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	149.4	149.6	149.8	150.1	150.3	150.6	151.0	151.3	151.6	151.9	152.1
115°	174.2	174.5	175.0	175.3	175.7	175.9	176.1	176.3	176.5	176.6	176.6
117.5°	199.1	199.2	199.4	199.6	199.7	199.9	200.1	200.2	200.4	200.5	200.6
120°	214.6	215.1	215.5	216.0	216.4	216.7	216.8	216.9	217.0	217.0	217.0
122.5°	231.4	231.6	231.8	231.9	232.0	232.3	232.5	232.7	233.0	233.2	233.1
125°	254.2	254.8	255.3	255.8	256.4	256.7	256.8	256.9	257.0	257.1	256.9
127.5°	278.5	278.7	279.1	279.4	279.7	279.9	280.0	280.1	280.2	280.4	280.3
130°	293.0	293.5	293.9	294.4	294.8	295.2	295.3	295.5	295.7	295.9	295.8
132.5°	307.6	308.3	309.1	309.8	310.5	310.9	310.9	310.8	310.8	310.7	310.6
135°	330.6	331.2	331.7	332.3	332.8	333.1	333.1	333.2	333.3	333.4	333.4
137.5°	352.2	352.8	353.3	353.8	354.4	354.7	354.9	355.1	355.3	355.5	355.6
140°	366.1	366.6	367.0	367.5	367.9	368.4	368.6	368.9	369.2	369.4	369.6
142.5°	380.0	380.4	380.8	381.2	381.6	381.9	382.3	382.6	383.0	383.3	383.4
145°	400.6	400.9	401.3	401.6	402.0	402.3	402.5	402.8	403.1	403.3	403.3
147.5°	419.5	419.6	419.8	420.0	420.3	420.4	420.6	420.9	421.1	421.3	421.5
150°	432.0	431.9	431.9	431.8	431.7	431.9	432.2	432.6	432.9	433.3	433.3
152.5°	442.4	442.6	442.6	442.7	442.9	443.0	443.2	443.4	443.4	443.6	443.8
155°	458.3	458.3	458.3	458.3	458.3	458.3	458.4	458.5	458.6	458.7	459.1
157.5°	472.5	472.3	472.2	472.0	471.7	471.7	471.8	471.9	472.0	472.1	472.4
160°	481.0	480.7	480.4	480.1	479.8	479.7	479.8	479.9	480.0	480.1	480.5
162.5°	488.4	488.2	488.0	487.8	487.6	487.5	487.5	487.5	487.6	487.6	488.0
165°	498.3	498.1	497.9	497.8	497.6	497.6	497.7	497.8	497.8	497.9	498.3
167.5°	506.8	506.4	506.0	505.7	505.3	505.2	505.2	505.2	505.2	505.2	505.7
170°	511.2	510.9	510.5	510.1	509.8	509.6	509.6	509.6	509.6	509.6	510.1
172.5°	514.5	514.2	513.8	513.4	513.1	512.9	512.9	512.9	512.9	512.9	513.4
175°	518.2	517.7	517.4	517.0	516.7	516.5	516.5	516.5	516.5	516.5	517.0
177.5°	520.0	519.7	519.4	519.2	518.8	518.6	518.6	518.5	518.4	518.4	518.8
180°	519.3	519.3	519.3	519.3	519.3	519.3	519.3	519.3	519.3	519.3	519.3



TEST NUMBER: P333405-940

CATALOG NUMBER: S125DIW-S850D470U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5
2.5°	1167.2	1168.9	1170.5	1171.3	1171.1	1170.9	1170.7	1170.5
5°	1161.4	1163.1	1165.0	1165.8	1165.6	1165.5	1165.2	1165.0
7.5°	1149.6	1151.4	1153.2	1154.0	1153.8	1153.6	1153.3	1153.2
10°	1139.6	1141.3	1142.9	1143.6	1143.4	1143.2	1143.0	1142.8
12.5°	1126.3	1127.7	1129.0	1129.6	1129.6	1129.5	1129.5	1129.4
15°	1103.2	1104.2	1105.3	1105.7	1105.7	1105.7	1105.7	1105.7
17.5°	1076.3	1077.5	1078.8	1079.0	1077.9	1076.9	1075.8	1074.9
20°	1055.9	1057.3	1058.7	1058.9	1057.9	1056.9	1055.9	1054.8
22.5°	1032.6	1033.6	1034.6	1034.7	1033.9	1033.2	1032.5	1031.9
25°	995.4	995.9	996.3	996.1	995.6	995.0	994.3	993.7
27.5°	956.4	956.5	956.6	956.4	955.7	955.1	954.5	953.9
30°	928.1	927.6	927.2	926.8	926.1	925.5	924.9	924.3
32.5°	899.2	898.5	897.8	896.8	895.7	894.6	893.5	892.4
35°	854.6	853.5	852.6	851.2	849.5	847.9	846.2	844.6
37.5°	807.6	806.1	804.6	803.3	802.5	801.5	800.6	799.6
40°	775.2	773.3	771.4	770.2	769.5	769.0	768.4	767.8
42.5°	742.9	741.2	739.5	738.2	737.3	736.3	735.3	734.4
45°	695.2	692.7	690.3	688.7	688.1	687.5	686.9	686.3
47.5°	644.9	642.4	639.9	637.9	636.5	635.1	633.6	632.1
50°	610.5	607.8	605.1	603.1	601.6	600.2	598.8	597.4
52.5°	577.1	574.7	572.4	570.4	568.8	567.2	565.6	564.0
55°	525.1	523.3	521.4	519.8	518.3	516.8	515.4	514.0
57.5°	473.5	471.1	468.7	467.1	466.3	465.6	464.8	464.0
60°	438.5	436.5	434.4	432.7	431.2	429.8	428.4	427.0
62.5°	404.9	402.7	400.5	398.8	397.7	396.5	395.5	394.3
65°	352.0	350.1	348.2	346.9	346.1	345.3	344.4	343.6
67.5°	301.4	299.8	298.3	297.2	296.8	296.2	295.7	295.2
70°	268.0	266.7	265.5	264.5	263.6	262.8	262.0	261.2
72.5°	236.5	235.1	233.7	232.6	231.8	231.0	230.2	229.3
75°	187.7	187.1	186.5	185.7	184.9	184.0	183.2	182.4
77.5°	143.0	142.6	142.2	141.8	141.2	140.6	140.1	139.5
80°	114.4	114.2	114.0	113.7	113.3	112.9	112.4	112.1
82.5°	87.4	87.0	86.7	86.5	86.4	86.3	86.2	86.1
85°	51.5	51.3	51.0	50.7	50.3	49.9	49.5	49.0
87.5°	20.8	20.9	21.0	20.9	20.5	20.2	20.0	19.7
90°	7.4	7.8	8.3	8.6	8.9	9.2	9.5	9.7
92.5°	16.7	17.3	17.9	18.3	18.5	18.6	18.9	19.1
95°	32.4	33.0	33.6	34.1	34.2	34.4	34.6	34.8
97.5°	50.7	51.4	51.9	52.3	52.3	52.5	52.6	52.7
100°	63.5	64.3	65.1	65.5	65.7	65.9	66.1	66.3
102.5°	76.5	77.4	78.3	78.8	79.1	79.4	79.6	79.9
105°	97.6	98.2	98.7	99.2	99.4	99.7	100.0	100.2
107.5°	120.5	120.7	121.0	121.2	121.2	121.1	121.1	121.1
110°	136.3	136.6	136.9	137.0	136.9	136.8	136.7	136.6



TEST NUMBER: P333405-940

CATALOG NUMBER: S125DIW-S850D470U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	152.2	152.3	152.5	152.5	152.3	152.1	151.9	151.8
115°	176.5	176.4	176.3	176.2	176.1	176.0	175.9	175.8
117.5°	200.7	200.7	200.8	200.7	200.4	200.0	199.6	199.2
120°	217.0	217.0	217.0	216.9	216.5	216.2	215.8	215.4
122.5°	233.1	233.0	232.9	232.7	232.5	232.2	231.8	231.6
125°	256.7	256.5	256.4	256.2	256.1	256.0	255.9	255.8
127.5°	280.2	280.1	280.0	279.8	279.6	279.5	279.3	279.1
130°	295.7	295.6	295.5	295.3	295.2	295.0	294.8	294.6
132.5°	310.5	310.4	310.3	310.2	310.0	309.7	309.4	309.2
135°	333.4	333.4	333.4	333.2	332.9	332.5	332.2	331.8
137.5°	355.7	355.8	356.0	355.8	355.3	354.9	354.4	353.9
140°	369.8	370.0	370.1	370.0	369.5	369.1	368.6	368.2
142.5°	383.5	383.6	383.7	383.5	383.1	382.6	382.2	381.7
145°	403.3	403.3	403.3	403.2	403.0	402.7	402.4	402.2
147.5°	421.7	422.0	422.1	422.0	421.3	420.7	420.1	419.5
150°	433.3	433.3	433.3	433.2	433.0	432.8	432.7	432.5
152.5°	444.1	444.3	444.4	444.4	444.1	443.8	443.4	443.1
155°	459.4	459.8	460.1	460.1	459.7	459.2	458.8	458.3
157.5°	472.8	473.1	473.5	473.4	472.8	472.2	471.6	471.0
160°	480.9	481.3	481.6	481.5	481.1	480.6	480.2	479.7
162.5°	488.5	488.8	489.3	489.3	488.7	488.2	487.7	487.1
165°	498.6	499.0	499.4	499.3	498.7	498.2	497.7	497.1
167.5°	506.2	506.8	507.3	507.3	506.7	506.1	505.6	505.1
170°	510.7	511.2	511.8	511.8	511.1	510.5	509.9	509.3
172.5°	514.0	514.5	515.1	515.1	514.4	513.9	513.4	512.8
175°	517.5	518.2	518.7	518.6	518.0	517.4	516.7	516.1
177.5°	519.2	519.7	520.1	520.0	519.6	519.1	518.5	518.1
180°	519.3	519.3	519.3	519.3	519.3	519.3	519.3	519.3

(END OF REPORT)