

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333411-940

Luminaire Tested: **S125DIW-S850D770U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333411-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S850D770U940-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5421.5 lumens  
Efficiency: N/A  
Efficacy: 120.5 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333411-940

CATALOG NUMBER: S125DIW-S850D770U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333411-940

CATALOG NUMBER: S125DIW-S850D770U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56
1	99	95	91	87	92	88	85	82	76	73	71	65	63	61	55	53	52	47
2	90	83	76	71	84	77	72	67	67	62	59	57	54	51	48	46	44	39
3	82	73	65	59	76	68	61	56	59	54	49	50	46	43	42	40	37	33
4	75	64	56	50	70	60	53	47	52	47	42	45	41	37	38	35	32	29
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	31	28	25
6	64	51	43	37	59	48	41	35	42	36	32	36	32	28	31	27	25	22
7	59	46	38	33	55	44	36	31	38	32	28	33	28	25	28	25	22	19
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	16
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7559	7559	7559
5°	7577	7505	7553
10°	7531	7452	7494
15°	7449	7362	7393
20°	7332	7236	7249
25°	7207	7088	7081
30°	7052	6927	6893
35°	6885	6754	6659
40°	6715	6566	6473
45°	6530	6395	6268
50°	6327	6187	6002
55°	6132	5954	5788
60°	5898	5717	5515
65°	5619	5434	5251
70°	5351	5108	4932
75°	4876	4716	4551
80°	4340	4273	4169
85°	3772	3846	3631



TEST NUMBER: P333411-940

CATALOG NUMBER: S125DIW-S850D770U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	110.4	2.0
10°-20°	311.8	5.8
20°-30°	460.3	8.5
30°-40°	537.2	9.9
40°-50°	539.5	10.0
50°-60°	473.6	8.7
60°-70°	352.9	6.5
70°-80°	201.8	3.7
80°-90°	60.6	1.1
90°-100°	57.0	1.1
100°-110°	168.2	3.1
110°-120°	285.0	5.3
120°-130°	375.0	6.9
130°-140°	420.2	7.8
140°-150°	411.8	7.6
150°-160°	345.9	6.4
160°-170°	229.9	4.2
170°-180°	80.5	1.5
0°-30°	882.5	16.3
0°-40°	1419.6	26.2
0°-60°	2432.7	44.9
0°-90°	3047.9	56.2
90°-120°	510.2	9.4
90°-150°	1717.2	31.7
90°-180°	2374.0	43.8
0°-180°	5421.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1170	1170	1170	1170	1170	
5°	1169	1166	1158	1165	1165	111
15°	1114	1111	1101	1106	1106	314
25°	1011	1006	995	996	994	465
35°	873	869	857	852	845	546
45°	715	711	700	690	686	551
55°	545	541	529	521	514	486
65°	368	365	356	348	344	365
75°	195	193	189	186	182	208
85°	51	52	52	51	49	57
90°	1	6	11	14	16	5
95°	43	45	51	55	57	46
105°	151	154	158	162	164	161
115°	285	288	289	289	288	282
125°	416	420	421	420	419	373
135°	541	545	546	546	544	417
145°	656	659	661	661	659	410
155°	751	751	751	754	751	346
165°	816	815	816	818	814	230
175°	849	846	846	849	845	81
180°	851	851	851	851	851	



TEST NUMBER: P333411-940

CATALOG NUMBER: S125DIW-S850D770U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5
2.5°	1173.6	1173.0	1172.6	1172.1	1171.5	1170.5	1168.9	1167.2	1165.6	1164.0	1165.6
5°	1168.8	1168.3	1167.9	1167.5	1167.1	1165.8	1163.8	1161.7	1159.7	1157.6	1159.5
7.5°	1158.0	1157.6	1157.2	1156.7	1156.4	1155.0	1152.7	1150.5	1148.3	1145.9	1147.7
10°	1148.3	1148.0	1147.5	1147.1	1146.7	1145.4	1143.1	1140.9	1138.6	1136.3	1138.0
12.5°	1136.5	1135.8	1135.1	1134.3	1133.5	1132.1	1130.1	1127.9	1125.8	1123.7	1125.1
15°	1114.1	1113.5	1112.9	1112.2	1111.6	1110.2	1108.0	1105.6	1103.4	1101.1	1102.2
17.5°	1088.3	1087.4	1086.5	1085.7	1084.8	1083.1	1080.8	1078.4	1076.0	1073.7	1075.0
20°	1066.8	1066.5	1066.0	1065.6	1065.2	1063.6	1061.0	1058.3	1055.6	1052.9	1054.4
22.5°	1045.4	1044.6	1043.9	1043.1	1042.4	1040.8	1038.3	1035.7	1033.2	1030.7	1031.7
25°	1011.3	1010.3	1009.2	1008.2	1007.2	1005.3	1002.6	1000.0	997.3	994.6	995.1
27.5°	971.4	970.9	970.3	969.6	969.0	967.3	964.6	961.8	959.0	956.3	956.4
30°	945.6	944.9	944.3	943.7	943.1	941.2	938.2	935.0	931.9	928.9	928.4
32.5°	917.4	916.4	915.5	914.5	913.6	911.8	909.0	906.2	903.5	900.7	900.0
35°	873.3	872.4	871.6	870.8	870.0	868.2	865.3	862.4	859.5	856.7	855.6
37.5°	827.6	826.5	825.5	824.5	823.4	821.5	818.9	816.1	813.4	810.7	809.1
40°	796.5	795.4	794.4	793.4	792.3	790.4	787.5	784.6	781.8	778.8	777.0
42.5°	763.1	762.2	761.3	760.5	759.6	757.8	754.9	752.0	749.1	746.3	744.6
45°	715.0	714.1	713.3	712.5	711.7	710.0	707.6	705.1	702.6	700.2	697.7
47.5°	663.1	663.2	663.2	663.2	663.3	661.8	658.8	655.9	652.9	650.0	647.4
50°	629.7	629.1	628.5	627.9	627.3	625.7	623.3	620.8	618.3	615.8	613.1
52.5°	595.7	595.2	594.8	594.3	593.9	592.3	589.7	587.0	584.4	581.8	579.4
55°	544.6	543.9	543.3	542.7	542.1	540.3	537.4	534.6	531.6	528.8	526.9
57.5°	490.6	490.4	490.0	489.6	489.4	487.9	485.5	483.1	480.6	478.2	475.8
60°	456.6	455.8	455.0	454.1	453.3	451.7	449.4	447.2	445.0	442.6	440.6
62.5°	421.0	420.4	419.7	419.0	418.4	417.1	415.2	413.2	411.3	409.3	407.2
65°	367.7	367.2	366.8	366.4	366.0	364.7	362.4	360.2	357.8	355.6	353.7
67.5°	316.0	315.1	314.2	313.3	312.5	311.2	309.6	307.9	306.2	304.5	302.9
70°	283.4	282.3	281.3	280.3	279.3	277.9	276.0	274.1	272.2	270.5	269.2
72.5°	247.8	247.1	246.4	245.8	245.0	244.1	242.9	241.7	240.5	239.3	237.9
75°	195.4	195.0	194.6	194.2	193.8	193.1	192.0	191.0	189.9	189.0	188.3
77.5°	147.0	146.9	146.8	146.6	146.4	146.1	145.4	144.9	144.3	143.7	143.4
80°	116.7	116.7	116.7	116.7	116.7	116.5	116.1	115.7	115.2	114.9	114.7
82.5°	90.0	89.7	89.3	89.0	88.7	88.5	88.4	88.4	88.3	88.2	87.8
85°	50.9	51.2	51.4	51.5	51.7	51.9	51.9	51.9	51.9	51.9	51.6
87.5°	20.2	20.3	20.6	20.9	21.0	21.2	21.2	21.3	21.3	21.4	21.5
90°	0.6	1.9	3.0	4.2	5.4	6.5	7.5	8.6	9.5	10.6	11.3
92.5°	16.1	16.9	17.7	18.5	19.4	20.3	21.7	22.9	24.2	25.4	26.4
95°	43.1	43.3	43.6	43.9	44.2	45.1	46.5	48.1	49.5	51.0	52.0
97.5°	71.5	71.6	71.7	71.9	72.0	73.0	75.1	77.1	79.1	81.1	82.1
100°	92.6	92.6	92.6	92.6	92.6	93.6	95.5	97.5	99.3	101.3	102.6
102.5°	115.5	116.0	116.6	117.2	117.8	118.6	119.6	120.6	121.5	122.4	123.9
105°	151.0	151.7	152.4	153.1	153.9	154.7	155.6	156.4	157.3	158.2	159.1
107.5°	190.1	190.8	191.6	192.3	193.1	193.8	194.5	195.1	195.8	196.4	196.9
110°	217.1	217.8	218.6	219.4	220.1	220.6	221.1	221.5	221.9	222.4	222.8



TEST NUMBER: P333411-940

CATALOG NUMBER: S125DIW-S850D770U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	244.7	245.0	245.4	245.8	246.2	246.6	247.2	247.8	248.3	248.9	249.1
115°	285.3	285.9	286.5	287.0	287.7	288.1	288.4	288.6	289.0	289.3	289.1
117.5°	326.1	326.4	326.6	326.9	327.2	327.4	327.7	328.0	328.2	328.5	328.6
120°	351.5	352.2	352.9	353.7	354.5	354.9	355.0	355.2	355.3	355.4	355.4
122.5°	379.1	379.3	379.6	379.9	380.1	380.4	380.8	381.2	381.6	381.9	381.8
125°	416.3	417.2	418.1	419.0	419.9	420.4	420.5	420.7	420.9	421.0	420.7
127.5°	456.1	456.6	457.1	457.6	458.1	458.4	458.6	458.8	459.0	459.1	459.0
130°	479.9	480.6	481.4	482.1	482.9	483.4	483.7	483.9	484.3	484.6	484.4
132.5°	503.7	505.0	506.1	507.4	508.5	509.2	509.1	509.0	509.0	508.9	508.8
135°	541.4	542.3	543.2	544.1	545.0	545.5	545.6	545.8	546.0	546.1	546.1
137.5°	576.9	577.8	578.6	579.5	580.4	580.9	581.3	581.6	581.9	582.3	582.5
140°	599.8	600.5	601.2	601.9	602.7	603.2	603.7	604.1	604.6	605.0	605.3
142.5°	622.5	623.1	623.8	624.4	625.0	625.5	626.2	626.7	627.2	627.8	627.9
145°	656.0	656.6	657.2	657.7	658.4	658.9	659.3	659.8	660.2	660.7	660.7
147.5°	687.0	687.3	687.6	688.0	688.3	688.6	688.9	689.3	689.6	690.0	690.4
150°	707.7	707.5	707.3	707.2	707.0	707.3	707.8	708.5	709.0	709.6	709.6
152.5°	724.6	724.8	725.0	725.2	725.4	725.6	725.9	726.1	726.3	726.6	726.9
155°	750.6	750.6	750.6	750.6	750.6	750.7	750.9	751.0	751.2	751.4	751.9
157.5°	774.0	773.6	773.3	773.0	772.7	772.6	772.8	772.8	773.0	773.2	773.7
160°	787.7	787.3	786.8	786.4	786.0	785.8	786.0	786.1	786.2	786.4	787.0
162.5°	800.0	799.6	799.2	799.0	798.6	798.4	798.5	798.5	798.5	798.6	799.3
165°	816.2	815.9	815.6	815.3	815.0	814.9	815.1	815.2	815.4	815.6	816.1
167.5°	830.0	829.4	828.8	828.2	827.6	827.3	827.3	827.3	827.3	827.3	828.2
170°	837.4	836.8	836.2	835.6	835.0	834.7	834.7	834.7	834.7	834.7	835.6
172.5°	842.7	842.0	841.5	840.9	840.3	840.0	840.0	840.0	840.0	840.0	840.9
175°	848.6	848.0	847.5	846.9	846.2	846.0	846.0	846.0	846.0	846.0	846.9
177.5°	851.7	851.2	850.7	850.2	849.8	849.5	849.4	849.3	849.2	849.0	849.7
180°	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6



TEST NUMBER: P333411-940

CATALOG NUMBER: S125DIW-S850D770U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5	1170.5
2.5°	1167.2	1168.9	1170.5	1171.3	1171.1	1170.9	1170.7	1170.5
5°	1161.4	1163.1	1165.0	1165.8	1165.6	1165.5	1165.2	1165.0
7.5°	1149.6	1151.4	1153.2	1154.0	1153.8	1153.6	1153.3	1153.2
10°	1139.6	1141.3	1142.9	1143.6	1143.4	1143.2	1143.0	1142.8
12.5°	1126.3	1127.7	1129.0	1129.6	1129.6	1129.5	1129.5	1129.4
15°	1103.2	1104.2	1105.3	1105.7	1105.7	1105.7	1105.7	1105.7
17.5°	1076.3	1077.5	1078.8	1079.0	1077.9	1076.9	1075.8	1074.9
20°	1055.9	1057.3	1058.7	1058.9	1057.9	1056.9	1055.9	1054.8
22.5°	1032.6	1033.6	1034.6	1034.7	1033.9	1033.2	1032.5	1031.9
25°	995.4	995.9	996.3	996.1	995.6	995.0	994.3	993.7
27.5°	956.4	956.5	956.6	956.4	955.7	955.1	954.5	953.9
30°	928.1	927.6	927.2	926.8	926.1	925.5	924.9	924.3
32.5°	899.2	898.5	897.8	896.8	895.7	894.6	893.5	892.4
35°	854.6	853.5	852.6	851.2	849.5	847.9	846.2	844.6
37.5°	807.6	806.1	804.6	803.3	802.5	801.5	800.6	799.6
40°	775.2	773.3	771.4	770.2	769.5	769.0	768.4	767.8
42.5°	742.9	741.2	739.5	738.2	737.3	736.3	735.3	734.4
45°	695.2	692.7	690.3	688.7	688.1	687.5	686.9	686.3
47.5°	644.9	642.4	639.9	637.9	636.5	635.1	633.6	632.1
50°	610.5	607.8	605.1	603.1	601.6	600.2	598.8	597.4
52.5°	577.1	574.7	572.4	570.4	568.8	567.2	565.6	564.0
55°	525.1	523.3	521.4	519.8	518.3	516.8	515.4	514.0
57.5°	473.5	471.1	468.7	467.1	466.3	465.6	464.8	464.0
60°	438.5	436.5	434.4	432.7	431.2	429.8	428.4	427.0
62.5°	404.9	402.7	400.5	398.8	397.7	396.5	395.5	394.3
65°	352.0	350.1	348.2	346.9	346.1	345.3	344.4	343.6
67.5°	301.4	299.8	298.3	297.2	296.8	296.2	295.7	295.2
70°	268.0	266.7	265.5	264.5	263.6	262.8	262.0	261.2
72.5°	236.5	235.1	233.7	232.6	231.8	231.0	230.2	229.3
75°	187.7	187.1	186.5	185.7	184.9	184.0	183.2	182.4
77.5°	143.0	142.6	142.2	141.8	141.2	140.6	140.1	139.5
80°	114.4	114.2	114.0	113.7	113.3	112.9	112.4	112.1
82.5°	87.4	87.0	86.7	86.5	86.4	86.3	86.2	86.1
85°	51.5	51.3	51.0	50.7	50.3	49.9	49.5	49.0
87.5°	21.7	21.8	21.9	21.9	21.7	21.4	21.2	21.0
90°	12.0	12.8	13.6	14.1	14.5	15.0	15.4	15.9
92.5°	27.4	28.4	29.3	30.0	30.3	30.6	30.9	31.2
95°	53.1	54.0	55.1	55.7	56.1	56.4	56.6	56.9
97.5°	83.1	84.1	85.1	85.6	85.8	86.0	86.1	86.3
100°	103.9	105.2	106.6	107.4	107.7	108.0	108.3	108.5
102.5°	125.4	126.8	128.2	129.1	129.6	130.0	130.4	130.8
105°	160.0	160.9	161.8	162.4	162.8	163.3	163.7	164.2
107.5°	197.3	197.8	198.2	198.4	198.4	198.4	198.3	198.3
110°	223.3	223.7	224.2	224.4	224.2	224.0	223.9	223.7





TEST NUMBER: P333411-940

CATALOG NUMBER: S125DIW-S850D770U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	249.3	249.5	249.7	249.7	249.4	249.1	248.9	248.6
115°	289.0	288.8	288.6	288.6	288.4	288.3	288.1	287.9
117.5°	328.7	328.8	329.0	328.7	328.1	327.5	326.9	326.4
120°	355.4	355.4	355.4	355.2	354.6	354.0	353.4	352.8
122.5°	381.7	381.6	381.5	381.2	380.7	380.2	379.8	379.3
125°	420.4	420.1	419.8	419.6	419.5	419.3	419.2	419.0
127.5°	458.9	458.7	458.5	458.3	458.1	457.7	457.4	457.2
130°	484.3	484.1	483.9	483.8	483.5	483.1	482.9	482.6
132.5°	508.6	508.5	508.4	508.0	507.7	507.2	506.8	506.4
135°	546.1	546.1	546.1	545.8	545.2	544.7	544.0	543.5
137.5°	582.6	582.8	583.0	582.6	581.9	581.2	580.5	579.7
140°	605.6	605.9	606.2	606.0	605.3	604.5	603.8	603.1
142.5°	628.1	628.3	628.5	628.2	627.5	626.8	626.0	625.3
145°	660.7	660.7	660.7	660.4	660.0	659.5	659.1	658.6
147.5°	690.7	691.1	691.4	691.1	690.1	689.1	688.1	687.2
150°	709.6	709.6	709.6	709.4	709.2	708.9	708.6	708.3
152.5°	727.3	727.6	728.0	727.9	727.4	726.8	726.3	725.8
155°	752.5	753.0	753.7	753.6	752.9	752.2	751.4	750.6
157.5°	774.4	774.9	775.5	775.3	774.4	773.4	772.4	771.4
160°	787.6	788.2	788.7	788.7	787.9	787.2	786.5	785.8
162.5°	800.0	800.7	801.4	801.4	800.5	799.6	798.8	797.9
165°	816.7	817.3	817.9	817.7	816.9	816.0	815.1	814.2
167.5°	829.1	830.0	830.8	830.8	829.9	829.0	828.1	827.2
170°	836.5	837.4	838.3	838.2	837.1	836.2	835.1	834.1
172.5°	841.8	842.7	843.6	843.6	842.7	841.7	840.8	839.9
175°	847.7	848.6	849.5	849.4	848.4	847.4	846.3	845.3
177.5°	850.4	851.1	851.9	851.8	851.0	850.2	849.4	848.5
180°	850.6	850.6	850.6	850.6	850.6	850.6	850.6	850.6

(END OF REPORT)