

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333710-940

Luminaire Tested: **S125RDIW-S1090D1050U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333710-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1090D1050U940-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7503.8 lumens
Efficiency: N/A
Efficacy: 122.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333710-940

CATALOG NUMBER: S125RDIW-S1090D1050U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333710-940

CATALOG NUMBER: S125RDIW-S1090D1050U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	94	90	87	90	87	83	81	74	71	69	61	60	58	50	49	48	43
2	89	82	76	71	82	76	71	66	65	61	57	54	51	49	44	42	41	36
3	82	72	65	59	75	67	61	56	57	52	49	48	45	42	39	37	35	31
4	75	64	56	50	69	60	53	47	51	46	42	43	39	36	35	33	30	27
5	69	57	49	43	63	53	46	41	46	40	36	39	34	31	32	29	26	23
6	63	51	43	38	58	48	41	36	41	36	31	35	31	27	29	26	23	20
7	59	46	39	33	54	43	36	31	37	32	28	32	27	24	27	23	21	18
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	31	26	47	36	29	25	31	26	22	27	23	20	23	19	17	15
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10293	10293	10293
5°	10317	10200	10263
10°	10239	10105	10105
15°	10117	9900	9819
20°	9961	9614	9498
25°	9779	9333	9128
30°	9552	9004	8717
35°	9320	8665	8257
40°	9104	8312	7804
45°	8840	7916	7311
50°	8575	7486	6797
55°	8268	7076	6248
60°	7962	6577	5660
65°	7597	5997	4985
70°	7183	5274	4296
75°	6608	4447	3573
80°	5821	3492	2998
85°	4905	2853	2675



TEST NUMBER: P333710-940

CATALOG NUMBER: S125RDIW-S1090D1050U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.9	2.0
10°-20°	418.8	5.6
20°-30°	607.3	8.1
30°-40°	692.2	9.2
40°-50°	674.7	9.0
50°-60°	567.9	7.6
60°-70°	398.1	5.3
70°-80°	204.6	2.7
80°-90°	54.2	0.7
90°-100°	44.2	0.6
100°-110°	272.5	3.6
110°-120°	494.2	6.6
120°-130°	634.2	8.5
130°-140°	682.1	9.1
140°-150°	640.3	8.5
150°-160°	517.9	6.9
160°-170°	335.0	4.5
170°-180°	115.5	1.5
0°-30°	1176.0	15.7
0°-40°	1868.2	24.9
0°-60°	3110.9	41.5
0°-90°	3767.8	50.2
90°-120°	810.9	10.8
90°-150°	2767.5	36.9
90°-180°	3736.0	49.8
0°-180°	7503.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1594	1594	1594	1594	1594	
5°	1591	1586	1573	1585	1583	151
15°	1513	1505	1481	1479	1469	426
25°	1372	1353	1310	1294	1281	631
35°	1182	1152	1099	1065	1047	740
45°	968	931	867	820	800	746
55°	734	694	628	576	555	657
65°	497	455	392	346	326	492
75°	265	228	178	153	143	280
85°	66	45	38	37	36	74
90°	1	8	14	19	22	5
95°	51	47	14	19	19	66
105°	265	269	269	269	268	281
115°	498	502	503	500	494	493
125°	708	714	714	711	708	632
135°	883	888	886	884	879	680
145°	1024	1025	1025	1026	1021	640
155°	1127	1122	1124	1126	1119	519
165°	1190	1184	1185	1190	1183	336
175°	1217	1212	1212	1218	1211	116
180°	1217	1217	1217	1217	1217	



TEST NUMBER: P333710-940

CATALOG NUMBER: S125RDIW-S1090D1050U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1596.7	1596.1	1595.4	1594.7	1594.1	1592.8	1590.6	1588.5	1586.4	1584.2	1586.4
5°	1591.4	1590.4	1589.3	1588.2	1587.2	1585.1	1582.2	1579.2	1576.3	1573.3	1576.0
7.5°	1575.7	1574.8	1573.7	1572.7	1571.6	1569.4	1565.8	1562.4	1558.8	1555.3	1557.2
10°	1561.3	1560.5	1559.7	1558.9	1558.1	1555.9	1552.1	1548.4	1544.6	1540.9	1541.7
12.5°	1544.9	1543.9	1542.9	1541.9	1540.9	1537.8	1532.9	1527.8	1522.8	1517.7	1518.3
15°	1513.1	1511.5	1509.9	1508.3	1506.7	1503.2	1497.5	1491.9	1486.3	1480.7	1480.4
17.5°	1477.3	1474.8	1472.4	1469.9	1467.4	1462.7	1455.6	1448.6	1441.5	1434.4	1433.1
20°	1449.4	1446.7	1444.0	1441.4	1438.7	1433.1	1424.5	1415.9	1407.4	1398.8	1397.5
22.5°	1418.5	1415.9	1413.2	1410.5	1407.8	1402.0	1393.0	1384.0	1375.0	1366.0	1363.4
25°	1372.3	1368.3	1364.3	1360.3	1356.3	1349.3	1339.4	1329.5	1319.6	1309.7	1306.3
27.5°	1319.4	1314.5	1309.6	1304.8	1299.8	1292.2	1281.6	1271.0	1260.3	1249.7	1244.9
30°	1280.9	1275.8	1270.7	1265.6	1260.5	1252.3	1241.1	1229.8	1218.6	1207.4	1201.2
32.5°	1243.2	1237.3	1231.4	1225.5	1219.5	1210.9	1199.4	1187.9	1176.4	1165.0	1158.2
35°	1182.1	1175.7	1169.3	1162.9	1156.5	1147.2	1135.1	1123.1	1111.1	1099.0	1091.3
37.5°	1122.1	1114.4	1106.5	1098.8	1090.9	1080.8	1068.4	1056.0	1043.6	1031.2	1021.8
40°	1079.8	1071.7	1063.7	1055.7	1047.7	1037.2	1024.4	1011.6	998.7	985.9	975.7
42.5°	1035.5	1027.3	1019.0	1010.8	1002.6	991.8	978.5	965.3	952.0	938.7	929.0
45°	967.9	960.1	952.3	944.6	936.8	925.6	910.9	896.2	881.5	866.7	856.0
47.5°	897.8	889.6	881.4	873.3	865.0	853.5	838.7	823.9	809.0	794.2	783.2
50°	853.5	844.6	835.8	827.0	818.1	806.1	790.9	775.6	760.4	745.1	733.9
52.5°	805.3	796.3	787.2	778.2	769.2	757.4	743.1	728.6	714.3	699.9	687.8
55°	734.3	725.8	717.2	708.6	700.1	688.3	673.3	658.4	643.4	628.4	616.4
57.5°	662.5	653.4	644.3	635.1	626.0	614.2	599.8	585.3	570.9	556.4	544.7
60°	616.4	607.0	597.6	588.3	578.9	566.9	552.5	538.1	523.6	509.2	497.4
62.5°	567.2	558.3	549.4	540.4	531.5	519.7	505.1	490.4	475.7	461.0	450.1
65°	497.1	488.0	478.9	469.8	460.7	449.2	435.0	420.8	406.6	392.4	381.7
67.5°	427.6	418.5	409.4	400.3	391.2	379.9	366.2	352.7	339.1	325.5	315.8
70°	380.4	371.3	362.2	353.1	344.0	332.8	319.4	306.0	292.7	279.3	271.0
72.5°	334.2	325.3	316.4	307.6	298.6	287.9	275.4	262.9	250.4	237.9	230.2
75°	264.8	256.8	248.8	240.8	232.7	223.1	211.9	200.6	189.4	178.2	172.3
77.5°	196.0	189.6	183.2	176.7	170.3	162.6	153.6	144.6	135.6	126.6	122.5
80°	156.5	150.1	143.7	137.2	130.8	123.9	116.4	108.9	101.4	93.9	91.5
82.5°	118.0	112.2	106.4	100.7	94.9	89.4	84.3	79.1	74.0	68.8	67.8
85°	66.2	61.3	56.5	51.7	46.9	43.9	42.5	41.2	39.9	38.5	38.3
87.5°	22.3	21.1	20.0	18.8	17.7	17.0	17.1	17.2	17.3	17.3	17.6
90°	0.9	2.5	4.1	5.7	7.3	8.8	10.3	11.6	13.0	14.4	15.4
92.5°	13.9	12.8	11.7	10.5	9.4	9.5	10.7	11.9	13.2	14.4	15.4
95°	51.4	50.8	50.2	49.6	49.0	44.9	37.3	29.7	22.0	14.4	15.4
97.5°	107.4	108.4	109.5	110.6	111.6	104.7	89.6	74.5	59.5	44.4	38.7
100°	150.6	151.2	151.8	152.4	153.0	153.7	154.5	155.3	156.1	156.9	127.1
102.5°	194.7	195.4	196.2	196.9	197.7	198.3	198.8	199.2	199.7	200.2	194.6
105°	265.1	265.9	266.7	267.5	268.3	268.8	268.8	268.8	268.8	268.8	268.8
107.5°	338.4	338.4	338.4	338.4	338.4	338.6	338.9	339.4	339.7	340.2	340.2
110°	386.0	386.0	386.0	386.0	386.0	386.2	386.6	387.0	387.4	387.8	387.2



TEST NUMBER: P333710-940

CATALOG NUMBER: S125RDIW-S1090D1050U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	430.7	431.2	431.7	432.1	432.7	433.0	433.3	433.5	433.7	434.0	433.2
115°	497.8	498.8	499.8	500.8	501.9	502.4	502.7	502.8	503.0	503.2	502.4
117.5°	567.3	567.2	567.2	567.1	567.1	567.5	568.2	569.0	569.7	570.5	569.4
120°	610.6	610.4	610.1	609.9	609.8	609.9	610.6	611.2	611.7	612.3	612.0
122.5°	648.8	649.5	650.3	651.0	651.8	652.4	652.6	652.9	653.2	653.4	653.1
125°	707.9	709.4	710.8	712.1	713.5	714.3	714.3	714.3	714.3	714.3	713.5
127.5°	764.4	765.4	766.4	767.4	768.4	768.8	768.7	768.7	768.5	768.4	767.9
130°	799.1	800.0	801.0	802.0	803.1	803.6	803.9	804.1	804.2	804.4	803.9
132.5°	833.7	834.8	836.0	837.1	838.3	838.7	838.2	837.8	837.3	837.0	836.8
135°	882.9	884.1	885.3	886.5	887.7	888.1	887.7	887.3	886.9	886.5	886.1
137.5°	928.2	929.3	930.2	931.3	932.4	932.7	932.4	932.0	931.6	931.2	931.3
140°	957.8	958.1	958.6	958.9	959.4	959.5	959.3	959.0	958.9	958.7	959.0
142.5°	984.4	984.7	985.0	985.2	985.4	985.7	986.0	986.2	986.5	986.8	986.9
145°	1023.6	1024.0	1024.4	1024.8	1025.2	1025.4	1025.4	1025.4	1025.4	1025.4	1025.6
147.5°	1057.8	1057.8	1057.7	1057.7	1057.6	1057.7	1057.8	1058.1	1058.4	1058.5	1058.8
150°	1079.5	1079.1	1078.7	1078.3	1077.9	1077.9	1078.3	1078.7	1079.1	1079.5	1080.0
152.5°	1100.5	1099.6	1098.7	1097.8	1096.9	1096.7	1097.1	1097.5	1097.9	1098.2	1098.7
155°	1127.3	1126.1	1124.9	1123.7	1122.5	1122.1	1122.5	1122.9	1123.3	1123.7	1124.3
157.5°	1148.1	1147.4	1146.7	1145.9	1145.1	1144.9	1144.9	1144.9	1145.0	1145.0	1145.7
160°	1162.5	1161.3	1160.1	1158.9	1157.7	1157.2	1157.4	1157.6	1157.8	1158.0	1158.8
162.5°	1174.0	1172.9	1171.6	1170.5	1169.2	1168.7	1168.9	1169.1	1169.3	1169.5	1170.6
165°	1189.5	1188.4	1187.1	1186.0	1184.7	1184.2	1184.5	1184.6	1184.8	1185.0	1186.2
167.5°	1201.0	1199.9	1198.6	1197.4	1196.1	1195.6	1195.8	1196.0	1196.2	1196.4	1197.8
170°	1207.6	1206.2	1204.8	1203.4	1201.9	1201.4	1201.6	1201.8	1201.9	1202.2	1203.8
172.5°	1211.9	1210.5	1209.1	1207.7	1206.3	1205.8	1206.1	1206.5	1206.8	1207.2	1208.6
175°	1216.6	1215.4	1214.2	1213.0	1211.7	1211.3	1211.5	1211.7	1211.9	1212.1	1213.7
177.5°	1218.8	1217.8	1216.8	1215.8	1215.0	1214.5	1214.7	1214.9	1215.0	1215.1	1216.3
180°	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6



TEST NUMBER: P333710-940

CATALOG NUMBER: S125RDIW-S1090D1050U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1588.5	1590.6	1592.8	1593.7	1593.5	1593.3	1593.0	1592.9
5°	1578.7	1581.4	1584.0	1585.1	1584.6	1584.0	1583.5	1583.0
7.5°	1559.1	1560.9	1562.8	1563.4	1562.8	1562.3	1561.7	1561.0
10°	1542.5	1543.3	1544.1	1544.1	1543.3	1542.5	1541.7	1540.9
12.5°	1518.9	1519.5	1520.1	1519.7	1518.5	1517.3	1516.1	1514.8
15°	1480.2	1479.9	1479.6	1478.3	1475.9	1473.5	1471.1	1468.6
17.5°	1431.7	1430.4	1429.1	1427.5	1425.4	1423.4	1421.5	1419.5
20°	1396.2	1394.8	1393.5	1391.6	1389.2	1386.8	1384.4	1382.0
22.5°	1360.8	1358.2	1355.6	1353.3	1351.3	1349.3	1347.3	1345.3
25°	1302.8	1299.3	1295.8	1292.6	1289.7	1286.7	1283.8	1280.9
27.5°	1240.0	1235.2	1230.3	1226.5	1223.6	1220.8	1217.9	1215.1
30°	1195.1	1188.9	1182.8	1178.5	1176.1	1173.7	1171.3	1168.9
32.5°	1151.5	1144.6	1137.8	1132.9	1129.9	1126.9	1123.7	1120.7
35°	1083.5	1075.8	1068.0	1062.3	1058.5	1054.8	1051.1	1047.3
37.5°	1012.5	1003.3	993.9	987.5	983.8	980.2	976.5	972.9
40°	965.5	955.4	945.2	938.5	935.3	932.1	928.9	925.7
42.5°	919.3	909.5	899.7	892.5	887.8	883.2	878.4	873.7
45°	845.3	834.6	823.9	816.5	812.5	808.5	804.5	800.5
47.5°	772.2	761.2	750.2	742.4	738.0	733.5	729.2	724.7
50°	722.6	711.4	700.2	692.6	688.6	684.6	680.6	676.5
52.5°	675.7	663.6	651.5	643.5	639.4	635.4	631.4	627.4
55°	604.3	592.3	580.2	572.0	567.8	563.5	559.2	554.9
57.5°	532.9	521.1	509.3	501.5	497.8	493.9	490.1	486.3
60°	485.6	473.9	462.1	454.2	450.2	446.2	442.2	438.2
62.5°	439.3	428.3	417.4	409.9	405.9	401.9	397.9	393.9
65°	371.0	360.3	349.6	342.2	338.2	334.2	330.2	326.2
67.5°	305.9	296.1	286.3	279.8	276.6	273.4	270.2	267.0
70°	262.7	254.4	246.1	240.3	237.1	233.9	230.7	227.5
72.5°	222.6	214.9	207.2	202.3	200.2	198.0	195.9	193.8
75°	166.4	160.5	154.6	150.7	148.8	147.0	145.1	143.2
77.5°	118.4	114.3	110.1	107.4	106.0	104.6	103.3	101.8
80°	89.1	86.7	84.3	82.8	82.2	81.7	81.1	80.6
82.5°	66.6	65.5	64.4	63.7	63.3	63.0	62.7	62.3
85°	38.0	37.7	37.5	37.2	36.9	36.6	36.4	36.1
87.5°	17.7	17.9	18.1	18.2	18.1	18.0	17.9	17.8
90°	16.4	17.5	18.5	19.3	19.9	20.4	21.0	21.7
92.5°	16.4	17.5	18.5	19.1	19.4	19.6	19.9	20.2
95°	16.4	17.5	18.5	18.9	18.9	18.9	18.9	18.9
97.5°	33.1	27.4	21.8	18.9	18.9	18.9	18.9	18.9
100°	97.2	67.3	37.5	22.1	21.3	20.5	19.7	18.9
102.5°	188.9	183.2	177.6	168.0	154.4	140.7	127.1	113.4
105°	268.8	268.8	268.8	268.7	268.5	268.2	268.0	267.9
107.5°	340.3	340.3	340.4	340.1	339.5	338.9	338.2	337.7
110°	386.6	386.0	385.4	385.2	385.4	385.6	385.8	386.0



TEST NUMBER: P333710-940

CATALOG NUMBER: S125RDIW-S1090D1050U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	432.5	431.7	431.0	430.4	430.2	429.8	429.5	429.3
115°	501.6	500.8	500.0	499.0	497.8	496.6	495.4	494.2
117.5°	568.5	567.4	566.3	565.5	565.1	564.5	564.0	563.5
120°	611.5	611.2	610.7	610.0	609.0	608.1	607.1	606.0
122.5°	652.6	652.3	651.8	651.1	650.0	648.8	647.6	646.5
125°	712.7	711.9	711.1	710.3	709.8	709.2	708.6	707.9
127.5°	767.5	767.0	766.6	765.6	764.2	762.7	761.2	759.7
130°	803.3	802.6	802.0	801.2	800.2	799.2	798.3	797.3
132.5°	836.7	836.5	836.4	835.9	834.9	833.8	832.9	831.9
135°	885.7	885.3	884.9	884.1	882.9	881.7	880.5	879.3
137.5°	931.4	931.5	931.6	931.1	930.1	929.0	928.0	926.9
140°	959.5	959.8	960.3	959.8	958.7	957.4	956.3	955.0
142.5°	986.9	987.0	987.1	986.6	985.3	984.2	982.9	981.8
145°	1025.8	1026.0	1026.2	1025.7	1024.5	1023.3	1022.1	1020.9
147.5°	1059.1	1059.4	1059.5	1059.0	1057.5	1056.1	1054.6	1053.2
150°	1080.3	1080.8	1081.1	1080.5	1078.9	1077.3	1075.7	1074.1
152.5°	1099.0	1099.5	1099.8	1099.4	1097.9	1096.4	1095.0	1093.6
155°	1124.9	1125.5	1126.1	1125.6	1124.0	1122.4	1120.8	1119.2
157.5°	1146.3	1146.9	1147.5	1147.1	1145.5	1143.9	1142.3	1140.7
160°	1159.6	1160.4	1161.2	1160.7	1159.2	1157.6	1156.0	1154.4
162.5°	1171.8	1172.9	1174.0	1173.7	1171.9	1170.2	1168.4	1166.6
165°	1187.4	1188.7	1189.8	1189.6	1188.0	1186.4	1184.8	1183.2
167.5°	1199.3	1200.7	1202.2	1202.0	1200.2	1198.4	1196.6	1194.8
170°	1205.4	1207.0	1208.6	1208.4	1206.7	1204.9	1203.1	1201.2
172.5°	1210.1	1211.6	1213.0	1212.8	1211.0	1209.2	1207.4	1205.6
175°	1215.3	1216.9	1218.5	1218.4	1216.6	1214.8	1213.0	1211.2
177.5°	1217.4	1218.5	1219.7	1219.6	1218.3	1217.0	1215.8	1214.4
180°	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6

(END OF REPORT)