

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333702-940

Luminaire Tested: **S125RDIW-S1090D470U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333702-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1090D470U940-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5437.5 lumens
Efficiency: N/A
Efficacy: 117.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333702-940

CATALOG NUMBER: S125RDIW-S1090D470U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333702-940

CATALOG NUMBER: S125RDIW-S1090D470U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	94	94	94	83	83	83	74	74	74	69
1	102	98	94	91	97	93	89	86	83	80	78	74	72	70	66	64	63	59
2	94	86	80	75	88	82	76	71	73	69	65	65	62	59	58	56	54	50
3	86	76	68	63	81	72	65	60	65	60	55	58	54	50	52	49	46	43
4	78	67	59	53	74	64	57	51	58	52	47	52	47	43	47	43	40	37
5	72	60	52	46	68	57	50	44	52	46	41	47	42	38	42	38	35	32
6	67	54	46	40	63	52	44	39	47	41	36	42	37	33	38	34	31	28
7	62	49	41	35	58	47	40	34	43	37	32	39	34	30	35	31	28	25
8	57	45	37	32	54	43	36	31	39	33	29	36	30	27	32	28	25	23
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	30	26	22	20
10	50	38	31	26	48	36	29	25	33	27	23	30	25	22	28	23	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10293	10293	10293
5°	10317	10200	10263
10°	10239	10105	10105
15°	10117	9900	9819
20°	9961	9614	9498
25°	9779	9333	9128
30°	9552	9004	8717
35°	9320	8665	8257
40°	9104	8312	7804
45°	8840	7916	7311
50°	8575	7486	6797
55°	8268	7076	6248
60°	7962	6577	5660
65°	7597	5997	4985
70°	7183	5274	4296
75°	6608	4447	3573
80°	5821	3492	2998
85°	4905	2853	2675



TEST NUMBER: P333702-940

CATALOG NUMBER: S125RDIW-S1090D470U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.9	2.8
10°-20°	418.8	7.7
20°-30°	607.3	11.2
30°-40°	692.2	12.7
40°-50°	674.7	12.4
50°-60°	567.9	10.4
60°-70°	398.1	7.3
70°-80°	204.6	3.8
80°-90°	52.8	1.0
90°-100°	19.8	0.4
100°-110°	121.9	2.2
110°-120°	221.0	4.1
120°-130°	283.7	5.2
130°-140°	305.1	5.6
140°-150°	286.4	5.3
150°-160°	231.7	4.3
160°-170°	149.8	2.8
170°-180°	51.7	1.0
0°-30°	1176.0	21.6
0°-40°	1868.2	34.4
0°-60°	3110.9	57.2
0°-90°	3766.4	69.3
90°-120°	362.7	6.7
90°-150°	1237.9	22.8
90°-180°	1671.0	30.7
0°-180°	5437.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1594	1594	1594	1594	1594	
5°	1591	1586	1573	1585	1583	151
15°	1513	1505	1481	1479	1469	426
25°	1372	1353	1310	1294	1281	631
35°	1182	1152	1099	1065	1047	740
45°	968	931	867	820	800	746
55°	734	694	628	576	555	657
65°	497	455	392	346	326	492
75°	265	228	178	153	143	280
85°	66	45	38	37	36	74
90°	0	4	6	8	10	4
95°	23	21	6	8	8	29
105°	119	120	120	120	120	126
115°	223	225	225	223	221	221
125°	317	319	320	318	317	283
135°	395	397	396	396	393	304
145°	458	459	459	459	457	286
155°	504	502	503	504	501	232
165°	532	530	530	532	529	150
175°	544	542	542	545	542	52
180°	544	544	544	544	544	



TEST NUMBER: P333702-940

CATALOG NUMBER: S125RDIW-S1090D470U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1596.7	1596.1	1595.4	1594.7	1594.1	1592.8	1590.6	1588.5	1586.4	1584.2	1586.4
5°	1591.4	1590.4	1589.3	1588.2	1587.2	1585.1	1582.2	1579.2	1576.3	1573.3	1576.0
7.5°	1575.7	1574.8	1573.7	1572.7	1571.6	1569.4	1565.8	1562.4	1558.8	1555.3	1557.2
10°	1561.3	1560.5	1559.7	1558.9	1558.1	1555.9	1552.1	1548.4	1544.6	1540.9	1541.7
12.5°	1544.9	1543.9	1542.9	1541.9	1540.9	1537.8	1532.9	1527.8	1522.8	1517.7	1518.3
15°	1513.1	1511.5	1509.9	1508.3	1506.7	1503.2	1497.5	1491.9	1486.3	1480.7	1480.4
17.5°	1477.3	1474.8	1472.4	1469.9	1467.4	1462.7	1455.6	1448.6	1441.5	1434.4	1433.1
20°	1449.4	1446.7	1444.0	1441.4	1438.7	1433.1	1424.5	1415.9	1407.4	1398.8	1397.5
22.5°	1418.5	1415.9	1413.2	1410.5	1407.8	1402.0	1393.0	1384.0	1375.0	1366.0	1363.4
25°	1372.3	1368.3	1364.3	1360.3	1356.3	1349.3	1339.4	1329.5	1319.6	1309.7	1306.3
27.5°	1319.4	1314.5	1309.6	1304.8	1299.8	1292.2	1281.6	1271.0	1260.3	1249.7	1244.9
30°	1280.9	1275.8	1270.7	1265.6	1260.5	1252.3	1241.1	1229.8	1218.6	1207.4	1201.2
32.5°	1243.2	1237.3	1231.4	1225.5	1219.5	1210.9	1199.4	1187.9	1176.4	1165.0	1158.2
35°	1182.1	1175.7	1169.3	1162.9	1156.5	1147.2	1135.1	1123.1	1111.1	1099.0	1091.3
37.5°	1122.1	1114.4	1106.5	1098.8	1090.9	1080.8	1068.4	1056.0	1043.6	1031.2	1021.8
40°	1079.8	1071.7	1063.7	1055.7	1047.7	1037.2	1024.4	1011.6	998.7	985.9	975.7
42.5°	1035.5	1027.3	1019.0	1010.8	1002.6	991.8	978.5	965.3	952.0	938.7	929.0
45°	967.9	960.1	952.3	944.6	936.8	925.6	910.9	896.2	881.5	866.7	856.0
47.5°	897.8	889.6	881.4	873.3	865.0	853.5	838.7	823.9	809.0	794.2	783.2
50°	853.5	844.6	835.8	827.0	818.1	806.1	790.9	775.6	760.4	745.1	733.9
52.5°	805.3	796.3	787.2	778.2	769.2	757.4	743.1	728.6	714.3	699.9	687.8
55°	734.3	725.8	717.2	708.6	700.1	688.3	673.3	658.4	643.4	628.4	616.4
57.5°	662.5	653.4	644.3	635.1	626.0	614.2	599.8	585.3	570.9	556.4	544.7
60°	616.4	607.0	597.6	588.3	578.9	566.9	552.5	538.1	523.6	509.2	497.4
62.5°	567.2	558.3	549.4	540.4	531.5	519.7	505.1	490.4	475.7	461.0	450.1
65°	497.1	488.0	478.9	469.8	460.7	449.2	435.0	420.8	406.6	392.4	381.7
67.5°	427.6	418.5	409.4	400.3	391.2	379.9	366.2	352.7	339.1	325.5	315.8
70°	380.4	371.3	362.2	353.1	344.0	332.8	319.4	306.0	292.7	279.3	271.0
72.5°	334.2	325.3	316.4	307.6	298.6	287.9	275.4	262.9	250.4	237.9	230.2
75°	264.8	256.8	248.8	240.8	232.7	223.1	211.9	200.6	189.4	178.2	172.3
77.5°	196.0	189.6	183.2	176.7	170.3	162.6	153.6	144.6	135.6	126.6	122.5
80°	156.5	150.1	143.7	137.2	130.8	123.9	116.4	108.9	101.4	93.9	91.5
82.5°	118.0	112.2	106.4	100.7	94.9	89.4	84.3	79.1	74.0	68.8	67.8
85°	66.2	61.3	56.5	51.7	46.9	43.9	42.5	41.2	39.9	38.5	38.3
87.5°	22.2	20.9	19.5	18.2	16.9	16.1	16.0	15.9	15.8	15.7	15.8
90°	0.4	1.2	1.9	2.6	3.3	3.9	4.5	5.2	5.8	6.4	6.9
92.5°	6.2	5.7	5.2	4.7	4.2	4.2	4.8	5.4	5.9	6.4	6.9
95°	23.0	22.7	22.5	22.2	21.9	20.1	16.7	13.3	9.9	6.4	6.9
97.5°	48.0	48.5	49.0	49.5	49.9	46.8	40.0	33.3	26.6	19.9	17.3
100°	67.3	67.7	67.9	68.2	68.5	68.8	69.1	69.5	69.8	70.2	56.8
102.5°	87.0	87.4	87.7	88.1	88.5	88.7	88.9	89.1	89.3	89.5	87.0
105°	118.6	119.0	119.3	119.7	120.0	120.2	120.2	120.2	120.2	120.2	120.2
107.5°	151.3	151.3	151.3	151.3	151.3	151.4	151.6	151.8	151.9	152.1	152.2
110°	172.6	172.6	172.6	172.6	172.6	172.7	172.9	173.1	173.3	173.4	173.2



TEST NUMBER: P333702-940

CATALOG NUMBER: S125RDIW-S1090D470U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	192.7	192.9	193.1	193.3	193.5	193.7	193.8	193.9	194.0	194.1	193.8
115°	222.7	223.1	223.6	224.0	224.4	224.7	224.8	224.9	225.0	225.1	224.7
117.5°	253.8	253.7	253.7	253.7	253.7	253.9	254.1	254.5	254.9	255.2	254.8
120°	273.1	273.0	273.0	272.9	272.8	272.9	273.1	273.4	273.7	273.9	273.8
122.5°	290.3	290.5	290.9	291.2	291.6	291.8	291.9	292.0	292.2	292.3	292.1
125°	316.6	317.3	317.9	318.5	319.1	319.5	319.5	319.5	319.5	319.5	319.1
127.5°	341.9	342.4	342.9	343.3	343.8	343.9	343.8	343.8	343.8	343.7	343.5
130°	357.4	357.8	358.3	358.7	359.2	359.4	359.5	359.6	359.7	359.8	359.5
132.5°	372.9	373.4	374.0	374.4	375.0	375.1	375.0	374.8	374.5	374.3	374.3
135°	394.9	395.5	396.0	396.5	397.1	397.3	397.1	396.9	396.7	396.5	396.4
137.5°	415.2	415.6	416.1	416.6	417.1	417.2	417.1	416.9	416.7	416.5	416.6
140°	428.4	428.6	428.7	428.9	429.1	429.2	429.1	429.0	428.9	428.8	429.0
142.5°	440.3	440.5	440.6	440.7	440.8	440.9	441.0	441.1	441.3	441.4	441.4
145°	457.9	458.1	458.3	458.4	458.6	458.7	458.7	458.7	458.7	458.7	458.8
147.5°	473.2	473.1	473.1	473.1	473.1	473.1	473.2	473.3	473.4	473.5	473.6
150°	482.9	482.7	482.5	482.3	482.1	482.1	482.3	482.5	482.7	482.9	483.0
152.5°	492.2	491.9	491.4	491.1	490.6	490.5	490.7	490.9	491.1	491.2	491.4
155°	504.3	503.7	503.2	502.7	502.1	501.9	502.1	502.3	502.5	502.7	502.9
157.5°	513.5	513.2	512.9	512.6	512.2	512.1	512.1	512.1	512.1	512.2	512.5
160°	520.0	519.4	518.9	518.4	517.8	517.6	517.7	517.8	517.9	518.0	518.4
162.5°	525.1	524.6	524.1	523.5	523.0	522.8	522.9	523.0	523.1	523.2	523.6
165°	532.1	531.5	531.0	530.5	529.9	529.7	529.8	529.9	529.9	530.0	530.6
167.5°	537.3	536.7	536.2	535.6	535.0	534.8	534.8	534.9	535.0	535.1	535.8
170°	540.2	539.6	538.9	538.2	537.6	537.3	537.4	537.5	537.6	537.7	538.4
172.5°	542.1	541.4	540.8	540.2	539.6	539.4	539.5	539.7	539.8	540.0	540.6
175°	544.2	543.7	543.1	542.6	542.1	541.8	541.9	542.0	542.1	542.2	542.9
177.5°	545.2	544.7	544.3	543.9	543.4	543.2	543.3	543.4	543.5	543.6	544.0
180°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2



TEST NUMBER: P333702-940

CATALOG NUMBER: S125RDIW-S1090D470U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1588.5	1590.6	1592.8	1593.7	1593.5	1593.3	1593.0	1592.9
5°	1578.7	1581.4	1584.0	1585.1	1584.6	1584.0	1583.5	1583.0
7.5°	1559.1	1560.9	1562.8	1563.4	1562.8	1562.3	1561.7	1561.0
10°	1542.5	1543.3	1544.1	1544.1	1543.3	1542.5	1541.7	1540.9
12.5°	1518.9	1519.5	1520.1	1519.7	1518.5	1517.3	1516.1	1514.8
15°	1480.2	1479.9	1479.6	1478.3	1475.9	1473.5	1471.1	1468.6
17.5°	1431.7	1430.4	1429.1	1427.5	1425.4	1423.4	1421.5	1419.5
20°	1396.2	1394.8	1393.5	1391.6	1389.2	1386.8	1384.4	1382.0
22.5°	1360.8	1358.2	1355.6	1353.3	1351.3	1349.3	1347.3	1345.3
25°	1302.8	1299.3	1295.8	1292.6	1289.7	1286.7	1283.8	1280.9
27.5°	1240.0	1235.2	1230.3	1226.5	1223.6	1220.8	1217.9	1215.1
30°	1195.1	1188.9	1182.8	1178.5	1176.1	1173.7	1171.3	1168.9
32.5°	1151.5	1144.6	1137.8	1132.9	1129.9	1126.9	1123.7	1120.7
35°	1083.5	1075.8	1068.0	1062.3	1058.5	1054.8	1051.1	1047.3
37.5°	1012.5	1003.3	993.9	987.5	983.8	980.2	976.5	972.9
40°	965.5	955.4	945.2	938.5	935.3	932.1	928.9	925.7
42.5°	919.3	909.5	899.7	892.5	887.8	883.2	878.4	873.7
45°	845.3	834.6	823.9	816.5	812.5	808.5	804.5	800.5
47.5°	772.2	761.2	750.2	742.4	738.0	733.5	729.2	724.7
50°	722.6	711.4	700.2	692.6	688.6	684.6	680.6	676.5
52.5°	675.7	663.6	651.5	643.5	639.4	635.4	631.4	627.4
55°	604.3	592.3	580.2	572.0	567.8	563.5	559.2	554.9
57.5°	532.9	521.1	509.3	501.5	497.8	493.9	490.1	486.3
60°	485.6	473.9	462.1	454.2	450.2	446.2	442.2	438.2
62.5°	439.3	428.3	417.4	409.9	405.9	401.9	397.9	393.9
65°	371.0	360.3	349.6	342.2	338.2	334.2	330.2	326.2
67.5°	305.9	296.1	286.3	279.8	276.6	273.4	270.2	267.0
70°	262.7	254.4	246.1	240.3	237.1	233.9	230.7	227.5
72.5°	222.6	214.9	207.2	202.3	200.2	198.0	195.9	193.8
75°	166.4	160.5	154.6	150.7	148.8	147.0	145.1	143.2
77.5°	118.4	114.3	110.1	107.4	106.0	104.6	103.3	101.8
80°	89.1	86.7	84.3	82.8	82.2	81.7	81.1	80.6
82.5°	66.6	65.5	64.4	63.7	63.3	63.0	62.7	62.3
85°	38.0	37.7	37.5	37.2	36.9	36.6	36.4	36.1
87.5°	15.9	16.0	16.1	16.1	15.9	15.8	15.6	15.4
90°	7.3	7.8	8.2	8.6	8.9	9.2	9.5	9.7
92.5°	7.3	7.8	8.2	8.6	8.6	8.8	8.9	9.0
95°	7.3	7.8	8.2	8.5	8.5	8.5	8.5	8.5
97.5°	14.8	12.3	9.7	8.5	8.5	8.5	8.5	8.5
100°	43.5	30.1	16.8	9.9	9.5	9.2	8.8	8.5
102.5°	84.5	81.9	79.5	75.2	69.0	63.0	56.8	50.7
105°	120.2	120.2	120.2	120.2	120.1	120.0	119.9	119.8
107.5°	152.2	152.2	152.2	152.1	151.9	151.6	151.3	151.1
110°	172.9	172.6	172.4	172.3	172.4	172.5	172.5	172.6



TEST NUMBER: P333702-940

CATALOG NUMBER: S125RDIW-S1090D470U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	193.4	193.1	192.8	192.5	192.4	192.3	192.2	192.0
115°	224.4	224.0	223.6	223.2	222.7	222.1	221.6	221.1
117.5°	254.2	253.8	253.3	253.0	252.7	252.5	252.3	252.1
120°	273.6	273.4	273.2	272.9	272.4	272.0	271.5	271.1
122.5°	291.9	291.8	291.6	291.2	290.7	290.2	289.7	289.2
125°	318.8	318.4	318.1	317.7	317.4	317.2	316.9	316.6
127.5°	343.3	343.1	343.0	342.5	341.8	341.2	340.5	339.8
130°	359.3	359.0	358.7	358.4	357.9	357.5	357.0	356.6
132.5°	374.3	374.2	374.2	373.9	373.4	373.0	372.6	372.1
135°	396.2	396.0	395.8	395.5	394.9	394.4	393.9	393.3
137.5°	416.6	416.7	416.7	416.5	416.0	415.5	415.1	414.6
140°	429.2	429.4	429.5	429.4	428.8	428.3	427.8	427.2
142.5°	441.5	441.5	441.6	441.3	440.8	440.2	439.7	439.2
145°	458.9	459.0	459.1	458.8	458.3	457.7	457.2	456.6
147.5°	473.8	473.9	473.9	473.7	473.1	472.4	471.7	471.1
150°	483.2	483.4	483.6	483.3	482.6	481.9	481.2	480.5
152.5°	491.6	491.8	492.0	491.8	491.1	490.4	489.8	489.2
155°	503.2	503.5	503.7	503.5	502.7	502.0	501.3	500.6
157.5°	512.7	513.0	513.3	513.1	512.4	511.7	511.0	510.2
160°	518.7	519.1	519.4	519.2	518.5	517.8	517.1	516.4
162.5°	524.1	524.7	525.1	525.0	524.2	523.4	522.6	521.8
165°	531.2	531.7	532.3	532.2	531.5	530.7	529.9	529.2
167.5°	536.5	537.1	537.7	537.7	536.8	536.0	535.2	534.4
170°	539.1	539.9	540.6	540.6	539.8	539.0	538.1	537.3
172.5°	541.3	541.9	542.6	542.5	541.7	540.9	540.1	539.3
175°	543.6	544.3	545.0	545.0	544.2	543.4	542.6	541.8
177.5°	544.6	545.0	545.5	545.5	544.9	544.4	543.8	543.2
180°	544.2	544.2	544.2	544.2	544.2	544.2	544.2	544.2

(END OF REPORT)