

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333733-940

Luminaire Tested: **S125RDIW-S1270D1340U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333733-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1270D1340U940-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8537.8 lumens
Efficiency: N/A
Efficacy: 112.0 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333733-940

CATALOG NUMBER: S125RDIW-S1270D1340U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333733-940

CATALOG NUMBER: S125RDIW-S1270D1340U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	99	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	83	77	72	83	77	72	67	66	62	59	55	53	50	46	44	42	38
3	82	73	66	60	76	68	62	57	58	54	50	49	46	43	41	38	36	32
4	76	65	57	51	70	60	54	48	52	47	43	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	42	47	41	37	40	36	32	33	30	28	25
6	64	52	44	38	59	49	42	36	42	37	32	36	32	28	30	27	24	22
7	59	47	39	34	55	44	37	32	38	33	29	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	25	22	20	17
9	51	39	32	27	47	37	30	25	32	27	23	28	23	20	23	20	18	16
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10936	10936	10936	10936
5°	12582	10950	9671	10950
10°	14432	10895	8533	10895
15°	15588	10783	7585	10783
20°	17189	10654	7003	10654
25°	19892	10481	6499	10481
30°	21647	10300	6169	10300
35°	18260	10089	5864	10089
40°	12752	9711	5602	9711
45°	9460	9199	5345	9199
50°	7543	8667	5126	8667
55°	6402	8007	4931	8007
60°	5531	7417	4615	7417
65°	4928	6776	3972	6776
70°	4330	6209	3622	6209
75°	3748	5375	3401	5375
80°	2841	4523	2841	4523
85°	2371	3557	2675	3557



TEST NUMBER: P333733-940

CATALOG NUMBER: S125RDIW-S1270D1340U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.4	1.9
10°-20°	475.9	5.6
20°-30°	754.5	8.8
30°-40°	909.8	10.7
40°-50°	812.5	9.5
50°-60°	623.1	7.3
60°-70°	404.9	4.7
70°-80°	196.9	2.3
80°-90°	50.2	0.6
90°-100°	99.5	1.2
100°-110°	294.0	3.4
110°-120°	497.9	5.8
120°-130°	655.3	7.7
130°-140°	734.3	8.6
140°-150°	719.7	8.4
150°-160°	604.5	7.1
160°-170°	401.8	4.7
170°-180°	140.6	1.6
0°-30°	1392.7	16.3
0°-40°	2302.6	27.0
0°-60°	3738.2	43.8
0°-90°	4390.2	51.4
90°-120°	891.4	10.4
90°-150°	3000.7	35.1
90°-180°	4148.0	48.6
0°-180°	8537.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1693	1693	1693	1693	1693	
5°	1941	1689	1492	1689	1941	194
15°	2331	1613	1134	1613	2331	668
25°	2792	1471	912	1471	2792	1282
35°	2316	1280	744	1280	2316	1399
45°	1036	1007	585	1007	1036	826
55°	569	711	438	711	569	516
65°	322	443	260	443	322	321
75°	150	215	136	215	150	160
85°	32	48	36	48	32	37
90°	28	1	28	1	28	17
95°	100	75	100	75	100	101
105°	287	264	287	264	287	304
115°	503	499	503	499	503	498
125°	732	728	732	728	732	654
135°	950	946	950	946	950	733
145°	1151	1146	1151	1146	1151	718
155°	1312	1312	1312	1312	1312	604
165°	1423	1426	1423	1426	1423	401
175°	1477	1483	1477	1483	1477	140
180°	1486	1486	1486	1486	1486	



TEST NUMBER: P333733-940

CATALOG NUMBER: S125RDIW-S1270D1340U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1781.1	1780.0	1782.3	1776.1	1776.6	1767.2	1767.2	1760.0	1750.5	1743.3	1740.0
5°	1940.7	1942.1	1939.3	1928.9	1922.0	1911.6	1899.7	1878.8	1861.4	1844.8	1831.6
7.5°	2105.1	2106.0	2096.9	2093.6	2076.1	2063.3	2037.0	2008.7	1983.5	1951.6	1927.1
10°	2200.7	2200.0	2190.2	2182.6	2167.3	2147.9	2122.2	2088.7	2057.5	2022.8	1989.4
12.5°	2256.3	2254.5	2251.4	2242.1	2227.9	2210.7	2188.9	2156.1	2117.5	2079.5	2040.5
15°	2331.4	2326.5	2317.5	2305.6	2285.5	2265.3	2241.0	2211.8	2175.0	2131.9	2095.7
17.5°	2424.2	2424.4	2410.5	2394.1	2366.7	2331.1	2293.6	2246.4	2196.4	2148.9	2110.5
20°	2501.0	2498.8	2485.0	2453.0	2421.7	2377.2	2334.1	2276.4	2215.3	2153.4	2105.4
22.5°	2611.1	2605.7	2591.2	2549.2	2500.7	2443.4	2377.5	2307.0	2233.1	2162.8	2099.9
25°	2791.5	2787.3	2758.9	2710.2	2642.0	2553.8	2467.6	2371.0	2264.7	2172.2	2095.7
27.5°	2915.0	2910.4	2889.2	2848.8	2786.0	2693.1	2576.4	2447.3	2314.5	2187.4	2077.1
30°	2902.7	2913.1	2910.4	2891.6	2844.4	2760.9	2653.2	2507.9	2350.1	2200.7	2069.3
32.5°	2728.1	2737.5	2761.9	2798.7	2801.5	2768.1	2687.7	2553.5	2390.1	2220.2	2063.2
35°	2316.0	2328.6	2375.9	2450.2	2547.5	2628.9	2645.5	2573.3	2426.6	2243.8	2054.1
37.5°	1780.6	1849.0	1888.7	1967.0	2114.1	2263.7	2407.5	2460.5	2398.1	2234.1	2039.2
40°	1512.5	1529.2	1600.1	1688.4	1812.1	1967.8	2172.9	2320.9	2325.8	2211.8	2015.8
42.5°	1294.6	1315.7	1364.3	1434.9	1540.8	1696.5	1908.2	2103.5	2194.1	2150.6	1985.2
45°	1035.7	1051.7	1087.2	1141.4	1222.7	1351.3	1533.4	1759.3	1938.7	2008.8	1903.2
47.5°	850.8	859.4	890.3	931.6	991.8	1085.5	1226.5	1422.5	1637.6	1788.5	1773.6
50°	750.7	760.5	784.1	815.4	866.1	945.3	1057.9	1221.3	1443.1	1627.2	1664.1
52.5°	672.9	680.9	695.6	725.2	767.1	828.0	918.9	1066.7	1266.2	1462.0	1547.3
55°	568.6	574.2	585.9	602.6	636.1	679.8	758.3	860.5	1021.8	1219.2	1344.3
57.5°	482.7	485.4	492.9	508.4	531.5	563.5	620.2	706.8	822.4	1000.2	1138.3
60°	428.2	431.0	440.7	451.1	469.2	498.4	542.9	603.3	714.5	861.2	1000.9
62.5°	384.8	386.5	390.7	401.1	417.0	439.4	474.5	523.8	612.2	741.1	873.1
65°	322.5	323.2	324.6	333.0	342.7	359.4	382.3	417.1	483.8	581.1	697.9
67.5°	262.8	263.7	268.6	271.5	281.7	290.4	303.9	330.5	377.5	443.1	533.9
70°	229.3	228.7	233.5	237.0	240.5	250.9	259.9	281.5	310.7	360.8	436.5
72.5°	198.2	196.4	198.5	199.7	204.4	211.4	220.5	233.7	256.2	290.7	348.7
75°	150.2	150.9	150.9	152.2	155.7	158.5	161.2	168.2	180.7	203.7	235.0
77.5°	105.4	104.2	107.2	107.6	109.7	112.7	115.1	117.9	123.1	132.5	148.6
80°	76.4	76.4	77.1	79.3	78.6	79.9	83.4	86.2	92.5	98.0	103.5
82.5°	58.7	58.1	58.8	59.2	59.1	60.5	61.7	62.2	64.6	67.4	71.3
85°	32.0	32.0	32.6	32.6	33.3	33.3	34.1	34.1	34.1	34.8	35.5
87.5°	17.7	17.0	16.4	16.2	16.6	17.5	16.7	15.9	15.6	15.3	15.6
90°	27.7	27.0	26.2	25.4	24.7	23.6	22.4	21.0	19.8	18.5	16.7
92.5°	54.6	54.0	53.5	52.9	52.3	51.2	49.5	47.8	46.1	44.4	42.2
95°	99.5	99.0	98.4	97.9	97.4	96.3	94.4	92.6	90.9	89.1	86.5
97.5°	150.9	150.5	150.3	149.9	149.6	148.6	146.9	145.2	143.5	141.8	138.3
100°	189.7	189.2	188.7	188.2	187.6	186.2	183.9	181.6	179.3	177.0	173.6
102.5°	228.5	227.8	227.1	226.4	225.7	224.1	221.5	219.0	216.5	214.0	212.3
105°	286.9	286.1	285.3	284.5	283.7	282.6	281.1	279.6	278.0	276.4	274.9
107.5°	346.5	346.6	346.6	346.7	346.8	346.4	345.6	344.8	344.1	343.3	342.1
110°	390.9	391.2	391.5	391.7	392.0	391.7	390.9	390.2	389.4	388.6	387.9



TEST NUMBER: P333733-940

CATALOG NUMBER: S125RDIW-S1270D1340U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	434.4	434.9	435.4	435.9	436.3	436.3	436.0	435.6	435.2	434.9	433.9
115°	503.2	503.5	503.6	503.9	504.2	504.4	504.7	505.0	505.2	505.5	505.0
117.5°	570.2	571.3	572.3	573.4	574.4	574.8	574.5	574.4	574.2	574.0	573.5
120°	616.5	617.5	618.6	619.6	620.6	621.2	621.2	621.2	621.2	621.2	620.9
122.5°	662.8	663.6	664.4	665.2	666.1	666.6	666.8	667.0	667.2	667.4	666.7
125°	732.2	732.5	732.7	733.0	733.3	733.6	734.1	734.6	735.1	735.7	735.4
127.5°	798.8	799.3	799.9	800.4	800.8	801.3	801.5	801.7	802.0	802.3	802.0
130°	843.2	843.7	844.3	844.8	845.3	845.7	846.0	846.1	846.4	846.7	846.1
132.5°	884.8	885.6	886.3	887.1	887.8	888.2	888.5	888.8	889.0	889.3	889.4
135°	949.7	950.7	951.7	952.7	953.8	954.3	954.3	954.3	954.3	954.3	954.0
137.5°	1013.1	1014.3	1015.6	1016.9	1018.2	1018.7	1018.3	1018.1	1017.7	1017.4	1016.9
140°	1053.7	1055.1	1056.3	1057.6	1058.9	1059.3	1058.7	1058.3	1057.7	1057.2	1056.4
142.5°	1092.6	1093.9	1095.2	1096.4	1097.8	1098.2	1098.0	1097.6	1097.3	1097.0	1096.0
145°	1150.9	1151.6	1152.4	1153.2	1154.0	1154.4	1154.4	1154.4	1154.4	1154.4	1153.6
147.5°	1200.7	1202.4	1204.2	1205.9	1207.6	1208.2	1207.6	1206.9	1206.4	1205.8	1205.1
150°	1237.7	1238.1	1238.7	1239.2	1239.7	1240.0	1240.0	1240.0	1240.0	1240.0	1238.9
152.5°	1268.2	1269.1	1270.1	1271.0	1271.9	1272.0	1271.4	1270.8	1270.2	1269.6	1269.2
155°	1311.7	1313.0	1314.3	1315.5	1316.8	1317.0	1315.9	1314.9	1313.8	1312.9	1312.6
157.5°	1348.0	1349.7	1351.4	1353.1	1354.8	1355.1	1354.1	1353.1	1352.0	1351.0	1350.8
160°	1373.0	1374.3	1375.6	1376.9	1378.1	1378.2	1377.2	1376.2	1375.2	1374.1	1373.9
162.5°	1394.3	1395.8	1397.2	1398.7	1400.3	1400.3	1399.1	1397.9	1396.7	1395.4	1395.3
165°	1422.7	1424.2	1425.8	1427.4	1428.9	1429.1	1428.2	1427.1	1426.1	1425.0	1424.8
167.5°	1445.4	1447.0	1448.6	1450.2	1451.8	1451.8	1450.3	1448.8	1447.2	1445.6	1445.6
170°	1457.4	1459.2	1461.1	1462.9	1464.6	1464.7	1463.2	1461.7	1460.2	1458.6	1458.6
172.5°	1467.6	1469.2	1470.8	1472.4	1474.0	1474.0	1472.5	1471.0	1469.4	1467.8	1467.8
175°	1477.1	1478.9	1480.7	1482.5	1484.3	1484.4	1482.9	1481.3	1479.8	1478.3	1478.3
177.5°	1482.6	1484.1	1485.5	1486.9	1488.4	1488.5	1487.3	1486.0	1484.8	1483.5	1483.8
180°	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4



TEST NUMBER: P333733-940

CATALOG NUMBER: S125RDIW-S1270D1340U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1740.0	1736.1	1728.8	1722.2	1713.9	1706.6	1701.6	1695.5	1687.7	1678.3	1670.4
5°	1816.9	1801.7	1781.5	1764.2	1742.0	1724.6	1706.5	1689.1	1671.7	1649.5	1630.0
7.5°	1902.4	1870.8	1840.0	1801.4	1766.4	1735.1	1705.0	1674.6	1644.8	1613.3	1582.9
10°	1954.6	1916.4	1874.0	1825.3	1780.8	1738.5	1699.5	1661.3	1621.0	1585.6	1547.3
12.5°	2003.6	1954.2	1905.7	1844.2	1790.8	1739.0	1689.5	1641.8	1598.7	1552.7	1511.7
15°	2047.7	1999.1	1944.9	1869.8	1795.5	1732.9	1674.5	1612.7	1559.1	1507.7	1461.8
17.5°	2064.8	2013.8	1950.9	1878.7	1797.4	1718.7	1643.5	1575.7	1512.7	1452.8	1401.1
20°	2058.2	2008.8	1944.2	1875.4	1788.5	1706.5	1625.1	1550.1	1479.9	1416.6	1361.7
22.5°	2042.1	1991.0	1928.6	1855.9	1773.4	1686.5	1599.6	1519.5	1445.9	1380.5	1320.5
25°	2017.9	1948.4	1884.5	1813.5	1735.0	1648.8	1559.1	1470.8	1392.3	1325.5	1260.3
27.5°	1992.7	1905.9	1824.6	1754.2	1671.2	1594.3	1507.8	1417.3	1334.7	1266.8	1199.7
30°	1969.9	1872.6	1782.9	1703.0	1624.4	1551.5	1469.5	1381.2	1296.4	1226.2	1158.1
32.5°	1941.5	1838.1	1739.5	1647.3	1571.6	1499.2	1425.0	1340.6	1258.0	1185.5	1116.3
35°	1905.9	1773.9	1666.9	1568.9	1484.7	1414.5	1347.8	1279.7	1196.9	1121.9	1054.4
37.5°	1859.2	1709.4	1585.6	1478.7	1390.1	1319.6	1266.9	1204.6	1129.1	1057.2	994.7
40°	1830.9	1662.7	1527.1	1421.5	1328.3	1253.9	1204.6	1151.8	1083.0	1015.6	953.0
42.5°	1793.1	1619.9	1468.2	1358.1	1264.4	1192.8	1142.9	1096.7	1039.0	975.5	908.5
45°	1719.0	1536.9	1377.7	1259.5	1165.0	1094.8	1048.2	1007.2	963.4	905.0	846.6
47.5°	1622.5	1450.3	1283.7	1154.7	1062.1	996.9	951.7	919.4	888.1	838.4	781.7
50°	1545.2	1379.1	1216.4	1091.3	992.6	930.8	888.3	862.6	834.1	788.9	741.6
52.5°	1454.0	1305.6	1146.4	1018.4	925.3	867.4	826.6	800.9	777.4	740.6	695.5
55°	1310.3	1180.3	1034.3	918.2	832.8	774.4	735.4	711.1	697.2	665.9	630.4
57.5°	1144.4	1051.2	922.6	810.7	735.0	677.3	648.8	628.1	612.4	590.3	565.3
60°	1028.8	963.4	848.0	741.6	672.2	617.2	591.6	574.2	559.5	540.8	521.3
62.5°	911.4	863.9	763.5	672.2	608.2	562.2	538.1	522.5	505.6	492.9	474.0
65°	754.2	711.8	642.3	570.7	511.6	474.7	457.4	443.4	433.0	419.1	405.9
67.5°	586.7	569.4	521.5	472.1	429.7	396.9	381.9	372.2	359.6	351.3	342.2
70°	483.8	475.5	441.4	408.8	369.1	346.9	333.0	328.8	313.5	305.1	298.9
72.5°	392.6	388.7	369.1	346.4	318.5	299.0	286.2	281.5	271.8	265.1	261.1
75°	269.0	270.4	266.9	252.4	241.9	229.3	218.3	215.4	208.6	203.0	199.5
77.5°	170.1	177.3	177.5	176.8	172.6	165.1	160.4	158.4	151.5	149.5	148.6
80°	116.8	124.4	131.3	130.6	129.3	127.2	123.8	121.6	118.2	116.1	114.7
82.5°	77.8	85.0	90.8	94.5	94.3	92.2	89.8	88.8	88.1	86.6	86.3
85°	36.8	38.3	40.3	45.2	48.7	49.3	48.7	48.0	45.8	46.5	47.3
87.5°	15.8	15.4	15.6	15.2	14.3	16.6	17.9	18.0	17.3	16.6	16.0
90°	14.9	13.1	11.3	9.4	7.3	5.3	3.2	1.2	3.2	5.3	7.3
92.5°	40.0	37.8	35.6	33.7	32.3	30.9	29.4	28.0	29.4	30.9	32.3
95°	83.9	81.3	78.8	77.2	76.7	76.2	75.7	75.2	75.7	76.2	76.7
97.5°	134.7	131.2	127.6	125.7	125.6	125.4	125.1	124.9	125.1	125.4	125.6
100°	170.3	166.9	163.6	161.9	161.9	161.9	161.9	161.9	161.9	161.9	161.9
102.5°	210.6	208.9	207.2	205.8	204.8	203.8	202.8	201.7	202.8	203.8	204.8
105°	273.4	271.8	270.3	268.9	267.6	266.3	265.0	263.8	265.0	266.3	267.6
107.5°	340.9	339.7	338.6	337.3	336.1	334.7	333.5	332.2	333.5	334.7	336.1
110°	387.1	386.4	385.6	384.5	383.3	382.0	380.7	379.4	380.7	382.0	383.3



TEST NUMBER: P333733-940

CATALOG NUMBER: S125RDIW-S1270D1340U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	432.9	431.9	431.1	430.2	429.5	428.8	428.2	427.5	428.2	428.8	429.5
115°	504.4	503.9	503.5	502.7	501.6	500.6	499.5	498.6	499.5	500.6	501.6
117.5°	573.0	572.6	572.1	571.7	571.1	570.7	570.2	569.8	570.2	570.7	571.1
120°	620.6	620.4	620.1	619.4	618.0	616.8	615.5	614.2	615.5	616.8	618.0
122.5°	666.1	665.4	664.8	664.1	663.7	663.3	662.8	662.4	662.8	663.3	663.7
125°	735.1	734.9	734.6	733.7	732.2	730.7	729.1	727.5	729.1	730.7	732.2
127.5°	801.6	801.4	801.0	800.5	799.6	798.7	797.8	796.9	797.8	798.7	799.6
130°	845.7	845.2	844.6	843.7	842.5	841.2	839.9	838.6	839.9	841.2	842.5
132.5°	889.5	889.6	889.7	888.7	886.5	884.5	882.3	880.2	882.3	884.5	886.5
135°	953.8	953.5	953.2	952.3	950.8	949.2	947.7	946.2	947.7	949.2	950.8
137.5°	1016.3	1015.7	1015.1	1014.1	1012.6	1011.2	1009.7	1008.2	1009.7	1011.2	1012.6
140°	1055.7	1054.9	1054.1	1053.1	1051.9	1050.5	1049.3	1047.9	1049.3	1050.5	1051.9
142.5°	1095.0	1094.0	1093.1	1092.1	1091.0	1089.9	1088.9	1087.8	1088.9	1089.9	1091.0
145°	1152.8	1152.1	1151.3	1150.4	1149.3	1148.3	1147.3	1146.3	1147.3	1148.3	1149.3
147.5°	1204.5	1203.9	1203.3	1202.7	1202.1	1201.6	1201.0	1200.4	1201.0	1201.6	1202.1
150°	1238.0	1236.9	1235.8	1235.5	1235.7	1236.0	1236.3	1236.5	1236.3	1236.0	1235.7
152.5°	1268.7	1268.4	1267.9	1267.6	1267.2	1266.9	1266.5	1266.1	1266.5	1266.9	1267.2
155°	1312.3	1312.1	1311.8	1311.7	1311.7	1311.7	1311.7	1311.7	1311.7	1311.7	1311.7
157.5°	1350.5	1350.2	1350.0	1350.1	1350.7	1351.3	1351.8	1352.4	1351.8	1351.3	1350.7
160°	1373.7	1373.4	1373.1	1373.4	1374.1	1374.9	1375.7	1376.4	1375.7	1374.9	1374.1
162.5°	1395.3	1395.3	1395.3	1395.5	1396.1	1396.6	1397.2	1397.8	1397.2	1396.6	1396.1
165°	1424.5	1424.2	1424.1	1424.2	1424.7	1425.1	1425.7	1426.2	1425.7	1425.1	1424.7
167.5°	1445.6	1445.6	1445.6	1446.2	1447.2	1448.2	1449.2	1450.3	1449.2	1448.2	1447.2
170°	1458.6	1458.6	1458.6	1459.1	1460.2	1461.2	1462.2	1463.2	1462.2	1461.2	1460.2
172.5°	1467.8	1467.8	1467.8	1468.4	1469.4	1470.4	1471.4	1472.5	1471.4	1470.4	1469.4
175°	1478.3	1478.3	1478.3	1478.8	1479.8	1480.9	1481.8	1482.9	1481.8	1480.9	1479.8
177.5°	1484.0	1484.2	1484.4	1484.9	1485.8	1486.6	1487.4	1488.2	1487.4	1486.6	1485.8
180°	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4



TEST NUMBER: P333733-940

CATALOG NUMBER: S125RDIW-S1270D1340U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1664.9	1657.2	1651.5	1640.4	1632.6	1629.3	1623.2	1621.5	1627.6	1623.2	1622.6
5°	1615.4	1595.3	1579.3	1563.3	1545.9	1534.8	1518.1	1515.3	1511.2	1504.9	1503.5
7.5°	1556.0	1529.8	1509.2	1482.8	1459.8	1441.4	1420.5	1410.6	1405.2	1397.1	1386.3
10°	1516.0	1484.7	1457.0	1430.5	1402.0	1379.1	1358.3	1342.2	1331.8	1322.1	1317.9
12.5°	1476.5	1444.7	1409.1	1377.2	1345.3	1319.6	1296.5	1286.1	1274.5	1263.1	1253.4
15°	1415.2	1372.8	1333.9	1297.1	1270.0	1242.2	1219.9	1204.6	1187.2	1182.4	1163.6
17.5°	1350.1	1308.6	1263.0	1224.2	1192.8	1162.2	1137.7	1120.3	1107.3	1089.4	1080.8
20°	1309.6	1260.3	1215.8	1180.3	1145.5	1109.4	1084.3	1069.8	1057.2	1042.7	1035.7
22.5°	1266.2	1218.0	1172.3	1130.8	1095.5	1059.9	1042.1	1027.0	1012.7	999.3	990.1
25°	1202.6	1153.9	1105.9	1062.8	1026.0	1000.2	979.4	962.0	954.4	941.2	931.4
27.5°	1139.5	1087.8	1038.0	995.1	966.2	940.8	923.6	909.9	896.1	884.6	876.1
30°	1098.9	1046.2	991.9	957.9	927.3	902.9	884.1	870.9	860.5	850.1	843.8
32.5°	1058.4	1003.9	955.7	918.9	890.0	869.0	849.7	837.0	826.1	814.5	807.2
35°	993.3	937.7	898.8	862.6	834.1	814.7	801.5	783.4	774.4	766.0	758.3
37.5°	932.8	881.1	839.0	807.3	782.6	763.2	746.1	736.4	725.2	717.7	711.4
40°	888.3	841.1	802.8	769.5	751.4	729.9	713.9	701.3	693.0	683.3	676.4
42.5°	848.3	804.4	767.2	737.3	714.7	696.5	681.1	668.5	658.0	651.0	645.2
45°	791.8	748.0	711.8	683.9	663.2	645.8	629.7	623.5	609.6	601.3	598.5
47.5°	733.2	694.0	659.1	633.5	612.1	595.7	580.7	567.9	560.3	552.1	547.6
50°	693.8	656.2	623.5	598.5	577.7	559.5	545.6	537.3	526.9	519.2	513.7
52.5°	654.2	619.5	586.8	562.8	544.8	526.7	511.2	502.8	492.9	488.1	484.2
55°	597.8	561.0	533.2	509.5	490.7	474.0	459.5	451.1	444.9	440.0	438.6
57.5°	533.9	504.6	478.8	457.5	438.0	422.3	409.6	401.6	396.1	395.4	391.2
60°	492.1	465.7	442.1	419.1	402.4	387.9	376.7	367.7	362.1	361.4	360.1
62.5°	450.4	425.1	403.1	383.0	368.0	353.9	343.4	333.2	329.9	326.5	323.3
65°	388.5	365.6	347.6	331.5	315.6	303.7	293.4	287.0	279.5	275.3	267.6
67.5°	327.8	310.0	292.7	279.2	266.6	255.4	246.7	237.5	232.3	229.0	223.4
70°	287.8	273.8	256.5	241.9	232.2	223.1	216.2	205.7	202.2	199.5	196.7
72.5°	249.9	237.7	223.1	211.3	201.6	193.1	185.0	180.1	176.7	173.9	172.3
75°	196.7	184.9	172.4	164.1	157.1	150.2	146.0	142.5	141.1	140.4	137.6
77.5°	144.5	138.2	128.1	121.5	116.9	114.1	110.4	108.6	108.4	105.4	104.4
80°	110.5	107.0	98.7	95.9	92.5	89.7	87.6	84.1	80.6	79.3	77.1
82.5°	82.1	78.6	75.3	70.9	67.9	66.3	64.2	63.0	63.4	61.4	60.5
85°	43.8	40.3	39.0	38.3	36.8	38.3	37.5	36.8	36.1	35.5	36.1
87.5°	15.8	16.1	16.0	17.5	16.1	17.0	17.3	17.0	17.3	17.5	17.2
90°	9.4	11.3	13.1	14.9	16.7	18.5	19.8	21.0	22.4	23.6	24.7
92.5°	33.7	35.6	37.8	40.0	42.2	44.4	46.1	47.8	49.5	51.2	52.3
95°	77.2	78.8	81.3	83.9	86.5	89.1	90.9	92.6	94.4	96.3	97.4
97.5°	125.7	127.6	131.2	134.7	138.3	141.8	143.5	145.2	146.9	148.6	149.6
100°	161.9	163.6	166.9	170.3	173.6	177.0	179.3	181.6	183.9	186.2	187.6
102.5°	205.8	207.2	208.9	210.6	212.3	214.0	216.5	219.0	221.5	224.1	225.7
105°	268.9	270.3	271.8	273.4	274.9	276.4	278.0	279.6	281.1	282.6	283.7
107.5°	337.3	338.6	339.7	340.9	342.1	343.3	344.1	344.8	345.6	346.4	346.8
110°	384.5	385.6	386.4	387.1	387.9	388.6	389.4	390.2	390.9	391.7	392.0



TEST NUMBER: P333733-940

CATALOG NUMBER: S125RDIW-S1270D1340U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	430.2	431.1	431.9	432.9	433.9	434.9	435.2	435.6	436.0	436.3	436.3
115°	502.7	503.5	503.9	504.4	505.0	505.5	505.2	505.0	504.7	504.4	504.2
117.5°	571.7	572.1	572.6	573.0	573.5	574.0	574.2	574.4	574.5	574.8	574.4
120°	619.4	620.1	620.4	620.6	620.9	621.2	621.2	621.2	621.2	621.2	620.6
122.5°	664.1	664.8	665.4	666.1	666.7	667.4	667.2	667.0	666.8	666.6	666.1
125°	733.7	734.6	734.9	735.1	735.4	735.7	735.1	734.6	734.1	733.6	733.3
127.5°	800.5	801.0	801.4	801.6	802.0	802.3	802.0	801.7	801.5	801.3	800.8
130°	843.7	844.6	845.2	845.7	846.1	846.7	846.4	846.1	846.0	845.7	845.3
132.5°	888.7	889.7	889.6	889.5	889.4	889.3	889.0	888.8	888.5	888.2	887.8
135°	952.3	953.2	953.5	953.8	954.0	954.3	954.3	954.3	954.3	954.3	953.8
137.5°	1014.1	1015.1	1015.7	1016.3	1016.9	1017.4	1017.7	1018.1	1018.3	1018.7	1018.2
140°	1053.1	1054.1	1054.9	1055.7	1056.4	1057.2	1057.7	1058.3	1058.7	1059.3	1058.9
142.5°	1092.1	1093.1	1094.0	1095.0	1096.0	1097.0	1097.3	1097.6	1098.0	1098.2	1097.8
145°	1150.4	1151.3	1152.1	1152.8	1153.6	1154.4	1154.4	1154.4	1154.4	1154.4	1154.0
147.5°	1202.7	1203.3	1203.9	1204.5	1205.1	1205.8	1206.4	1206.9	1207.6	1208.2	1207.6
150°	1235.5	1235.8	1236.9	1238.0	1238.9	1240.0	1240.0	1240.0	1240.0	1240.0	1239.7
152.5°	1267.6	1267.9	1268.4	1268.7	1269.2	1269.6	1270.2	1270.8	1271.4	1272.0	1271.9
155°	1311.7	1311.8	1312.1	1312.3	1312.6	1312.9	1313.8	1314.9	1315.9	1317.0	1316.8
157.5°	1350.1	1350.0	1350.2	1350.5	1350.8	1351.0	1352.0	1353.1	1354.1	1355.1	1354.8
160°	1373.4	1373.1	1373.4	1373.7	1373.9	1374.1	1375.2	1376.2	1377.2	1378.2	1378.1
162.5°	1395.5	1395.3	1395.3	1395.3	1395.3	1395.4	1396.7	1397.9	1399.1	1400.3	1400.3
165°	1424.2	1424.1	1424.2	1424.5	1424.8	1425.0	1426.1	1427.1	1428.2	1429.1	1428.9
167.5°	1446.2	1445.6	1445.6	1445.6	1445.6	1445.6	1447.2	1448.8	1450.3	1451.8	1451.8
170°	1459.1	1458.6	1458.6	1458.6	1458.6	1458.6	1460.2	1461.7	1463.2	1464.7	1464.6
172.5°	1468.4	1467.8	1467.8	1467.8	1467.8	1467.8	1469.4	1471.0	1472.5	1474.0	1474.0
175°	1478.8	1478.3	1478.3	1478.3	1478.3	1478.3	1479.8	1481.3	1482.9	1484.4	1484.3
177.5°	1484.9	1484.4	1484.2	1484.0	1483.8	1483.5	1484.8	1486.0	1487.3	1488.5	1488.4
180°	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4



TEST NUMBER: P333733-940

CATALOG NUMBER: S125RDIW-S1270D1340U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1622.1	1616.0	1614.3	1616.5	1614.3	1616.0	1622.1	1622.6	1623.2	1627.6	1621.5
5°	1496.6	1489.6	1493.1	1491.7	1493.1	1489.6	1496.6	1503.5	1504.9	1511.2	1515.3
7.5°	1386.2	1377.5	1368.3	1371.3	1368.3	1377.5	1386.2	1386.3	1397.1	1405.2	1410.6
10°	1308.9	1301.9	1297.7	1301.2	1297.7	1301.9	1308.9	1317.9	1322.1	1331.8	1342.2
12.5°	1243.8	1239.7	1236.0	1234.5	1236.0	1239.7	1243.8	1253.4	1263.1	1274.5	1286.1
15°	1155.2	1146.9	1143.4	1134.4	1143.4	1146.9	1155.2	1163.6	1182.4	1187.2	1204.6
17.5°	1073.6	1070.9	1061.8	1057.9	1061.8	1070.9	1073.6	1080.8	1089.4	1107.3	1120.3
20°	1025.3	1022.5	1013.4	1019.0	1013.4	1022.5	1025.3	1035.7	1042.7	1057.2	1069.8
22.5°	985.3	979.1	976.2	974.6	976.2	979.1	985.3	990.1	999.3	1012.7	1027.0
25°	928.6	919.6	916.1	912.0	916.1	919.6	928.6	931.4	941.2	954.4	962.0
27.5°	872.2	867.4	862.7	861.7	862.7	867.4	872.2	876.1	884.6	896.1	909.9
30°	835.5	830.6	827.2	827.2	827.2	830.6	835.5	843.8	850.1	860.5	870.9
32.5°	802.7	799.0	795.5	795.0	795.5	799.0	802.7	807.2	814.5	826.1	837.0
35°	754.9	749.3	748.0	743.8	748.0	749.3	754.9	758.3	766.0	774.4	783.4
37.5°	705.3	700.6	700.5	700.1	700.5	700.6	705.3	711.4	717.7	725.2	736.4
40°	673.5	670.0	669.4	664.5	669.4	670.0	673.5	676.4	683.3	693.0	701.3
42.5°	639.6	637.8	635.4	633.4	635.4	637.8	639.6	645.2	651.0	658.0	668.5
45°	593.6	588.7	588.7	585.2	588.7	588.7	593.6	598.5	601.3	609.6	623.5
47.5°	546.1	542.3	542.7	539.1	542.7	542.3	546.1	547.6	552.1	560.3	567.9
50°	514.3	512.3	511.6	510.2	511.6	512.3	514.3	513.7	519.2	526.9	537.3
52.5°	482.7	481.7	484.4	481.3	484.4	481.7	482.7	484.2	488.1	492.9	502.8
55°	440.0	437.9	442.1	437.9	442.1	437.9	440.0	438.6	440.0	444.9	451.1
57.5°	390.9	389.0	392.7	390.7	392.7	389.0	390.9	391.2	395.4	396.1	401.6
60°	358.6	354.5	356.6	357.3	356.6	354.5	358.6	360.1	361.4	362.1	367.7
62.5°	320.3	317.8	319.3	316.1	319.3	317.8	320.3	323.3	326.5	329.9	333.2
65°	266.3	264.1	261.4	259.9	261.4	264.1	266.3	267.6	275.3	279.5	287.0
67.5°	223.6	218.6	218.6	219.6	218.6	218.6	223.6	223.4	229.0	232.3	237.5
70°	192.5	192.5	191.8	191.8	191.8	192.5	192.5	196.7	199.5	202.2	205.7
72.5°	170.9	170.3	169.1	168.5	169.1	170.3	170.9	172.3	173.9	176.7	180.1
75°	137.6	138.3	137.0	136.3	137.0	138.3	137.6	137.6	140.4	141.1	142.5
77.5°	101.7	98.7	100.2	98.7	100.2	98.7	101.7	104.4	105.4	108.4	108.6
80°	77.1	76.4	78.6	76.4	78.6	76.4	77.1	77.1	79.3	80.6	84.1
82.5°	61.0	60.4	61.3	59.7	61.3	60.4	61.0	60.5	61.4	63.4	63.0
85°	36.8	36.1	35.5	36.1	35.5	36.1	36.8	36.1	35.5	36.1	36.8
87.5°	17.9	17.5	17.7	17.7	17.7	17.5	17.9	17.2	17.5	17.3	17.0
90°	25.4	26.2	27.0	27.7	27.0	26.2	25.4	24.7	23.6	22.4	21.0
92.5°	52.9	53.5	54.0	54.6	54.0	53.5	52.9	52.3	51.2	49.5	47.8
95°	97.9	98.4	99.0	99.5	99.0	98.4	97.9	97.4	96.3	94.4	92.6
97.5°	149.9	150.3	150.5	150.9	150.5	150.3	149.9	149.6	148.6	146.9	145.2
100°	188.2	188.7	189.2	189.7	189.2	188.7	188.2	187.6	186.2	183.9	181.6
102.5°	226.4	227.1	227.8	228.5	227.8	227.1	226.4	225.7	224.1	221.5	219.0
105°	284.5	285.3	286.1	286.9	286.1	285.3	284.5	283.7	282.6	281.1	279.6
107.5°	346.7	346.6	346.6	346.5	346.6	346.6	346.7	346.8	346.4	345.6	344.8
110°	391.7	391.5	391.2	390.9	391.2	391.5	391.7	392.0	391.7	390.9	390.2



TEST NUMBER: P333733-940

CATALOG NUMBER: S125RDIW-S1270D1340U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	435.9	435.4	434.9	434.4	434.9	435.4	435.9	436.3	436.3	436.0	435.6
115°	503.9	503.6	503.5	503.2	503.5	503.6	503.9	504.2	504.4	504.7	505.0
117.5°	573.4	572.3	571.3	570.2	571.3	572.3	573.4	574.4	574.8	574.5	574.4
120°	619.6	618.6	617.5	616.5	617.5	618.6	619.6	620.6	621.2	621.2	621.2
122.5°	665.2	664.4	663.6	662.8	663.6	664.4	665.2	666.1	666.6	666.8	667.0
125°	733.0	732.7	732.5	732.2	732.5	732.7	733.0	733.3	733.6	734.1	734.6
127.5°	800.4	799.9	799.3	798.8	799.3	799.9	800.4	800.8	801.3	801.5	801.7
130°	844.8	844.3	843.7	843.2	843.7	844.3	844.8	845.3	845.7	846.0	846.1
132.5°	887.1	886.3	885.6	884.8	885.6	886.3	887.1	887.8	888.2	888.5	888.8
135°	952.7	951.7	950.7	949.7	950.7	951.7	952.7	953.8	954.3	954.3	954.3
137.5°	1016.9	1015.6	1014.3	1013.1	1014.3	1015.6	1016.9	1018.2	1018.7	1018.3	1018.1
140°	1057.6	1056.3	1055.1	1053.7	1055.1	1056.3	1057.6	1058.9	1059.3	1058.7	1058.3
142.5°	1096.4	1095.2	1093.9	1092.6	1093.9	1095.2	1096.4	1097.8	1098.2	1098.0	1097.6
145°	1153.2	1152.4	1151.6	1150.9	1151.6	1152.4	1153.2	1154.0	1154.4	1154.4	1154.4
147.5°	1205.9	1204.2	1202.4	1200.7	1202.4	1204.2	1205.9	1207.6	1208.2	1207.6	1206.9
150°	1239.2	1238.7	1238.1	1237.7	1238.1	1238.7	1239.2	1239.7	1240.0	1240.0	1240.0
152.5°	1271.0	1270.1	1269.1	1268.2	1269.1	1270.1	1271.0	1271.9	1272.0	1271.4	1270.8
155°	1315.5	1314.3	1313.0	1311.7	1313.0	1314.3	1315.5	1316.8	1317.0	1315.9	1314.9
157.5°	1353.1	1351.4	1349.7	1348.0	1349.7	1351.4	1353.1	1354.8	1355.1	1354.1	1353.1
160°	1376.9	1375.6	1374.3	1373.0	1374.3	1375.6	1376.9	1378.1	1378.2	1377.2	1376.2
162.5°	1398.7	1397.2	1395.8	1394.3	1395.8	1397.2	1398.7	1400.3	1400.3	1399.1	1397.9
165°	1427.4	1425.8	1424.2	1422.7	1424.2	1425.8	1427.4	1428.9	1429.1	1428.2	1427.1
167.5°	1450.2	1448.6	1447.0	1445.4	1447.0	1448.6	1450.2	1451.8	1451.8	1450.3	1448.8
170°	1462.9	1461.1	1459.2	1457.4	1459.2	1461.1	1462.9	1464.6	1464.7	1463.2	1461.7
172.5°	1472.4	1470.8	1469.2	1467.6	1469.2	1470.8	1472.4	1474.0	1474.0	1472.5	1471.0
175°	1482.5	1480.7	1478.9	1477.1	1478.9	1480.7	1482.5	1484.3	1484.4	1482.9	1481.3
177.5°	1486.9	1485.5	1484.1	1482.6	1484.1	1485.5	1486.9	1488.4	1488.5	1487.3	1486.0
180°	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4



TEST NUMBER: P333733-940

CATALOG NUMBER: S125RDIW-S1270D1340U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1623.2	1629.3	1632.6	1640.4	1651.5	1657.2	1664.9	1670.4	1678.3	1687.7	1695.5
5°	1518.1	1534.8	1545.9	1563.3	1579.3	1595.3	1615.4	1630.0	1649.5	1671.7	1689.1
7.5°	1420.5	1441.4	1459.8	1482.8	1509.2	1529.8	1556.0	1582.9	1613.3	1644.8	1674.6
10°	1358.3	1379.1	1402.0	1430.5	1457.0	1484.7	1516.0	1547.3	1585.6	1621.0	1661.3
12.5°	1296.5	1319.6	1345.3	1377.2	1409.1	1444.7	1476.5	1511.7	1552.7	1598.7	1641.8
15°	1219.9	1242.2	1270.0	1297.1	1333.9	1372.8	1415.2	1461.8	1507.7	1559.1	1612.7
17.5°	1137.7	1162.2	1192.8	1224.2	1263.0	1308.6	1350.1	1401.1	1452.8	1512.7	1575.7
20°	1084.3	1109.4	1145.5	1180.3	1215.8	1260.3	1309.6	1361.7	1416.6	1479.9	1550.1
22.5°	1042.1	1059.9	1095.5	1130.8	1172.3	1218.0	1266.2	1320.5	1380.5	1445.9	1519.5
25°	979.4	1000.2	1026.0	1062.8	1105.9	1153.9	1202.6	1260.3	1325.5	1392.3	1470.8
27.5°	923.6	940.8	966.2	995.1	1038.0	1087.8	1139.5	1199.7	1266.8	1334.7	1417.3
30°	884.1	902.9	927.3	957.9	991.9	1046.2	1098.9	1158.1	1226.2	1296.4	1381.2
32.5°	849.7	869.0	890.0	918.9	955.7	1003.9	1058.4	1116.3	1185.5	1258.0	1340.6
35°	801.5	814.7	834.1	862.6	898.8	937.7	993.3	1054.4	1121.9	1196.9	1279.7
37.5°	746.1	763.2	782.6	807.3	839.0	881.1	932.8	994.7	1057.2	1129.1	1204.6
40°	713.9	729.9	751.4	769.5	802.8	841.1	888.3	953.0	1015.6	1083.0	1151.8
42.5°	681.1	696.5	714.7	737.3	767.2	804.4	848.3	908.5	975.5	1039.0	1096.7
45°	629.7	645.8	663.2	683.9	711.8	748.0	791.8	846.6	905.0	963.4	1007.2
47.5°	580.7	595.7	612.1	633.5	659.1	694.0	733.2	781.7	838.4	888.1	919.4
50°	545.6	559.5	577.7	598.5	623.5	656.2	693.8	741.6	788.9	834.1	862.6
52.5°	511.2	526.7	544.8	562.8	586.8	619.5	654.2	695.5	740.6	777.4	800.9
55°	459.5	474.0	490.7	509.5	533.2	561.0	597.8	630.4	665.9	697.2	711.1
57.5°	409.6	422.3	438.0	457.5	478.8	504.6	533.9	565.3	590.3	612.4	628.1
60°	376.7	387.9	402.4	419.1	442.1	465.7	492.1	521.3	540.8	559.5	574.2
62.5°	343.4	353.9	368.0	383.0	403.1	425.1	450.4	474.0	492.9	505.6	522.5
65°	293.4	303.7	315.6	331.5	347.6	365.6	388.5	405.9	419.1	433.0	443.4
67.5°	246.7	255.4	266.6	279.2	292.7	310.0	327.8	342.2	351.3	359.6	372.2
70°	216.2	223.1	232.2	241.9	256.5	273.8	287.8	298.9	305.1	313.5	328.8
72.5°	185.0	193.1	201.6	211.3	223.1	237.7	249.9	261.1	265.1	271.8	281.5
75°	146.0	150.2	157.1	164.1	172.4	184.9	196.7	199.5	203.0	208.6	215.4
77.5°	110.4	114.1	116.9	121.5	128.1	138.2	144.5	148.6	149.5	151.5	158.4
80°	87.6	89.7	92.5	95.9	98.7	107.0	110.5	114.7	116.1	118.2	121.6
82.5°	64.2	66.3	67.9	70.9	75.3	78.6	82.1	86.3	86.6	88.1	88.8
85°	37.5	38.3	36.8	38.3	39.0	40.3	43.8	47.3	46.5	45.8	48.0
87.5°	17.3	17.0	16.1	17.5	16.0	16.1	15.8	16.0	16.6	17.3	18.0
90°	19.8	18.5	16.7	14.9	13.1	11.3	9.4	7.3	5.3	3.2	1.2
92.5°	46.1	44.4	42.2	40.0	37.8	35.6	33.7	32.3	30.9	29.4	28.0
95°	90.9	89.1	86.5	83.9	81.3	78.8	77.2	76.7	76.2	75.7	75.2
97.5°	143.5	141.8	138.3	134.7	131.2	127.6	125.7	125.6	125.4	125.1	124.9
100°	179.3	177.0	173.6	170.3	166.9	163.6	161.9	161.9	161.9	161.9	161.9
102.5°	216.5	214.0	212.3	210.6	208.9	207.2	205.8	204.8	203.8	202.8	201.7
105°	278.0	276.4	274.9	273.4	271.8	270.3	268.9	267.6	266.3	265.0	263.8
107.5°	344.1	343.3	342.1	340.9	339.7	338.6	337.3	336.1	334.7	333.5	332.2
110°	389.4	388.6	387.9	387.1	386.4	385.6	384.5	383.3	382.0	380.7	379.4



TEST NUMBER: P333733-940

CATALOG NUMBER: S125RDIW-S1270D1340U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	435.2	434.9	433.9	432.9	431.9	431.1	430.2	429.5	428.8	428.2	427.5
115°	505.2	505.5	505.0	504.4	503.9	503.5	502.7	501.6	500.6	499.5	498.6
117.5°	574.2	574.0	573.5	573.0	572.6	572.1	571.7	571.1	570.7	570.2	569.8
120°	621.2	621.2	620.9	620.6	620.4	620.1	619.4	618.0	616.8	615.5	614.2
122.5°	667.2	667.4	666.7	666.1	665.4	664.8	664.1	663.7	663.3	662.8	662.4
125°	735.1	735.7	735.4	735.1	734.9	734.6	733.7	732.2	730.7	729.1	727.5
127.5°	802.0	802.3	802.0	801.6	801.4	801.0	800.5	799.6	798.7	797.8	796.9
130°	846.4	846.7	846.1	845.7	845.2	844.6	843.7	842.5	841.2	839.9	838.6
132.5°	889.0	889.3	889.4	889.5	889.6	889.7	888.7	886.5	884.5	882.3	880.2
135°	954.3	954.3	954.0	953.8	953.5	953.2	952.3	950.8	949.2	947.7	946.2
137.5°	1017.7	1017.4	1016.9	1016.3	1015.7	1015.1	1014.1	1012.6	1011.2	1009.7	1008.2
140°	1057.7	1057.2	1056.4	1055.7	1054.9	1054.1	1053.1	1051.9	1050.5	1049.3	1047.9
142.5°	1097.3	1097.0	1096.0	1095.0	1094.0	1093.1	1092.1	1091.0	1089.9	1088.9	1087.8
145°	1154.4	1154.4	1153.6	1152.8	1152.1	1151.3	1150.4	1149.3	1148.3	1147.3	1146.3
147.5°	1206.4	1205.8	1205.1	1204.5	1203.9	1203.3	1202.7	1202.1	1201.6	1201.0	1200.4
150°	1240.0	1240.0	1238.9	1238.0	1236.9	1235.8	1235.5	1235.7	1236.0	1236.3	1236.5
152.5°	1270.2	1269.6	1269.2	1268.7	1268.4	1267.9	1267.6	1267.2	1266.9	1266.5	1266.1
155°	1313.8	1312.9	1312.6	1312.3	1312.1	1311.8	1311.7	1311.7	1311.7	1311.7	1311.7
157.5°	1352.0	1351.0	1350.8	1350.5	1350.2	1350.0	1350.1	1350.7	1351.3	1351.8	1352.4
160°	1375.2	1374.1	1373.9	1373.7	1373.4	1373.1	1373.4	1374.1	1374.9	1375.7	1376.4
162.5°	1396.7	1395.4	1395.3	1395.3	1395.3	1395.3	1395.5	1396.1	1396.6	1397.2	1397.8
165°	1426.1	1425.0	1424.8	1424.5	1424.2	1424.1	1424.2	1424.7	1425.1	1425.7	1426.2
167.5°	1447.2	1445.6	1445.6	1445.6	1445.6	1445.6	1446.2	1447.2	1448.2	1449.2	1450.3
170°	1460.2	1458.6	1458.6	1458.6	1458.6	1458.6	1459.1	1460.2	1461.2	1462.2	1463.2
172.5°	1469.4	1467.8	1467.8	1467.8	1467.8	1467.8	1468.4	1469.4	1470.4	1471.4	1472.5
175°	1479.8	1478.3	1478.3	1478.3	1478.3	1478.3	1478.8	1479.8	1480.9	1481.8	1482.9
177.5°	1484.8	1483.5	1483.8	1484.0	1484.2	1484.4	1484.9	1485.8	1486.6	1487.4	1488.2
180°	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4



TEST NUMBER: P333733-940

CATALOG NUMBER: S125RDIW-S1270D1340U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1701.6	1706.6	1713.9	1722.2	1728.8	1736.1	1740.0	1740.0	1743.3	1750.5	1760.0
5°	1706.5	1724.6	1742.0	1764.2	1781.5	1801.7	1816.9	1831.6	1844.8	1861.4	1878.8
7.5°	1705.0	1735.1	1766.4	1801.4	1840.0	1870.8	1902.4	1927.1	1951.6	1983.5	2008.7
10°	1699.5	1738.5	1780.8	1825.3	1874.0	1916.4	1954.6	1989.4	2022.8	2057.5	2088.7
12.5°	1689.5	1739.0	1790.8	1844.2	1905.7	1954.2	2003.6	2040.5	2079.5	2117.5	2156.1
15°	1674.5	1732.9	1795.5	1869.8	1944.9	1999.1	2047.7	2095.7	2131.9	2175.0	2211.8
17.5°	1643.5	1718.7	1797.4	1878.7	1950.9	2013.8	2064.8	2110.5	2148.9	2196.4	2246.4
20°	1625.1	1706.5	1788.5	1875.4	1944.2	2008.8	2058.2	2105.4	2153.4	2215.3	2276.4
22.5°	1599.6	1686.5	1773.4	1855.9	1928.6	1991.0	2042.1	2099.9	2162.8	2233.1	2307.0
25°	1559.1	1648.8	1735.0	1813.5	1884.5	1948.4	2017.9	2095.7	2172.2	2264.7	2371.0
27.5°	1507.8	1594.3	1671.2	1754.2	1824.6	1905.9	1992.7	2077.1	2187.4	2314.5	2447.3
30°	1469.5	1551.5	1624.4	1703.0	1782.9	1872.6	1969.9	2069.3	2200.7	2350.1	2507.9
32.5°	1425.0	1499.2	1571.6	1647.3	1739.5	1838.1	1941.5	2063.2	2220.2	2390.1	2553.5
35°	1347.8	1414.5	1484.7	1568.9	1666.9	1773.9	1905.9	2054.1	2243.8	2426.6	2573.3
37.5°	1266.9	1319.6	1390.1	1478.7	1585.6	1709.4	1859.2	2039.2	2234.1	2398.1	2460.5
40°	1204.6	1253.9	1328.3	1421.5	1527.1	1662.7	1830.9	2015.8	2211.8	2325.8	2320.9
42.5°	1142.9	1192.8	1264.4	1358.1	1468.2	1619.9	1793.1	1985.2	2150.6	2194.1	2103.5
45°	1048.2	1094.8	1165.0	1259.5	1377.7	1536.9	1719.0	1903.2	2008.8	1938.7	1759.3
47.5°	951.7	996.9	1062.1	1154.7	1283.7	1450.3	1622.5	1773.6	1788.5	1637.6	1422.5
50°	888.3	930.8	992.6	1091.3	1216.4	1379.1	1545.2	1664.1	1627.2	1443.1	1221.3
52.5°	826.6	867.4	925.3	1018.4	1146.4	1305.6	1454.0	1547.3	1462.0	1266.2	1066.7
55°	735.4	774.4	832.8	918.2	1034.3	1180.3	1310.3	1344.3	1219.2	1021.8	860.5
57.5°	648.8	677.3	735.0	810.7	922.6	1051.2	1144.4	1138.3	1000.2	822.4	706.8
60°	591.6	617.2	672.2	741.6	848.0	963.4	1028.8	1000.9	861.2	714.5	603.3
62.5°	538.1	562.2	608.2	672.2	763.5	863.9	911.4	873.1	741.1	612.2	523.8
65°	457.4	474.7	511.6	570.7	642.3	711.8	754.2	697.9	581.1	483.8	417.1
67.5°	381.9	396.9	429.7	472.1	521.5	569.4	586.7	533.9	443.1	377.5	330.5
70°	333.0	346.9	369.1	408.8	441.4	475.5	483.8	436.5	360.8	310.7	281.5
72.5°	286.2	299.0	318.5	346.4	369.1	388.7	392.6	348.7	290.7	256.2	233.7
75°	218.3	229.3	241.9	252.4	266.9	270.4	269.0	235.0	203.7	180.7	168.2
77.5°	160.4	165.1	172.6	176.8	177.5	177.3	170.1	148.6	132.5	123.1	117.9
80°	123.8	127.2	129.3	130.6	131.3	124.4	116.8	103.5	98.0	92.5	86.2
82.5°	89.8	92.2	94.3	94.5	90.8	85.0	77.8	71.3	67.4	64.6	62.2
85°	48.7	49.3	48.7	45.2	40.3	38.3	36.8	35.5	34.8	34.1	34.1
87.5°	17.9	16.6	14.3	15.2	15.6	15.4	15.8	15.6	15.3	15.6	15.9
90°	3.2	5.3	7.3	9.4	11.3	13.1	14.9	16.7	18.5	19.8	21.0
92.5°	29.4	30.9	32.3	33.7	35.6	37.8	40.0	42.2	44.4	46.1	47.8
95°	75.7	76.2	76.7	77.2	78.8	81.3	83.9	86.5	89.1	90.9	92.6
97.5°	125.1	125.4	125.6	125.7	127.6	131.2	134.7	138.3	141.8	143.5	145.2
100°	161.9	161.9	161.9	161.9	163.6	166.9	170.3	173.6	177.0	179.3	181.6
102.5°	202.8	203.8	204.8	205.8	207.2	208.9	210.6	212.3	214.0	216.5	219.0
105°	265.0	266.3	267.6	268.9	270.3	271.8	273.4	274.9	276.4	278.0	279.6
107.5°	333.5	334.7	336.1	337.3	338.6	339.7	340.9	342.1	343.3	344.1	344.8
110°	380.7	382.0	383.3	384.5	385.6	386.4	387.1	387.9	388.6	389.4	390.2



TEST NUMBER: P333733-940

CATALOG NUMBER: S125RDIW-S1270D1340U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	428.2	428.8	429.5	430.2	431.1	431.9	432.9	433.9	434.9	435.2	435.6
115°	499.5	500.6	501.6	502.7	503.5	503.9	504.4	505.0	505.5	505.2	505.0
117.5°	570.2	570.7	571.1	571.7	572.1	572.6	573.0	573.5	574.0	574.2	574.4
120°	615.5	616.8	618.0	619.4	620.1	620.4	620.6	620.9	621.2	621.2	621.2
122.5°	662.8	663.3	663.7	664.1	664.8	665.4	666.1	666.7	667.4	667.2	667.0
125°	729.1	730.7	732.2	733.7	734.6	734.9	735.1	735.4	735.7	735.1	734.6
127.5°	797.8	798.7	799.6	800.5	801.0	801.4	801.6	802.0	802.3	802.0	801.7
130°	839.9	841.2	842.5	843.7	844.6	845.2	845.7	846.1	846.7	846.4	846.1
132.5°	882.3	884.5	886.5	888.7	889.7	889.6	889.5	889.4	889.3	889.0	888.8
135°	947.7	949.2	950.8	952.3	953.2	953.5	953.8	954.0	954.3	954.3	954.3
137.5°	1009.7	1011.2	1012.6	1014.1	1015.1	1015.7	1016.3	1016.9	1017.4	1017.7	1018.1
140°	1049.3	1050.5	1051.9	1053.1	1054.1	1054.9	1055.7	1056.4	1057.2	1057.7	1058.3
142.5°	1088.9	1089.9	1091.0	1092.1	1093.1	1094.0	1095.0	1096.0	1097.0	1097.3	1097.6
145°	1147.3	1148.3	1149.3	1150.4	1151.3	1152.1	1152.8	1153.6	1154.4	1154.4	1154.4
147.5°	1201.0	1201.6	1202.1	1202.7	1203.3	1203.9	1204.5	1205.1	1205.8	1206.4	1206.9
150°	1236.3	1236.0	1235.7	1235.5	1235.8	1236.9	1238.0	1238.9	1240.0	1240.0	1240.0
152.5°	1266.5	1266.9	1267.2	1267.6	1267.9	1268.4	1268.7	1269.2	1269.6	1270.2	1270.8
155°	1311.7	1311.7	1311.7	1311.7	1311.8	1312.1	1312.3	1312.6	1312.9	1313.8	1314.9
157.5°	1351.8	1351.3	1350.7	1350.1	1350.0	1350.2	1350.5	1350.8	1351.0	1352.0	1353.1
160°	1375.7	1374.9	1374.1	1373.4	1373.1	1373.4	1373.7	1373.9	1374.1	1375.2	1376.2
162.5°	1397.2	1396.6	1396.1	1395.5	1395.3	1395.3	1395.3	1395.3	1395.4	1396.7	1397.9
165°	1425.7	1425.1	1424.7	1424.2	1424.1	1424.2	1424.5	1424.8	1425.0	1426.1	1427.1
167.5°	1449.2	1448.2	1447.2	1446.2	1445.6	1445.6	1445.6	1445.6	1445.6	1447.2	1448.8
170°	1462.2	1461.2	1460.2	1459.1	1458.6	1458.6	1458.6	1458.6	1458.6	1460.2	1461.7
172.5°	1471.4	1470.4	1469.4	1468.4	1467.8	1467.8	1467.8	1467.8	1467.8	1469.4	1471.0
175°	1481.8	1480.9	1479.8	1478.8	1478.3	1478.3	1478.3	1478.3	1478.3	1479.8	1481.3
177.5°	1487.4	1486.6	1485.8	1484.9	1484.4	1484.2	1484.0	1483.8	1483.5	1484.8	1486.0
180°	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4



TEST NUMBER: P333733-940

CATALOG NUMBER: S125RDIW-S1270D1340U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1767.2	1767.2	1776.6	1776.1	1782.3	1780.0	1781.1
5°	1899.7	1911.6	1922.0	1928.9	1939.3	1942.1	1940.7
7.5°	2037.0	2063.3	2076.1	2093.6	2096.9	2106.0	2105.1
10°	2122.2	2147.9	2167.3	2182.6	2190.2	2200.0	2200.7
12.5°	2188.9	2210.7	2227.9	2242.1	2251.4	2254.5	2256.3
15°	2241.0	2265.3	2285.5	2305.6	2317.5	2326.5	2331.4
17.5°	2293.6	2331.1	2366.7	2394.1	2410.5	2424.4	2424.2
20°	2334.1	2377.2	2421.7	2453.0	2485.0	2498.8	2501.0
22.5°	2377.5	2443.4	2500.7	2549.2	2591.2	2605.7	2611.1
25°	2467.6	2553.8	2642.0	2710.2	2758.9	2787.3	2791.5
27.5°	2576.4	2693.1	2786.0	2848.8	2889.2	2910.4	2915.0
30°	2653.2	2760.9	2844.4	2891.6	2910.4	2913.1	2902.7
32.5°	2687.7	2768.1	2801.5	2798.7	2761.9	2737.5	2728.1
35°	2645.5	2628.9	2547.5	2450.2	2375.9	2328.6	2316.0
37.5°	2407.5	2263.7	2114.1	1967.0	1888.7	1849.0	1780.6
40°	2172.9	1967.8	1812.1	1688.4	1600.1	1529.2	1512.5
42.5°	1908.2	1696.5	1540.8	1434.9	1364.3	1315.7	1294.6
45°	1533.4	1351.3	1222.7	1141.4	1087.2	1051.7	1035.7
47.5°	1226.5	1085.5	991.8	931.6	890.3	859.4	850.8
50°	1057.9	945.3	866.1	815.4	784.1	760.5	750.7
52.5°	918.9	828.0	767.1	725.2	695.6	680.9	672.9
55°	758.3	679.8	636.1	602.6	585.9	574.2	568.6
57.5°	620.2	563.5	531.5	508.4	492.9	485.4	482.7
60°	542.9	498.4	469.2	451.1	440.7	431.0	428.2
62.5°	474.5	439.4	417.0	401.1	390.7	386.5	384.8
65°	382.3	359.4	342.7	333.0	324.6	323.2	322.5
67.5°	303.9	290.4	281.7	271.5	268.6	263.7	262.8
70°	259.9	250.9	240.5	237.0	233.5	228.7	229.3
72.5°	220.5	211.4	204.4	199.7	198.5	196.4	198.2
75°	161.2	158.5	155.7	152.2	150.9	150.9	150.2
77.5°	115.1	112.7	109.7	107.6	107.2	104.2	105.4
80°	83.4	79.9	78.6	79.3	77.1	76.4	76.4
82.5°	61.7	60.5	59.1	59.2	58.8	58.1	58.7
85°	34.1	33.3	33.3	32.6	32.6	32.0	32.0
87.5°	16.7	17.5	16.6	16.2	16.4	17.0	17.7
90°	22.4	23.6	24.7	25.4	26.2	27.0	27.7
92.5°	49.5	51.2	52.3	52.9	53.5	54.0	54.6
95°	94.4	96.3	97.4	97.9	98.4	99.0	99.5
97.5°	146.9	148.6	149.6	149.9	150.3	150.5	150.9
100°	183.9	186.2	187.6	188.2	188.7	189.2	189.7
102.5°	221.5	224.1	225.7	226.4	227.1	227.8	228.5
105°	281.1	282.6	283.7	284.5	285.3	286.1	286.9
107.5°	345.6	346.4	346.8	346.7	346.6	346.6	346.5
110°	390.9	391.7	392.0	391.7	391.5	391.2	390.9



TEST NUMBER: P333733-940

CATALOG NUMBER: S125RDIW-S1270D1340U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	436.0	436.3	436.3	435.9	435.4	434.9	434.4
115°	504.7	504.4	504.2	503.9	503.6	503.5	503.2
117.5°	574.5	574.8	574.4	573.4	572.3	571.3	570.2
120°	621.2	621.2	620.6	619.6	618.6	617.5	616.5
122.5°	666.8	666.6	666.1	665.2	664.4	663.6	662.8
125°	734.1	733.6	733.3	733.0	732.7	732.5	732.2
127.5°	801.5	801.3	800.8	800.4	799.9	799.3	798.8
130°	846.0	845.7	845.3	844.8	844.3	843.7	843.2
132.5°	888.5	888.2	887.8	887.1	886.3	885.6	884.8
135°	954.3	954.3	953.8	952.7	951.7	950.7	949.7
137.5°	1018.3	1018.7	1018.2	1016.9	1015.6	1014.3	1013.1
140°	1058.7	1059.3	1058.9	1057.6	1056.3	1055.1	1053.7
142.5°	1098.0	1098.2	1097.8	1096.4	1095.2	1093.9	1092.6
145°	1154.4	1154.4	1154.0	1153.2	1152.4	1151.6	1150.9
147.5°	1207.6	1208.2	1207.6	1205.9	1204.2	1202.4	1200.7
150°	1240.0	1240.0	1239.7	1239.2	1238.7	1238.1	1237.7
152.5°	1271.4	1272.0	1271.9	1271.0	1270.1	1269.1	1268.2
155°	1315.9	1317.0	1316.8	1315.5	1314.3	1313.0	1311.7
157.5°	1354.1	1355.1	1354.8	1353.1	1351.4	1349.7	1348.0
160°	1377.2	1378.2	1378.1	1376.9	1375.6	1374.3	1373.0
162.5°	1399.1	1400.3	1400.3	1398.7	1397.2	1395.8	1394.3
165°	1428.2	1429.1	1428.9	1427.4	1425.8	1424.2	1422.7
167.5°	1450.3	1451.8	1451.8	1450.2	1448.6	1447.0	1445.4
170°	1463.2	1464.7	1464.6	1462.9	1461.1	1459.2	1457.4
172.5°	1472.5	1474.0	1474.0	1472.4	1470.8	1469.2	1467.6
175°	1482.9	1484.4	1484.3	1482.5	1480.7	1478.9	1477.1
177.5°	1487.3	1488.5	1488.4	1486.9	1485.5	1484.1	1482.6
180°	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4	1486.4

(END OF REPORT)