

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333739-940

Luminaire Tested: **S125RDIW-S1270D1560U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333739-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1270D1560U940-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9174.6 lumens
Efficiency: N/A
Efficacy: 110.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333739-940

CATALOG NUMBER: S125RDIW-S1270D1560U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333739-940

CATALOG NUMBER: S125RDIW-S1270D1560U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	41	39
3	81	72	65	59	74	66	60	55	56	51	48	47	43	40	38	35	33
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	31	28	25
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22
7	58	46	38	33	53	43	36	31	37	31	27	31	27	23	25	22	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	18	16
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11889	11889	11889
5°	11916	11780	11852
10°	11825	11671	11671
15°	11685	11433	11340
20°	11504	11103	10970
25°	11294	10779	10541
30°	11032	10399	10068
35°	10764	10008	9536
40°	10514	9599	9014
45°	10209	9143	8444
50°	9904	8647	7850
55°	9549	8172	7218
60°	9195	7596	6536
65°	8775	6927	5757
70°	8295	6090	4962
75°	7633	5133	4127
80°	6721	4032	3466
85°	5669	3298	3090



TEST NUMBER: P333739-940

CATALOG NUMBER: S125RDIW-S1270D1560U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.1	1.9
10°-20°	483.7	5.3
20°-30°	701.4	7.6
30°-40°	799.4	8.7
40°-50°	779.2	8.5
50°-60°	655.9	7.1
60°-70°	459.8	5.0
70°-80°	236.3	2.6
80°-90°	63.5	0.7
90°-100°	115.7	1.3
100°-110°	341.8	3.7
110°-120°	578.9	6.3
120°-130°	761.9	8.3
130°-140°	853.7	9.3
140°-150°	836.7	9.1
150°-160°	702.8	7.7
160°-170°	467.2	5.1
170°-180°	163.5	1.8
0°-30°	1358.2	14.8
0°-40°	2157.6	23.5
0°-60°	3592.8	39.2
0°-90°	4352.4	47.4
90°-120°	1036.5	11.3
90°-150°	3488.8	38.0
90°-180°	4822.0	52.6
0°-180°	9174.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1841	1841	1841	1841	1841	
5°	1838	1832	1817	1830	1828	174
15°	1748	1738	1710	1708	1696	492
25°	1585	1562	1513	1495	1479	729
35°	1365	1330	1269	1230	1210	854
45°	1118	1075	1001	947	924	862
55°	848	802	726	665	641	758
65°	574	525	453	400	377	569
75°	306	263	206	176	165	324
85°	76	52	44	43	42	86
90°	1	12	22	28	32	8
95°	87	91	104	113	116	93
105°	307	313	322	329	334	327
115°	580	585	588	586	585	573
125°	846	854	855	853	851	757
135°	1100	1108	1110	1109	1104	848
145°	1333	1338	1342	1342	1338	833
155°	1525	1525	1526	1531	1525	702
165°	1658	1656	1657	1661	1654	468
175°	1724	1719	1719	1726	1717	164
180°	1728	1728	1728	1728	1728	



TEST NUMBER: P333739-940

CATALOG NUMBER: S125RDIW-S1270D1560U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8
2.5°	1844.1	1843.3	1842.5	1841.8	1841.1	1839.5	1837.0	1834.5	1832.1	1829.6	1832.1
5°	1838.0	1836.7	1835.5	1834.2	1833.0	1830.7	1827.3	1823.9	1820.5	1817.1	1820.2
7.5°	1819.9	1818.7	1817.6	1816.3	1815.2	1812.6	1808.5	1804.4	1800.4	1796.3	1798.4
10°	1803.2	1802.2	1801.3	1800.5	1799.5	1796.9	1792.5	1788.2	1783.9	1779.6	1780.5
12.5°	1784.3	1783.2	1781.9	1780.7	1779.6	1776.1	1770.3	1764.5	1758.6	1752.8	1753.5
15°	1747.6	1745.7	1743.9	1742.0	1740.2	1736.0	1729.5	1723.1	1716.5	1710.0	1709.8
17.5°	1706.1	1703.3	1700.5	1697.6	1694.8	1689.3	1681.1	1672.9	1664.8	1656.6	1655.1
20°	1673.9	1670.8	1667.7	1664.6	1661.5	1655.0	1645.2	1635.3	1625.4	1615.5	1614.0
22.5°	1638.3	1635.2	1632.1	1629.1	1625.9	1619.3	1608.8	1598.5	1588.0	1577.7	1574.7
25°	1584.9	1580.3	1575.7	1571.0	1566.4	1558.4	1546.9	1535.5	1524.0	1512.6	1508.6
27.5°	1523.8	1518.1	1512.5	1506.9	1501.3	1492.4	1480.1	1467.8	1455.6	1443.4	1437.8
30°	1479.3	1473.4	1467.5	1461.7	1455.8	1446.4	1433.3	1420.4	1407.4	1394.5	1387.3
32.5°	1435.9	1429.1	1422.2	1415.3	1408.5	1398.4	1385.2	1372.0	1358.7	1345.5	1337.7
35°	1365.3	1357.8	1350.4	1343.0	1335.6	1324.9	1311.0	1297.2	1283.3	1269.4	1260.3
37.5°	1296.0	1287.0	1278.0	1269.0	1259.9	1248.2	1233.9	1219.6	1205.2	1190.9	1180.2
40°	1247.1	1237.8	1228.5	1219.2	1210.1	1197.9	1183.1	1168.3	1153.4	1138.6	1126.9
42.5°	1196.0	1186.4	1176.9	1167.3	1157.9	1145.4	1130.2	1114.8	1099.5	1084.1	1072.9
45°	1117.8	1108.8	1099.8	1090.9	1081.9	1069.0	1052.0	1035.0	1018.0	1001.0	988.6
47.5°	1036.9	1027.4	1018.0	1008.5	999.1	985.8	968.7	951.5	934.4	917.3	904.6
50°	985.7	975.5	965.3	955.1	944.9	931.0	913.4	895.8	878.2	860.6	847.6
52.5°	930.1	919.6	909.2	898.8	888.3	874.8	858.2	841.6	824.9	808.3	794.3
55°	848.1	838.2	828.3	818.4	808.5	795.0	777.7	760.4	743.1	725.8	711.9
57.5°	765.2	754.7	744.0	733.5	722.9	709.4	692.7	675.9	659.2	642.6	629.0
60°	711.9	701.0	690.2	679.4	668.6	654.8	638.1	621.4	604.8	588.1	574.5
62.5°	655.1	644.8	634.5	624.1	613.9	600.2	583.3	566.3	549.4	532.4	519.9
65°	574.2	563.7	553.2	542.7	532.2	518.7	502.4	486.0	469.6	453.3	440.9
67.5°	493.8	483.3	472.8	462.4	451.8	438.7	423.0	407.3	391.6	375.9	364.6
70°	439.3	428.8	418.3	407.8	397.3	384.3	368.9	353.5	338.0	322.5	313.0
72.5°	385.9	375.7	365.4	355.2	344.9	332.5	318.1	303.6	289.2	274.7	265.9
75°	305.9	296.6	287.3	278.0	268.8	257.7	244.7	231.8	218.7	205.7	198.9
77.5°	226.3	218.9	211.5	204.1	196.7	187.8	177.4	167.0	156.7	146.2	141.5
80°	180.7	173.3	165.9	158.5	151.1	143.0	134.4	125.7	117.1	108.4	105.7
82.5°	136.3	129.6	122.9	116.2	109.6	103.3	97.3	91.4	85.4	79.5	78.2
85°	76.5	70.9	65.4	59.7	54.2	50.6	49.1	47.6	46.0	44.5	44.1
87.5°	25.9	24.6	23.4	22.1	20.9	20.3	20.5	20.7	20.8	21.0	21.3
90°	1.3	3.7	6.2	8.6	10.9	13.1	15.2	17.3	19.4	21.5	23.0
92.5°	32.5	34.2	35.9	37.5	39.2	41.4	44.0	46.5	49.0	51.6	53.6
95°	87.4	88.0	88.6	89.2	89.8	91.6	94.6	97.6	100.6	103.5	105.7
97.5°	145.3	145.4	145.7	146.0	146.2	148.4	152.5	156.7	160.8	164.9	166.8
100°	188.2	188.2	188.2	188.2	188.2	190.2	194.1	198.0	201.9	205.7	208.5
102.5°	234.5	235.8	236.9	238.1	239.3	240.9	242.9	244.9	246.8	248.8	251.7
105°	306.7	308.1	309.6	311.1	312.6	314.2	316.0	317.8	319.6	321.5	323.2
107.5°	386.2	387.7	389.2	390.7	392.2	393.7	395.0	396.4	397.8	399.1	400.0
110°	441.1	442.6	444.1	445.6	447.1	448.3	449.2	450.0	450.9	451.8	452.7



TEST NUMBER: P333739-940

CATALOG NUMBER: S125RDIW-S1270D1560U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	497.0	497.8	498.6	499.4	500.2	501.1	502.2	503.4	504.5	505.7	506.0
115°	579.6	580.9	582.0	583.2	584.4	585.3	585.9	586.5	587.1	587.7	587.4
117.5°	662.5	663.0	663.5	664.1	664.6	665.1	665.7	666.2	666.7	667.4	667.5
120°	714.1	715.6	717.1	718.6	720.1	720.9	721.3	721.6	721.8	722.2	722.2
122.5°	770.1	770.6	771.2	771.7	772.2	772.8	773.6	774.5	775.2	776.0	775.7
125°	845.9	847.7	849.5	851.3	853.1	854.2	854.4	854.7	855.1	855.3	854.7
127.5°	926.6	927.6	928.6	929.6	930.7	931.4	931.7	932.1	932.5	932.8	932.5
130°	975.0	976.5	978.0	979.5	981.0	982.0	982.7	983.2	983.8	984.4	984.1
132.5°	1023.4	1025.9	1028.3	1030.8	1033.2	1034.4	1034.3	1034.1	1034.0	1033.9	1033.6
135°	1100.1	1101.9	1103.7	1105.5	1107.2	1108.3	1108.6	1108.9	1109.2	1109.5	1109.5
137.5°	1172.2	1173.9	1175.6	1177.3	1179.1	1180.3	1181.0	1181.6	1182.2	1182.9	1183.3
140°	1218.4	1219.9	1221.4	1222.9	1224.4	1225.6	1226.5	1227.4	1228.3	1229.2	1229.8
142.5°	1264.7	1266.0	1267.2	1268.5	1269.7	1270.9	1272.0	1273.2	1274.3	1275.4	1275.8
145°	1332.8	1333.9	1335.2	1336.3	1337.6	1338.5	1339.4	1340.3	1341.2	1342.1	1342.1
147.5°	1395.7	1396.3	1397.0	1397.7	1398.3	1399.0	1399.7	1400.4	1401.1	1401.9	1402.6
150°	1437.6	1437.3	1437.1	1436.7	1436.5	1436.9	1438.1	1439.3	1440.5	1441.7	1441.7
152.5°	1472.0	1472.5	1472.9	1473.3	1473.7	1474.2	1474.7	1475.2	1475.6	1476.1	1476.9
155°	1525.1	1525.1	1525.1	1525.1	1525.1	1525.2	1525.5	1525.8	1526.1	1526.4	1527.6
157.5°	1572.4	1571.7	1571.1	1570.4	1569.8	1569.6	1569.9	1570.2	1570.5	1570.7	1572.0
160°	1600.4	1599.5	1598.6	1597.7	1596.8	1596.5	1596.8	1597.1	1597.4	1597.7	1598.8
162.5°	1625.1	1624.4	1623.8	1623.2	1622.5	1622.2	1622.2	1622.3	1622.4	1622.4	1623.9
165°	1658.2	1657.6	1657.0	1656.4	1655.8	1655.6	1656.0	1656.3	1656.5	1656.9	1658.0
167.5°	1686.1	1685.0	1683.8	1682.6	1681.4	1680.8	1680.8	1680.8	1680.8	1680.8	1682.6
170°	1701.2	1700.0	1698.8	1697.6	1696.5	1695.9	1695.9	1695.9	1695.9	1695.9	1697.6
172.5°	1712.0	1710.8	1709.6	1708.4	1707.2	1706.6	1706.6	1706.6	1706.6	1706.6	1708.4
175°	1724.1	1722.9	1721.7	1720.5	1719.3	1718.7	1718.7	1718.7	1718.7	1718.7	1720.5
177.5°	1730.3	1729.3	1728.4	1727.4	1726.4	1725.8	1725.6	1725.4	1725.1	1724.9	1726.4
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1



TEST NUMBER: P333739-940

CATALOG NUMBER: S125RDIW-S1270D1560U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8	1840.8
2.5°	1834.5	1837.0	1839.5	1840.6	1840.4	1840.1	1839.9	1839.6
5°	1823.3	1826.4	1829.4	1830.7	1830.1	1829.4	1828.8	1828.2
7.5°	1800.5	1802.8	1804.9	1805.6	1804.9	1804.3	1803.6	1803.0
10°	1781.4	1782.4	1783.2	1783.2	1782.4	1781.4	1780.5	1779.6
12.5°	1754.3	1754.9	1755.6	1755.2	1753.8	1752.4	1751.0	1749.5
15°	1709.4	1709.1	1708.8	1707.3	1704.5	1701.7	1698.9	1696.1
17.5°	1653.6	1652.0	1650.5	1648.6	1646.3	1644.0	1641.7	1639.4
20°	1612.4	1610.9	1609.4	1607.1	1604.4	1601.6	1598.8	1596.1
22.5°	1571.6	1568.6	1565.6	1562.9	1560.7	1558.4	1556.0	1553.8
25°	1504.6	1500.6	1496.6	1492.8	1489.4	1486.0	1482.6	1479.3
27.5°	1432.2	1426.6	1420.9	1416.5	1413.2	1409.9	1406.6	1403.4
30°	1380.3	1373.1	1366.0	1361.1	1358.3	1355.5	1352.7	1350.0
32.5°	1329.8	1322.0	1314.1	1308.4	1304.9	1301.4	1297.9	1294.3
35°	1251.4	1242.4	1233.5	1226.8	1222.5	1218.2	1213.9	1209.5
37.5°	1169.4	1158.7	1147.9	1140.4	1136.2	1132.0	1127.8	1123.6
40°	1115.2	1103.4	1091.7	1084.0	1080.2	1076.6	1072.8	1069.2
42.5°	1061.7	1050.4	1039.2	1030.8	1025.4	1019.9	1014.5	1009.1
45°	976.2	963.9	951.5	943.1	938.4	933.8	929.2	924.5
47.5°	891.9	879.1	866.4	857.5	852.3	847.2	842.0	837.0
50°	834.6	821.6	808.7	799.9	795.2	790.6	786.0	781.3
52.5°	780.3	766.4	752.4	743.2	738.5	733.9	729.2	724.6
55°	697.9	684.0	670.1	660.7	655.8	650.8	645.9	641.0
57.5°	615.4	601.8	588.2	579.3	574.8	570.4	566.1	561.7
60°	560.9	547.3	533.7	524.6	520.0	515.3	510.7	506.0
62.5°	507.3	494.6	482.1	473.4	468.8	464.1	459.5	454.9
65°	428.6	416.2	403.8	395.3	390.7	386.0	381.4	376.7
67.5°	353.3	342.0	330.7	323.2	319.5	315.8	312.1	308.4
70°	303.4	293.8	284.3	277.6	273.8	270.2	266.4	262.8
72.5°	257.1	248.3	239.3	233.7	231.2	228.8	226.3	223.8
75°	192.2	185.4	178.6	174.1	171.9	169.8	167.6	165.4
77.5°	136.7	132.0	127.2	124.0	122.4	120.8	119.2	117.6
80°	102.9	100.1	97.3	95.6	95.0	94.3	93.8	93.2
82.5°	77.0	75.6	74.4	73.5	73.1	72.8	72.4	72.1
85°	43.9	43.6	43.2	43.0	42.6	42.4	42.0	41.7
87.5°	21.6	21.8	22.2	22.3	22.2	22.2	22.1	22.0
90°	24.5	26.0	27.5	28.7	29.6	30.5	31.4	32.3
92.5°	55.6	57.5	59.6	60.8	61.5	62.2	62.8	63.5
95°	107.7	109.9	111.9	113.2	113.9	114.5	115.0	115.7
97.5°	168.8	170.8	172.7	174.0	174.3	174.7	175.0	175.4
100°	211.2	213.8	216.5	218.2	218.7	219.4	220.0	220.5
102.5°	254.7	257.6	260.5	262.4	263.2	264.0	264.9	265.7
105°	325.0	326.8	328.6	329.9	330.8	331.7	332.6	333.5
107.5°	400.9	401.8	402.7	403.1	403.1	403.1	403.0	402.9
110°	453.7	454.6	455.5	455.8	455.5	455.1	454.9	454.6



TEST NUMBER: P333739-940

CATALOG NUMBER: S125RDIW-S1270D1560U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	506.5	506.9	507.3	507.3	506.8	506.2	505.7	505.2
115°	587.1	586.8	586.5	586.2	585.9	585.6	585.3	585.1
117.5°	667.8	668.1	668.2	667.8	666.6	665.4	664.2	663.0
120°	722.2	722.2	722.2	721.6	720.4	719.2	718.0	716.8
122.5°	775.5	775.3	775.0	774.5	773.5	772.5	771.5	770.6
125°	854.2	853.5	852.9	852.5	852.2	851.9	851.6	851.3
127.5°	932.2	931.9	931.6	931.1	930.5	930.0	929.3	928.7
130°	983.8	983.6	983.2	982.8	982.2	981.6	981.0	980.4
132.5°	1033.3	1033.0	1032.7	1032.2	1031.4	1030.5	1029.7	1028.8
135°	1109.5	1109.5	1109.5	1108.9	1107.7	1106.5	1105.3	1104.1
137.5°	1183.7	1184.0	1184.4	1183.8	1182.3	1180.8	1179.3	1177.8
140°	1230.4	1231.0	1231.5	1231.1	1229.7	1228.2	1226.6	1225.1
142.5°	1276.1	1276.5	1276.9	1276.3	1274.8	1273.4	1271.8	1270.3
145°	1342.1	1342.1	1342.1	1341.7	1340.8	1339.9	1339.0	1338.1
147.5°	1403.3	1404.0	1404.7	1404.1	1402.0	1400.0	1398.0	1396.0
150°	1441.7	1441.7	1441.7	1441.4	1440.7	1440.2	1439.6	1439.0
152.5°	1477.6	1478.3	1479.0	1478.8	1477.7	1476.7	1475.6	1474.5
155°	1528.7	1530.0	1531.2	1531.1	1529.6	1528.0	1526.5	1525.1
157.5°	1573.2	1574.4	1575.6	1575.2	1573.2	1571.2	1569.2	1567.3
160°	1600.1	1601.2	1602.5	1602.3	1600.8	1599.3	1597.9	1596.3
162.5°	1625.3	1626.7	1628.2	1628.0	1626.3	1624.5	1622.8	1621.0
165°	1659.2	1660.5	1661.6	1661.3	1659.6	1657.8	1656.0	1654.1
167.5°	1684.4	1686.1	1687.9	1687.9	1686.0	1684.3	1682.4	1680.5
170°	1699.4	1701.2	1703.0	1702.9	1700.8	1698.7	1696.6	1694.5
172.5°	1710.2	1712.0	1713.8	1713.8	1711.9	1710.0	1708.2	1706.4
175°	1722.3	1724.1	1725.9	1725.7	1723.7	1721.5	1719.5	1717.3
177.5°	1727.8	1729.2	1730.6	1730.5	1728.8	1727.2	1725.5	1723.9
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1

(END OF REPORT)