

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333724-940

Luminaire Tested: **S125RDIW-S1270D770U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333724-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S1270D770U940-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 770 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7125.9 lumens  
Efficiency: N/A  
Efficacy: 119.2 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 59.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333724-940

CATALOG NUMBER: S125RDIW-S1270D770U940-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333724-940

CATALOG NUMBER: S125RDIW-S1270D770U940-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	97	93	90	94	91	88	85	80	77	75	69	68	66	60	59	57	53
2	92	85	79	74	86	80	75	70	70	66	63	61	58	56	53	51	49	45
3	85	75	68	62	79	71	64	59	62	57	53	55	51	48	48	45	42	39
4	78	67	59	53	72	63	56	51	56	50	46	49	45	41	43	40	37	34
5	71	60	52	46	67	56	49	44	50	44	40	44	40	36	39	35	32	29
6	66	54	46	40	62	51	44	38	45	39	35	40	35	32	35	31	29	26
7	61	49	41	35	57	46	39	34	41	35	31	37	32	28	32	28	25	23
8	57	44	37	31	53	42	35	30	38	32	28	33	29	25	30	26	23	21
9	53	41	33	28	50	38	32	27	35	29	25	31	26	23	27	24	21	19
10	49	37	30	25	46	35	29	24	32	26	22	29	24	21	25	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10936	10936	10936	10936
5°	12582	10950	9671	10950
10°	14432	10895	8533	10895
15°	15588	10783	7585	10783
20°	17189	10654	7003	10654
25°	19892	10481	6499	10481
30°	21647	10300	6169	10300
35°	18260	10089	5864	10089
40°	12752	9711	5602	9711
45°	9460	9199	5345	9199
50°	7543	8667	5126	8667
55°	6402	8007	4931	8007
60°	5531	7417	4615	7417
65°	4928	6776	3972	6776
70°	4330	6209	3622	6209
75°	3748	5375	3401	5375
80°	2841	4523	2841	4523
85°	2371	3557	2675	3557



TEST NUMBER: P333724-940

CATALOG NUMBER: S125RDIW-S1270D770U940-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	162.4	2.3
10°-20°	475.9	6.7
20°-30°	754.5	10.6
30°-40°	909.8	12.8
40°-50°	812.5	11.4
50°-60°	623.1	8.7
60°-70°	404.9	5.7
70°-80°	196.9	2.8
80°-90°	48.8	0.7
90°-100°	32.4	0.5
100°-110°	199.6	2.8
110°-120°	362.0	5.1
120°-130°	464.6	6.5
130°-140°	499.8	7.0
140°-150°	469.1	6.6
150°-160°	379.5	5.3
160°-170°	245.4	3.4
170°-180°	84.6	1.2
0°-30°	1392.7	19.5
0°-40°	2302.6	32.3
0°-60°	3738.2	52.5
0°-90°	4388.8	61.6
90°-120°	594.1	8.3
90°-150°	2027.6	28.5
90°-180°	2737.0	38.4
0°-180°	7125.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1693	1693	1693	1693	1693	
5°	1941	1689	1492	1689	1941	194
15°	2331	1613	1134	1613	2331	668
25°	2792	1471	912	1471	2792	1282
35°	2316	1280	744	1280	2316	1399
45°	1036	1007	585	1007	1036	826
55°	569	711	438	711	569	516
65°	322	443	260	443	322	321
75°	150	215	136	215	150	160
85°	32	48	36	48	32	37
90°	16	1	16	1	16	8
95°	14	38	14	38	14	11
105°	196	194	196	194	196	177
115°	362	365	362	365	362	359
125°	519	519	519	519	519	461
135°	644	647	644	647	644	497
145°	748	750	748	750	748	467
155°	820	826	820	826	820	378
165°	867	872	867	872	867	245
175°	887	891	887	891	887	84
180°	891	891	891	891	891	



TEST NUMBER: P333724-940

CATALOG NUMBER: S125RDIW-S1270D770U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1781.1	1780.0	1782.3	1776.1	1776.6	1767.2	1767.2	1760.0	1750.5	1743.3	1740.0
5°	1940.7	1942.1	1939.3	1928.9	1922.0	1911.6	1899.7	1878.8	1861.4	1844.8	1831.6
7.5°	2105.1	2106.0	2096.9	2093.6	2076.1	2063.3	2037.0	2008.7	1983.5	1951.6	1927.1
10°	2200.7	2200.0	2190.2	2182.6	2167.3	2147.9	2122.2	2088.7	2057.5	2022.8	1989.4
12.5°	2256.3	2254.5	2251.4	2242.1	2227.9	2210.7	2188.9	2156.1	2117.5	2079.5	2040.5
15°	2331.4	2326.5	2317.5	2305.6	2285.5	2265.3	2241.0	2211.8	2175.0	2131.9	2095.7
17.5°	2424.2	2424.4	2410.5	2394.1	2366.7	2331.1	2293.6	2246.4	2196.4	2148.9	2110.5
20°	2501.0	2498.8	2485.0	2453.0	2421.7	2377.2	2334.1	2276.4	2215.3	2153.4	2105.4
22.5°	2611.1	2605.7	2591.2	2549.2	2500.7	2443.4	2377.5	2307.0	2233.1	2162.8	2099.9
25°	2791.5	2787.3	2758.9	2710.2	2642.0	2553.8	2467.6	2371.0	2264.7	2172.2	2095.7
27.5°	2915.0	2910.4	2889.2	2848.8	2786.0	2693.1	2576.4	2447.3	2314.5	2187.4	2077.1
30°	2902.7	2913.1	2910.4	2891.6	2844.4	2760.9	2653.2	2507.9	2350.1	2200.7	2069.3
32.5°	2728.1	2737.5	2761.9	2798.7	2801.5	2768.1	2687.7	2553.5	2390.1	2220.2	2063.2
35°	2316.0	2328.6	2375.9	2450.2	2547.5	2628.9	2645.5	2573.3	2426.6	2243.8	2054.1
37.5°	1780.6	1849.0	1888.7	1967.0	2114.1	2263.7	2407.5	2460.5	2398.1	2234.1	2039.2
40°	1512.5	1529.2	1600.1	1688.4	1812.1	1967.8	2172.9	2320.9	2325.8	2211.8	2015.8
42.5°	1294.6	1315.7	1364.3	1434.9	1540.8	1696.5	1908.2	2103.5	2194.1	2150.6	1985.2
45°	1035.7	1051.7	1087.2	1141.4	1222.7	1351.3	1533.4	1759.3	1938.7	2008.8	1903.2
47.5°	850.8	859.4	890.3	931.6	991.8	1085.5	1226.5	1422.5	1637.6	1788.5	1773.6
50°	750.7	760.5	784.1	815.4	866.1	945.3	1057.9	1221.3	1443.1	1627.2	1664.1
52.5°	672.9	680.9	695.6	725.2	767.1	828.0	918.9	1066.7	1266.2	1462.0	1547.3
55°	568.6	574.2	585.9	602.6	636.1	679.8	758.3	860.5	1021.8	1219.2	1344.3
57.5°	482.7	485.4	492.9	508.4	531.5	563.5	620.2	706.8	822.4	1000.2	1138.3
60°	428.2	431.0	440.7	451.1	469.2	498.4	542.9	603.3	714.5	861.2	1000.9
62.5°	384.8	386.5	390.7	401.1	417.0	439.4	474.5	523.8	612.2	741.1	873.1
65°	322.5	323.2	324.6	333.0	342.7	359.4	382.3	417.1	483.8	581.1	697.9
67.5°	262.8	263.7	268.6	271.5	281.7	290.4	303.9	330.5	377.5	443.1	533.9
70°	229.3	228.7	233.5	237.0	240.5	250.9	259.9	281.5	310.7	360.8	436.5
72.5°	198.2	196.4	198.5	199.7	204.4	211.4	220.5	233.7	256.2	290.7	348.7
75°	150.2	150.9	150.9	152.2	155.7	158.5	161.2	168.2	180.7	203.7	235.0
77.5°	105.4	104.2	107.2	107.6	109.7	112.7	115.1	117.9	123.1	132.5	148.6
80°	76.4	76.4	77.1	79.3	78.6	79.9	83.4	86.2	92.5	98.0	103.5
82.5°	58.7	58.1	58.8	59.2	59.1	60.5	61.7	62.2	64.6	67.4	71.3
85°	32.0	32.0	32.6	32.6	33.3	33.3	34.1	34.1	34.1	34.8	35.5
87.5°	15.4	14.8	14.1	14.0	14.5	15.5	14.8	14.1	13.9	13.8	14.2
90°	15.9	15.4	15.0	14.5	14.1	13.5	12.8	12.0	11.3	10.6	9.5
92.5°	14.8	14.6	14.4	14.2	14.0	13.5	12.8	12.0	11.3	10.6	9.6
95°	13.9	13.9	13.9	13.9	13.9	13.5	12.8	12.0	11.3	10.6	16.1
97.5°	13.9	13.9	13.9	13.9	13.9	16.0	20.1	24.3	28.4	32.5	43.5
100°	13.9	14.4	15.1	15.6	16.2	27.5	49.3	71.2	93.1	114.9	114.4
102.5°	83.1	93.1	103.1	113.1	123.1	130.1	134.3	138.4	142.6	146.7	146.3
105°	196.3	196.4	196.5	196.7	196.8	196.9	196.9	196.9	196.9	196.9	196.9
107.5°	247.4	247.8	248.3	248.7	249.1	249.3	249.3	249.3	249.2	249.2	249.0
110°	282.8	282.7	282.5	282.3	282.2	282.3	282.8	283.2	283.7	284.1	283.8



TEST NUMBER: P333724-940

CATALOG NUMBER: S125RDIW-S1270D770U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	314.5	314.7	315.0	315.1	315.3	315.7	316.3	316.8	317.4	318.0	317.8
115°	362.0	362.9	363.8	364.7	365.6	366.3	366.9	367.5	368.1	368.7	368.5
117.5°	412.9	413.2	413.6	413.9	414.4	414.9	415.7	416.4	417.2	417.9	417.4
120°	444.0	444.8	445.5	446.2	446.9	447.5	447.7	448.1	448.4	448.6	448.2
122.5°	473.6	474.5	475.3	476.2	477.0	477.6	477.9	478.1	478.5	478.8	478.6
125°	518.7	519.2	519.5	520.0	520.4	520.9	521.6	522.1	522.7	523.3	523.3
127.5°	556.6	557.7	558.7	559.8	561.0	561.7	562.0	562.3	562.6	562.9	563.0
130°	584.1	584.8	585.6	586.3	587.0	587.6	588.1	588.5	588.9	589.3	589.2
132.5°	609.5	610.2	610.9	611.6	612.4	612.8	612.9	613.0	613.1	613.1	613.5
135°	644.2	645.1	646.0	646.8	647.7	648.4	648.6	648.9	649.2	649.5	649.8
137.5°	679.1	679.8	680.6	681.4	682.2	682.5	682.4	682.4	682.3	682.2	682.5
140°	699.7	700.6	701.5	702.3	703.2	703.6	703.2	702.9	702.7	702.3	702.5
142.5°	719.3	720.1	721.0	721.9	722.8	723.2	723.2	723.1	723.0	723.0	722.7
145°	748.0	748.9	749.7	750.6	751.4	751.8	751.7	751.5	751.4	751.3	751.3
147.5°	771.6	772.7	773.7	774.8	775.8	776.2	776.1	775.9	775.7	775.5	775.3
150°	786.9	788.1	789.3	790.4	791.7	792.1	791.8	791.5	791.2	790.9	790.6
152.5°	801.2	802.3	803.3	804.3	805.4	805.8	805.5	805.2	804.9	804.6	804.3
155°	819.9	821.2	822.3	823.5	824.7	825.0	824.6	824.1	823.7	823.2	823.0
157.5°	835.7	836.9	838.0	839.2	840.3	840.7	840.3	839.8	839.4	838.8	838.8
160°	845.7	846.9	848.1	849.3	850.4	850.7	850.2	849.5	849.0	848.4	848.2
162.5°	854.7	856.0	857.3	858.6	859.9	860.1	859.3	858.4	857.6	856.8	856.7
165°	866.8	868.1	869.2	870.4	871.6	871.7	870.8	870.0	869.1	868.2	868.1
167.5°	875.3	876.6	878.0	879.3	880.7	880.7	879.7	878.6	877.5	876.6	876.4
170°	880.1	881.4	882.7	884.0	885.4	885.5	884.3	883.1	881.9	880.7	880.6
172.5°	883.2	884.6	885.9	887.3	888.5	888.7	887.6	886.5	885.5	884.5	884.2
175°	887.3	888.7	890.0	891.4	892.6	892.7	891.5	890.4	889.2	888.1	887.9
177.5°	889.7	890.6	891.6	892.5	893.5	893.6	892.7	891.9	891.1	890.3	890.1
180°	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4



TEST NUMBER: P333724-940

CATALOG NUMBER: S125RDIW-S1270D770U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1740.0	1736.1	1728.8	1722.2	1713.9	1706.6	1701.6	1695.5	1687.7	1678.3	1670.4
5°	1816.9	1801.7	1781.5	1764.2	1742.0	1724.6	1706.5	1689.1	1671.7	1649.5	1630.0
7.5°	1902.4	1870.8	1840.0	1801.4	1766.4	1735.1	1705.0	1674.6	1644.8	1613.3	1582.9
10°	1954.6	1916.4	1874.0	1825.3	1780.8	1738.5	1699.5	1661.3	1621.0	1585.6	1547.3
12.5°	2003.6	1954.2	1905.7	1844.2	1790.8	1739.0	1689.5	1641.8	1598.7	1552.7	1511.7
15°	2047.7	1999.1	1944.9	1869.8	1795.5	1732.9	1674.5	1612.7	1559.1	1507.7	1461.8
17.5°	2064.8	2013.8	1950.9	1878.7	1797.4	1718.7	1643.5	1575.7	1512.7	1452.8	1401.1
20°	2058.2	2008.8	1944.2	1875.4	1788.5	1706.5	1625.1	1550.1	1479.9	1416.6	1361.7
22.5°	2042.1	1991.0	1928.6	1855.9	1773.4	1686.5	1599.6	1519.5	1445.9	1380.5	1320.5
25°	2017.9	1948.4	1884.5	1813.5	1735.0	1648.8	1559.1	1470.8	1392.3	1325.5	1260.3
27.5°	1992.7	1905.9	1824.6	1754.2	1671.2	1594.3	1507.8	1417.3	1334.7	1266.8	1199.7
30°	1969.9	1872.6	1782.9	1703.0	1624.4	1551.5	1469.5	1381.2	1296.4	1226.2	1158.1
32.5°	1941.5	1838.1	1739.5	1647.3	1571.6	1499.2	1425.0	1340.6	1258.0	1185.5	1116.3
35°	1905.9	1773.9	1666.9	1568.9	1484.7	1414.5	1347.8	1279.7	1196.9	1121.9	1054.4
37.5°	1859.2	1709.4	1585.6	1478.7	1390.1	1319.6	1266.9	1204.6	1129.1	1057.2	994.7
40°	1830.9	1662.7	1527.1	1421.5	1328.3	1253.9	1204.6	1151.8	1083.0	1015.6	953.0
42.5°	1793.1	1619.9	1468.2	1358.1	1264.4	1192.8	1142.9	1096.7	1039.0	975.5	908.5
45°	1719.0	1536.9	1377.7	1259.5	1165.0	1094.8	1048.2	1007.2	963.4	905.0	846.6
47.5°	1622.5	1450.3	1283.7	1154.7	1062.1	996.9	951.7	919.4	888.1	838.4	781.7
50°	1545.2	1379.1	1216.4	1091.3	992.6	930.8	888.3	862.6	834.1	788.9	741.6
52.5°	1454.0	1305.6	1146.4	1018.4	925.3	867.4	826.6	800.9	777.4	740.6	695.5
55°	1310.3	1180.3	1034.3	918.2	832.8	774.4	735.4	711.1	697.2	665.9	630.4
57.5°	1144.4	1051.2	922.6	810.7	735.0	677.3	648.8	628.1	612.4	590.3	565.3
60°	1028.8	963.4	848.0	741.6	672.2	617.2	591.6	574.2	559.5	540.8	521.3
62.5°	911.4	863.9	763.5	672.2	608.2	562.2	538.1	522.5	505.6	492.9	474.0
65°	754.2	711.8	642.3	570.7	511.6	474.7	457.4	443.4	433.0	419.1	405.9
67.5°	586.7	569.4	521.5	472.1	429.7	396.9	381.9	372.2	359.6	351.3	342.2
70°	483.8	475.5	441.4	408.8	369.1	346.9	333.0	328.8	313.5	305.1	298.9
72.5°	392.6	388.7	369.1	346.4	318.5	299.0	286.2	281.5	271.8	265.1	261.1
75°	269.0	270.4	266.9	252.4	241.9	229.3	218.3	215.4	208.6	203.0	199.5
77.5°	170.1	177.3	177.5	176.8	172.6	165.1	160.4	158.4	151.5	149.5	148.6
80°	116.8	124.4	131.3	130.6	129.3	127.2	123.8	121.6	118.2	116.1	114.7
82.5°	77.8	85.0	90.8	94.5	94.3	92.2	89.8	88.8	88.1	86.6	86.3
85°	36.8	38.3	40.3	45.2	48.7	49.3	48.7	48.0	45.8	46.5	47.3
87.5°	14.5	14.3	14.6	14.4	13.6	16.1	17.6	17.9	17.0	16.1	15.3
90°	8.6	7.5	6.4	5.4	4.2	3.0	1.9	0.6	1.9	3.0	4.2
92.5°	8.7	7.8	7.0	6.9	7.7	8.6	9.4	10.2	9.4	8.6	7.7
95°	21.8	27.3	32.9	35.9	36.4	36.7	37.2	37.6	37.2	36.7	36.4
97.5°	54.6	65.6	76.7	81.8	81.0	80.3	79.5	78.6	79.5	80.3	81.0
100°	113.8	113.2	112.6	112.1	111.6	111.2	110.8	110.3	110.8	111.2	111.6
102.5°	146.0	145.6	145.3	144.8	144.3	143.7	143.1	142.6	143.1	143.7	144.3
105°	196.9	196.9	196.9	196.6	196.0	195.5	194.8	194.2	194.8	195.5	196.0
107.5°	248.6	248.3	248.1	247.9	247.9	247.9	247.9	247.9	247.9	247.9	247.9
110°	283.6	283.2	282.9	282.8	282.8	282.8	282.8	282.8	282.8	282.8	282.8





TEST NUMBER: P333724-940

CATALOG NUMBER: S125RDIW-S1270D770U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	317.6	317.4	317.3	317.0	316.6	316.3	315.9	315.6	315.9	316.3	316.6
115°	368.4	368.3	368.1	367.7	366.9	366.2	365.4	364.7	365.4	366.2	366.9
117.5°	416.9	416.3	415.7	415.4	415.5	415.5	415.5	415.6	415.5	415.5	415.5
120°	447.7	447.3	446.8	446.7	446.8	447.0	447.2	447.3	447.2	447.0	446.8
122.5°	478.3	478.1	478.0	477.6	477.0	476.4	475.9	475.3	475.9	476.4	477.0
125°	523.3	523.3	523.3	522.8	521.7	520.8	519.7	518.7	519.7	520.8	521.7
127.5°	563.1	563.2	563.3	562.9	562.2	561.5	560.8	560.0	560.8	561.5	562.2
130°	589.1	588.9	588.8	588.4	587.6	586.8	586.1	585.4	586.1	586.8	587.6
132.5°	613.8	614.1	614.5	614.2	613.3	612.5	611.6	610.7	611.6	612.5	613.3
135°	650.1	650.4	650.7	650.4	649.5	648.6	647.7	646.8	647.7	648.6	649.5
137.5°	682.8	683.1	683.3	683.1	682.3	681.5	680.8	680.0	680.8	681.5	682.3
140°	702.7	702.8	702.9	702.8	702.6	702.3	702.0	701.7	702.0	702.3	702.6
142.5°	722.6	722.4	722.1	721.9	721.8	721.6	721.4	721.2	721.4	721.6	721.8
145°	751.3	751.3	751.3	751.1	750.8	750.6	750.2	749.9	750.2	750.6	750.8
147.5°	775.2	775.1	774.9	774.8	774.9	774.9	775.0	775.1	775.0	774.9	774.9
150°	790.3	790.0	789.7	789.7	790.0	790.3	790.6	790.9	790.6	790.3	790.0
152.5°	804.1	803.8	803.4	803.6	804.3	804.9	805.6	806.2	805.6	804.9	804.3
155°	822.7	822.4	822.1	822.4	823.2	824.1	825.0	825.9	825.0	824.1	823.2
157.5°	838.8	838.7	838.7	839.0	839.5	840.1	840.6	841.1	840.6	840.1	839.5
160°	848.1	847.9	847.7	848.2	849.0	849.9	850.8	851.7	850.8	849.9	849.0
162.5°	856.6	856.4	856.2	856.6	857.5	858.4	859.3	860.1	859.3	858.4	857.5
165°	867.9	867.7	867.6	868.0	868.9	869.8	870.6	871.5	870.6	869.8	868.9
167.5°	876.2	876.1	875.9	876.3	877.3	878.2	879.0	879.9	879.0	878.2	877.3
170°	880.5	880.3	880.1	880.6	881.6	882.6	883.7	884.8	883.7	882.6	881.6
172.5°	884.0	883.7	883.4	883.8	884.8	885.8	886.9	887.9	886.9	885.8	884.8
175°	887.7	887.6	887.4	887.8	888.7	889.6	890.5	891.4	890.5	889.6	888.7
177.5°	890.0	889.9	889.7	890.1	890.8	891.5	892.2	892.9	892.2	891.5	890.8
180°	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4



TEST NUMBER: P333724-940

CATALOG NUMBER: S125RDIW-S1270D770U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1664.9	1657.2	1651.5	1640.4	1632.6	1629.3	1623.2	1621.5	1627.6	1623.2	1622.6
5°	1615.4	1595.3	1579.3	1563.3	1545.9	1534.8	1518.1	1515.3	1511.2	1504.9	1503.5
7.5°	1556.0	1529.8	1509.2	1482.8	1459.8	1441.4	1420.5	1410.6	1405.2	1397.1	1386.3
10°	1516.0	1484.7	1457.0	1430.5	1402.0	1379.1	1358.3	1342.2	1331.8	1322.1	1317.9
12.5°	1476.5	1444.7	1409.1	1377.2	1345.3	1319.6	1296.5	1286.1	1274.5	1263.1	1253.4
15°	1415.2	1372.8	1333.9	1297.1	1270.0	1242.2	1219.9	1204.6	1187.2	1182.4	1163.6
17.5°	1350.1	1308.6	1263.0	1224.2	1192.8	1162.2	1137.7	1120.3	1107.3	1089.4	1080.8
20°	1309.6	1260.3	1215.8	1180.3	1145.5	1109.4	1084.3	1069.8	1057.2	1042.7	1035.7
22.5°	1266.2	1218.0	1172.3	1130.8	1095.5	1059.9	1042.1	1027.0	1012.7	999.3	990.1
25°	1202.6	1153.9	1105.9	1062.8	1026.0	1000.2	979.4	962.0	954.4	941.2	931.4
27.5°	1139.5	1087.8	1038.0	995.1	966.2	940.8	923.6	909.9	896.1	884.6	876.1
30°	1098.9	1046.2	991.9	957.9	927.3	902.9	884.1	870.9	860.5	850.1	843.8
32.5°	1058.4	1003.9	955.7	918.9	890.0	869.0	849.7	837.0	826.1	814.5	807.2
35°	993.3	937.7	898.8	862.6	834.1	814.7	801.5	783.4	774.4	766.0	758.3
37.5°	932.8	881.1	839.0	807.3	782.6	763.2	746.1	736.4	725.2	717.7	711.4
40°	888.3	841.1	802.8	769.5	751.4	729.9	713.9	701.3	693.0	683.3	676.4
42.5°	848.3	804.4	767.2	737.3	714.7	696.5	681.1	668.5	658.0	651.0	645.2
45°	791.8	748.0	711.8	683.9	663.2	645.8	629.7	623.5	609.6	601.3	598.5
47.5°	733.2	694.0	659.1	633.5	612.1	595.7	580.7	567.9	560.3	552.1	547.6
50°	693.8	656.2	623.5	598.5	577.7	559.5	545.6	537.3	526.9	519.2	513.7
52.5°	654.2	619.5	586.8	562.8	544.8	526.7	511.2	502.8	492.9	488.1	484.2
55°	597.8	561.0	533.2	509.5	490.7	474.0	459.5	451.1	444.9	440.0	438.6
57.5°	533.9	504.6	478.8	457.5	438.0	422.3	409.6	401.6	396.1	395.4	391.2
60°	492.1	465.7	442.1	419.1	402.4	387.9	376.7	367.7	362.1	361.4	360.1
62.5°	450.4	425.1	403.1	383.0	368.0	353.9	343.4	333.2	329.9	326.5	323.3
65°	388.5	365.6	347.6	331.5	315.6	303.7	293.4	287.0	279.5	275.3	267.6
67.5°	327.8	310.0	292.7	279.2	266.6	255.4	246.7	237.5	232.3	229.0	223.4
70°	287.8	273.8	256.5	241.9	232.2	223.1	216.2	205.7	202.2	199.5	196.7
72.5°	249.9	237.7	223.1	211.3	201.6	193.1	185.0	180.1	176.7	173.9	172.3
75°	196.7	184.9	172.4	164.1	157.1	150.2	146.0	142.5	141.1	140.4	137.6
77.5°	144.5	138.2	128.1	121.5	116.9	114.1	110.4	108.6	108.4	105.4	104.4
80°	110.5	107.0	98.7	95.9	92.5	89.7	87.6	84.1	80.6	79.3	77.1
82.5°	82.1	78.6	75.3	70.9	67.9	66.3	64.2	63.0	63.4	61.4	60.5
85°	43.8	40.3	39.0	38.3	36.8	38.3	37.5	36.8	36.1	35.5	36.1
87.5°	15.0	15.2	14.8	16.1	14.7	15.4	15.6	15.2	15.3	15.5	15.1
90°	5.4	6.4	7.5	8.6	9.5	10.6	11.3	12.0	12.8	13.5	14.1
92.5°	6.9	7.0	7.8	8.7	9.6	10.6	11.3	12.0	12.8	13.5	14.0
95°	35.9	32.9	27.3	21.8	16.1	10.6	11.3	12.0	12.8	13.5	13.9
97.5°	81.8	76.7	65.6	54.6	43.5	32.5	28.4	24.3	20.1	16.0	13.9
100°	112.1	112.6	113.2	113.8	114.4	114.9	93.1	71.2	49.3	27.5	16.2
102.5°	144.8	145.3	145.6	146.0	146.3	146.7	142.6	138.4	134.3	130.1	123.1
105°	196.6	196.9	196.9	196.9	196.9	196.9	196.9	196.9	196.9	196.9	196.8
107.5°	247.9	248.1	248.3	248.6	249.0	249.2	249.2	249.3	249.3	249.3	249.1
110°	282.8	282.9	283.2	283.6	283.8	284.1	283.7	283.2	282.8	282.3	282.2



TEST NUMBER: P333724-940

CATALOG NUMBER: S125RDIW-S1270D770U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	317.0	317.3	317.4	317.6	317.8	318.0	317.4	316.8	316.3	315.7	315.3
115°	367.7	368.1	368.3	368.4	368.5	368.7	368.1	367.5	366.9	366.3	365.6
117.5°	415.4	415.7	416.3	416.9	417.4	417.9	417.2	416.4	415.7	414.9	414.4
120°	446.7	446.8	447.3	447.7	448.2	448.6	448.4	448.1	447.7	447.5	446.9
122.5°	477.6	478.0	478.1	478.3	478.6	478.8	478.5	478.1	477.9	477.6	477.0
125°	522.8	523.3	523.3	523.3	523.3	523.3	522.7	522.1	521.6	520.9	520.4
127.5°	562.9	563.3	563.2	563.1	563.0	562.9	562.6	562.3	562.0	561.7	561.0
130°	588.4	588.8	588.9	589.1	589.2	589.3	588.9	588.5	588.1	587.6	587.0
132.5°	614.2	614.5	614.1	613.8	613.5	613.1	613.1	613.0	612.9	612.8	612.4
135°	650.4	650.7	650.4	650.1	649.8	649.5	649.2	648.9	648.6	648.4	647.7
137.5°	683.1	683.3	683.1	682.8	682.5	682.2	682.3	682.4	682.4	682.5	682.2
140°	702.8	702.9	702.8	702.7	702.5	702.3	702.7	702.9	703.2	703.6	703.2
142.5°	721.9	722.1	722.4	722.6	722.7	723.0	723.0	723.1	723.2	723.2	722.8
145°	751.1	751.3	751.3	751.3	751.3	751.3	751.4	751.5	751.7	751.8	751.4
147.5°	774.8	774.9	775.1	775.2	775.3	775.5	775.7	775.9	776.1	776.2	775.8
150°	789.7	789.7	790.0	790.3	790.6	790.9	791.2	791.5	791.8	792.1	791.7
152.5°	803.6	803.4	803.8	804.1	804.3	804.6	804.9	805.2	805.5	805.8	805.4
155°	822.4	822.1	822.4	822.7	823.0	823.2	823.7	824.1	824.6	825.0	824.7
157.5°	839.0	838.7	838.7	838.8	838.8	838.8	839.4	839.8	840.3	840.7	840.3
160°	848.2	847.7	847.9	848.1	848.2	848.4	849.0	849.5	850.2	850.7	850.4
162.5°	856.6	856.2	856.4	856.6	856.7	856.8	857.6	858.4	859.3	860.1	859.9
165°	868.0	867.6	867.7	867.9	868.1	868.2	869.1	870.0	870.8	871.7	871.6
167.5°	876.3	875.9	876.1	876.2	876.4	876.6	877.5	878.6	879.7	880.7	880.7
170°	880.6	880.1	880.3	880.5	880.6	880.7	881.9	883.1	884.3	885.5	885.4
172.5°	883.8	883.4	883.7	884.0	884.2	884.5	885.5	886.5	887.6	888.7	888.5
175°	887.8	887.4	887.6	887.7	887.9	888.1	889.2	890.4	891.5	892.7	892.6
177.5°	890.1	889.7	889.9	890.0	890.1	890.3	891.1	891.9	892.7	893.6	893.5
180°	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4



TEST NUMBER: P333724-940

CATALOG NUMBER: S125RDIW-S1270D770U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1622.1	1616.0	1614.3	1616.5	1614.3	1616.0	1622.1	1622.6	1623.2	1627.6	1621.5
5°	1496.6	1489.6	1493.1	1491.7	1493.1	1489.6	1496.6	1503.5	1504.9	1511.2	1515.3
7.5°	1386.2	1377.5	1368.3	1371.3	1368.3	1377.5	1386.2	1386.3	1397.1	1405.2	1410.6
10°	1308.9	1301.9	1297.7	1301.2	1297.7	1301.9	1308.9	1317.9	1322.1	1331.8	1342.2
12.5°	1243.8	1239.7	1236.0	1234.5	1236.0	1239.7	1243.8	1253.4	1263.1	1274.5	1286.1
15°	1155.2	1146.9	1143.4	1134.4	1143.4	1146.9	1155.2	1163.6	1182.4	1187.2	1204.6
17.5°	1073.6	1070.9	1061.8	1057.9	1061.8	1070.9	1073.6	1080.8	1089.4	1107.3	1120.3
20°	1025.3	1022.5	1013.4	1019.0	1013.4	1022.5	1025.3	1035.7	1042.7	1057.2	1069.8
22.5°	985.3	979.1	976.2	974.6	976.2	979.1	985.3	990.1	999.3	1012.7	1027.0
25°	928.6	919.6	916.1	912.0	916.1	919.6	928.6	931.4	941.2	954.4	962.0
27.5°	872.2	867.4	862.7	861.7	862.7	867.4	872.2	876.1	884.6	896.1	909.9
30°	835.5	830.6	827.2	827.2	827.2	830.6	835.5	843.8	850.1	860.5	870.9
32.5°	802.7	799.0	795.5	795.0	795.5	799.0	802.7	807.2	814.5	826.1	837.0
35°	754.9	749.3	748.0	743.8	748.0	749.3	754.9	758.3	766.0	774.4	783.4
37.5°	705.3	700.6	700.5	700.1	700.5	700.6	705.3	711.4	717.7	725.2	736.4
40°	673.5	670.0	669.4	664.5	669.4	670.0	673.5	676.4	683.3	693.0	701.3
42.5°	639.6	637.8	635.4	633.4	635.4	637.8	639.6	645.2	651.0	658.0	668.5
45°	593.6	588.7	588.7	585.2	588.7	588.7	593.6	598.5	601.3	609.6	623.5
47.5°	546.1	542.3	542.7	539.1	542.7	542.3	546.1	547.6	552.1	560.3	567.9
50°	514.3	512.3	511.6	510.2	511.6	512.3	514.3	513.7	519.2	526.9	537.3
52.5°	482.7	481.7	484.4	481.3	484.4	481.7	482.7	484.2	488.1	492.9	502.8
55°	440.0	437.9	442.1	437.9	442.1	437.9	440.0	438.6	440.0	444.9	451.1
57.5°	390.9	389.0	392.7	390.7	392.7	389.0	390.9	391.2	395.4	396.1	401.6
60°	358.6	354.5	356.6	357.3	356.6	354.5	358.6	360.1	361.4	362.1	367.7
62.5°	320.3	317.8	319.3	316.1	319.3	317.8	320.3	323.3	326.5	329.9	333.2
65°	266.3	264.1	261.4	259.9	261.4	264.1	266.3	267.6	275.3	279.5	287.0
67.5°	223.6	218.6	218.6	219.6	218.6	218.6	223.6	223.4	229.0	232.3	237.5
70°	192.5	192.5	191.8	191.8	191.8	192.5	192.5	196.7	199.5	202.2	205.7
72.5°	170.9	170.3	169.1	168.5	169.1	170.3	170.9	172.3	173.9	176.7	180.1
75°	137.6	138.3	137.0	136.3	137.0	138.3	137.6	137.6	140.4	141.1	142.5
77.5°	101.7	98.7	100.2	98.7	100.2	98.7	101.7	104.4	105.4	108.4	108.6
80°	77.1	76.4	78.6	76.4	78.6	76.4	77.1	77.1	79.3	80.6	84.1
82.5°	61.0	60.4	61.3	59.7	61.3	60.4	61.0	60.5	61.4	63.4	63.0
85°	36.8	36.1	35.5	36.1	35.5	36.1	36.8	36.1	35.5	36.1	36.8
87.5°	15.7	15.2	15.3	15.4	15.3	15.2	15.7	15.1	15.5	15.3	15.2
90°	14.5	15.0	15.4	15.9	15.4	15.0	14.5	14.1	13.5	12.8	12.0
92.5°	14.2	14.4	14.6	14.8	14.6	14.4	14.2	14.0	13.5	12.8	12.0
95°	13.9	13.9	13.9	13.9	13.9	13.9	13.9	13.9	13.5	12.8	12.0
97.5°	13.9	13.9	13.9	13.9	13.9	13.9	13.9	13.9	16.0	20.1	24.3
100°	15.6	15.1	14.4	13.9	14.4	15.1	15.6	16.2	27.5	49.3	71.2
102.5°	113.1	103.1	93.1	83.1	93.1	103.1	113.1	123.1	130.1	134.3	138.4
105°	196.7	196.5	196.4	196.3	196.4	196.5	196.7	196.8	196.9	196.9	196.9
107.5°	248.7	248.3	247.8	247.4	247.8	248.3	248.7	249.1	249.3	249.3	249.3
110°	282.3	282.5	282.7	282.8	282.7	282.5	282.3	282.2	282.3	282.8	283.2



TEST NUMBER: P333724-940

CATALOG NUMBER: S125RDIW-S1270D770U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	315.1	315.0	314.7	314.5	314.7	315.0	315.1	315.3	315.7	316.3	316.8
115°	364.7	363.8	362.9	362.0	362.9	363.8	364.7	365.6	366.3	366.9	367.5
117.5°	413.9	413.6	413.2	412.9	413.2	413.6	413.9	414.4	414.9	415.7	416.4
120°	446.2	445.5	444.8	444.0	444.8	445.5	446.2	446.9	447.5	447.7	448.1
122.5°	476.2	475.3	474.5	473.6	474.5	475.3	476.2	477.0	477.6	477.9	478.1
125°	520.0	519.5	519.2	518.7	519.2	519.5	520.0	520.4	520.9	521.6	522.1
127.5°	559.8	558.7	557.7	556.6	557.7	558.7	559.8	561.0	561.7	562.0	562.3
130°	586.3	585.6	584.8	584.1	584.8	585.6	586.3	587.0	587.6	588.1	588.5
132.5°	611.6	610.9	610.2	609.5	610.2	610.9	611.6	612.4	612.8	612.9	613.0
135°	646.8	646.0	645.1	644.2	645.1	646.0	646.8	647.7	648.4	648.6	648.9
137.5°	681.4	680.6	679.8	679.1	679.8	680.6	681.4	682.2	682.5	682.4	682.4
140°	702.3	701.5	700.6	699.7	700.6	701.5	702.3	703.2	703.6	703.2	702.9
142.5°	721.9	721.0	720.1	719.3	720.1	721.0	721.9	722.8	723.2	723.2	723.1
145°	750.6	749.7	748.9	748.0	748.9	749.7	750.6	751.4	751.8	751.7	751.5
147.5°	774.8	773.7	772.7	771.6	772.7	773.7	774.8	775.8	776.2	776.1	775.9
150°	790.4	789.3	788.1	786.9	788.1	789.3	790.4	791.7	792.1	791.8	791.5
152.5°	804.3	803.3	802.3	801.2	802.3	803.3	804.3	805.4	805.8	805.5	805.2
155°	823.5	822.3	821.2	819.9	821.2	822.3	823.5	824.7	825.0	824.6	824.1
157.5°	839.2	838.0	836.9	835.7	836.9	838.0	839.2	840.3	840.7	840.3	839.8
160°	849.3	848.1	846.9	845.7	846.9	848.1	849.3	850.4	850.7	850.2	849.5
162.5°	858.6	857.3	856.0	854.7	856.0	857.3	858.6	859.9	860.1	859.3	858.4
165°	870.4	869.2	868.1	866.8	868.1	869.2	870.4	871.6	871.7	870.8	870.0
167.5°	879.3	878.0	876.6	875.3	876.6	878.0	879.3	880.7	880.7	879.7	878.6
170°	884.0	882.7	881.4	880.1	881.4	882.7	884.0	885.4	885.5	884.3	883.1
172.5°	887.3	885.9	884.6	883.2	884.6	885.9	887.3	888.5	888.7	887.6	886.5
175°	891.4	890.0	888.7	887.3	888.7	890.0	891.4	892.6	892.7	891.5	890.4
177.5°	892.5	891.6	890.6	889.7	890.6	891.6	892.5	893.5	893.6	892.7	891.9
180°	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4



TEST NUMBER: P333724-940

CATALOG NUMBER: S125RDIW-S1270D770U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1623.2	1629.3	1632.6	1640.4	1651.5	1657.2	1664.9	1670.4	1678.3	1687.7	1695.5
5°	1518.1	1534.8	1545.9	1563.3	1579.3	1595.3	1615.4	1630.0	1649.5	1671.7	1689.1
7.5°	1420.5	1441.4	1459.8	1482.8	1509.2	1529.8	1556.0	1582.9	1613.3	1644.8	1674.6
10°	1358.3	1379.1	1402.0	1430.5	1457.0	1484.7	1516.0	1547.3	1585.6	1621.0	1661.3
12.5°	1296.5	1319.6	1345.3	1377.2	1409.1	1444.7	1476.5	1511.7	1552.7	1598.7	1641.8
15°	1219.9	1242.2	1270.0	1297.1	1333.9	1372.8	1415.2	1461.8	1507.7	1559.1	1612.7
17.5°	1137.7	1162.2	1192.8	1224.2	1263.0	1308.6	1350.1	1401.1	1452.8	1512.7	1575.7
20°	1084.3	1109.4	1145.5	1180.3	1215.8	1260.3	1309.6	1361.7	1416.6	1479.9	1550.1
22.5°	1042.1	1059.9	1095.5	1130.8	1172.3	1218.0	1266.2	1320.5	1380.5	1445.9	1519.5
25°	979.4	1000.2	1026.0	1062.8	1105.9	1153.9	1202.6	1260.3	1325.5	1392.3	1470.8
27.5°	923.6	940.8	966.2	995.1	1038.0	1087.8	1139.5	1199.7	1266.8	1334.7	1417.3
30°	884.1	902.9	927.3	957.9	991.9	1046.2	1098.9	1158.1	1226.2	1296.4	1381.2
32.5°	849.7	869.0	890.0	918.9	955.7	1003.9	1058.4	1116.3	1185.5	1258.0	1340.6
35°	801.5	814.7	834.1	862.6	898.8	937.7	993.3	1054.4	1121.9	1196.9	1279.7
37.5°	746.1	763.2	782.6	807.3	839.0	881.1	932.8	994.7	1057.2	1129.1	1204.6
40°	713.9	729.9	751.4	769.5	802.8	841.1	888.3	953.0	1015.6	1083.0	1151.8
42.5°	681.1	696.5	714.7	737.3	767.2	804.4	848.3	908.5	975.5	1039.0	1096.7
45°	629.7	645.8	663.2	683.9	711.8	748.0	791.8	846.6	905.0	963.4	1007.2
47.5°	580.7	595.7	612.1	633.5	659.1	694.0	733.2	781.7	838.4	888.1	919.4
50°	545.6	559.5	577.7	598.5	623.5	656.2	693.8	741.6	788.9	834.1	862.6
52.5°	511.2	526.7	544.8	562.8	586.8	619.5	654.2	695.5	740.6	777.4	800.9
55°	459.5	474.0	490.7	509.5	533.2	561.0	597.8	630.4	665.9	697.2	711.1
57.5°	409.6	422.3	438.0	457.5	478.8	504.6	533.9	565.3	590.3	612.4	628.1
60°	376.7	387.9	402.4	419.1	442.1	465.7	492.1	521.3	540.8	559.5	574.2
62.5°	343.4	353.9	368.0	383.0	403.1	425.1	450.4	474.0	492.9	505.6	522.5
65°	293.4	303.7	315.6	331.5	347.6	365.6	388.5	405.9	419.1	433.0	443.4
67.5°	246.7	255.4	266.6	279.2	292.7	310.0	327.8	342.2	351.3	359.6	372.2
70°	216.2	223.1	232.2	241.9	256.5	273.8	287.8	298.9	305.1	313.5	328.8
72.5°	185.0	193.1	201.6	211.3	223.1	237.7	249.9	261.1	265.1	271.8	281.5
75°	146.0	150.2	157.1	164.1	172.4	184.9	196.7	199.5	203.0	208.6	215.4
77.5°	110.4	114.1	116.9	121.5	128.1	138.2	144.5	148.6	149.5	151.5	158.4
80°	87.6	89.7	92.5	95.9	98.7	107.0	110.5	114.7	116.1	118.2	121.6
82.5°	64.2	66.3	67.9	70.9	75.3	78.6	82.1	86.3	86.6	88.1	88.8
85°	37.5	38.3	36.8	38.3	39.0	40.3	43.8	47.3	46.5	45.8	48.0
87.5°	15.6	15.4	14.7	16.1	14.8	15.2	15.0	15.3	16.1	17.0	17.9
90°	11.3	10.6	9.5	8.6	7.5	6.4	5.4	4.2	3.0	1.9	0.6
92.5°	11.3	10.6	9.6	8.7	7.8	7.0	6.9	7.7	8.6	9.4	10.2
95°	11.3	10.6	16.1	21.8	27.3	32.9	35.9	36.4	36.7	37.2	37.6
97.5°	28.4	32.5	43.5	54.6	65.6	76.7	81.8	81.0	80.3	79.5	78.6
100°	93.1	114.9	114.4	113.8	113.2	112.6	112.1	111.6	111.2	110.8	110.3
102.5°	142.6	146.7	146.3	146.0	145.6	145.3	144.8	144.3	143.7	143.1	142.6
105°	196.9	196.9	196.9	196.9	196.9	196.9	196.6	196.0	195.5	194.8	194.2
107.5°	249.2	249.2	249.0	248.6	248.3	248.1	247.9	247.9	247.9	247.9	247.9
110°	283.7	284.1	283.8	283.6	283.2	282.9	282.8	282.8	282.8	282.8	282.8



TEST NUMBER: P333724-940

CATALOG NUMBER: S125RDIW-S1270D770U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	317.4	318.0	317.8	317.6	317.4	317.3	317.0	316.6	316.3	315.9	315.6
115°	368.1	368.7	368.5	368.4	368.3	368.1	367.7	366.9	366.2	365.4	364.7
117.5°	417.2	417.9	417.4	416.9	416.3	415.7	415.4	415.5	415.5	415.5	415.6
120°	448.4	448.6	448.2	447.7	447.3	446.8	446.7	446.8	447.0	447.2	447.3
122.5°	478.5	478.8	478.6	478.3	478.1	478.0	477.6	477.0	476.4	475.9	475.3
125°	522.7	523.3	523.3	523.3	523.3	523.3	522.8	521.7	520.8	519.7	518.7
127.5°	562.6	562.9	563.0	563.1	563.2	563.3	562.9	562.2	561.5	560.8	560.0
130°	588.9	589.3	589.2	589.1	588.9	588.8	588.4	587.6	586.8	586.1	585.4
132.5°	613.1	613.1	613.5	613.8	614.1	614.5	614.2	613.3	612.5	611.6	610.7
135°	649.2	649.5	649.8	650.1	650.4	650.7	650.4	649.5	648.6	647.7	646.8
137.5°	682.3	682.2	682.5	682.8	683.1	683.3	683.1	682.3	681.5	680.8	680.0
140°	702.7	702.3	702.5	702.7	702.8	702.9	702.8	702.6	702.3	702.0	701.7
142.5°	723.0	723.0	722.7	722.6	722.4	722.1	721.9	721.8	721.6	721.4	721.2
145°	751.4	751.3	751.3	751.3	751.3	751.3	751.1	750.8	750.6	750.2	749.9
147.5°	775.7	775.5	775.3	775.2	775.1	774.9	774.8	774.9	774.9	775.0	775.1
150°	791.2	790.9	790.6	790.3	790.0	789.7	789.7	790.0	790.3	790.6	790.9
152.5°	804.9	804.6	804.3	804.1	803.8	803.4	803.6	804.3	804.9	805.6	806.2
155°	823.7	823.2	823.0	822.7	822.4	822.1	822.4	823.2	824.1	825.0	825.9
157.5°	839.4	838.8	838.8	838.8	838.7	838.7	839.0	839.5	840.1	840.6	841.1
160°	849.0	848.4	848.2	848.1	847.9	847.7	848.2	849.0	849.9	850.8	851.7
162.5°	857.6	856.8	856.7	856.6	856.4	856.2	856.6	857.5	858.4	859.3	860.1
165°	869.1	868.2	868.1	867.9	867.7	867.6	868.0	868.9	869.8	870.6	871.5
167.5°	877.5	876.6	876.4	876.2	876.1	875.9	876.3	877.3	878.2	879.0	879.9
170°	881.9	880.7	880.6	880.5	880.3	880.1	880.6	881.6	882.6	883.7	884.8
172.5°	885.5	884.5	884.2	884.0	883.7	883.4	883.8	884.8	885.8	886.9	887.9
175°	889.2	888.1	887.9	887.7	887.6	887.4	887.8	888.7	889.6	890.5	891.4
177.5°	891.1	890.3	890.1	890.0	889.9	889.7	890.1	890.8	891.5	892.2	892.9
180°	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4



TEST NUMBER: P333724-940

CATALOG NUMBER: S125RDIW-S1270D770U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1701.6	1706.6	1713.9	1722.2	1728.8	1736.1	1740.0	1740.0	1743.3	1750.5	1760.0
5°	1706.5	1724.6	1742.0	1764.2	1781.5	1801.7	1816.9	1831.6	1844.8	1861.4	1878.8
7.5°	1705.0	1735.1	1766.4	1801.4	1840.0	1870.8	1902.4	1927.1	1951.6	1983.5	2008.7
10°	1699.5	1738.5	1780.8	1825.3	1874.0	1916.4	1954.6	1989.4	2022.8	2057.5	2088.7
12.5°	1689.5	1739.0	1790.8	1844.2	1905.7	1954.2	2003.6	2040.5	2079.5	2117.5	2156.1
15°	1674.5	1732.9	1795.5	1869.8	1944.9	1999.1	2047.7	2095.7	2131.9	2175.0	2211.8
17.5°	1643.5	1718.7	1797.4	1878.7	1950.9	2013.8	2064.8	2110.5	2148.9	2196.4	2246.4
20°	1625.1	1706.5	1788.5	1875.4	1944.2	2008.8	2058.2	2105.4	2153.4	2215.3	2276.4
22.5°	1599.6	1686.5	1773.4	1855.9	1928.6	1991.0	2042.1	2099.9	2162.8	2233.1	2307.0
25°	1559.1	1648.8	1735.0	1813.5	1884.5	1948.4	2017.9	2095.7	2172.2	2264.7	2371.0
27.5°	1507.8	1594.3	1671.2	1754.2	1824.6	1905.9	1992.7	2077.1	2187.4	2314.5	2447.3
30°	1469.5	1551.5	1624.4	1703.0	1782.9	1872.6	1969.9	2069.3	2200.7	2350.1	2507.9
32.5°	1425.0	1499.2	1571.6	1647.3	1739.5	1838.1	1941.5	2063.2	2220.2	2390.1	2553.5
35°	1347.8	1414.5	1484.7	1568.9	1666.9	1773.9	1905.9	2054.1	2243.8	2426.6	2573.3
37.5°	1266.9	1319.6	1390.1	1478.7	1585.6	1709.4	1859.2	2039.2	2234.1	2398.1	2460.5
40°	1204.6	1253.9	1328.3	1421.5	1527.1	1662.7	1830.9	2015.8	2211.8	2325.8	2320.9
42.5°	1142.9	1192.8	1264.4	1358.1	1468.2	1619.9	1793.1	1985.2	2150.6	2194.1	2103.5
45°	1048.2	1094.8	1165.0	1259.5	1377.7	1536.9	1719.0	1903.2	2008.8	1938.7	1759.3
47.5°	951.7	996.9	1062.1	1154.7	1283.7	1450.3	1622.5	1773.6	1788.5	1637.6	1422.5
50°	888.3	930.8	992.6	1091.3	1216.4	1379.1	1545.2	1664.1	1627.2	1443.1	1221.3
52.5°	826.6	867.4	925.3	1018.4	1146.4	1305.6	1454.0	1547.3	1462.0	1266.2	1066.7
55°	735.4	774.4	832.8	918.2	1034.3	1180.3	1310.3	1344.3	1219.2	1021.8	860.5
57.5°	648.8	677.3	735.0	810.7	922.6	1051.2	1144.4	1138.3	1000.2	822.4	706.8
60°	591.6	617.2	672.2	741.6	848.0	963.4	1028.8	1000.9	861.2	714.5	603.3
62.5°	538.1	562.2	608.2	672.2	763.5	863.9	911.4	873.1	741.1	612.2	523.8
65°	457.4	474.7	511.6	570.7	642.3	711.8	754.2	697.9	581.1	483.8	417.1
67.5°	381.9	396.9	429.7	472.1	521.5	569.4	586.7	533.9	443.1	377.5	330.5
70°	333.0	346.9	369.1	408.8	441.4	475.5	483.8	436.5	360.8	310.7	281.5
72.5°	286.2	299.0	318.5	346.4	369.1	388.7	392.6	348.7	290.7	256.2	233.7
75°	218.3	229.3	241.9	252.4	266.9	270.4	269.0	235.0	203.7	180.7	168.2
77.5°	160.4	165.1	172.6	176.8	177.5	177.3	170.1	148.6	132.5	123.1	117.9
80°	123.8	127.2	129.3	130.6	131.3	124.4	116.8	103.5	98.0	92.5	86.2
82.5°	89.8	92.2	94.3	94.5	90.8	85.0	77.8	71.3	67.4	64.6	62.2
85°	48.7	49.3	48.7	45.2	40.3	38.3	36.8	35.5	34.8	34.1	34.1
87.5°	17.6	16.1	13.6	14.4	14.6	14.3	14.5	14.2	13.8	13.9	14.1
90°	1.9	3.0	4.2	5.4	6.4	7.5	8.6	9.5	10.6	11.3	12.0
92.5°	9.4	8.6	7.7	6.9	7.0	7.8	8.7	9.6	10.6	11.3	12.0
95°	37.2	36.7	36.4	35.9	32.9	27.3	21.8	16.1	10.6	11.3	12.0
97.5°	79.5	80.3	81.0	81.8	76.7	65.6	54.6	43.5	32.5	28.4	24.3
100°	110.8	111.2	111.6	112.1	112.6	113.2	113.8	114.4	114.9	93.1	71.2
102.5°	143.1	143.7	144.3	144.8	145.3	145.6	146.0	146.3	146.7	142.6	138.4
105°	194.8	195.5	196.0	196.6	196.9	196.9	196.9	196.9	196.9	196.9	196.9
107.5°	247.9	247.9	247.9	247.9	248.1	248.3	248.6	249.0	249.2	249.2	249.3
110°	282.8	282.8	282.8	282.8	282.9	283.2	283.6	283.8	284.1	283.7	283.2





TEST NUMBER: P333724-940

CATALOG NUMBER: S125RDIW-S1270D770U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	315.9	316.3	316.6	317.0	317.3	317.4	317.6	317.8	318.0	317.4	316.8
115°	365.4	366.2	366.9	367.7	368.1	368.3	368.4	368.5	368.7	368.1	367.5
117.5°	415.5	415.5	415.5	415.4	415.7	416.3	416.9	417.4	417.9	417.2	416.4
120°	447.2	447.0	446.8	446.7	446.8	447.3	447.7	448.2	448.6	448.4	448.1
122.5°	475.9	476.4	477.0	477.6	478.0	478.1	478.3	478.6	478.8	478.5	478.1
125°	519.7	520.8	521.7	522.8	523.3	523.3	523.3	523.3	523.3	522.7	522.1
127.5°	560.8	561.5	562.2	562.9	563.3	563.2	563.1	563.0	562.9	562.6	562.3
130°	586.1	586.8	587.6	588.4	588.8	588.9	589.1	589.2	589.3	588.9	588.5
132.5°	611.6	612.5	613.3	614.2	614.5	614.1	613.8	613.5	613.1	613.1	613.0
135°	647.7	648.6	649.5	650.4	650.7	650.4	650.1	649.8	649.5	649.2	648.9
137.5°	680.8	681.5	682.3	683.1	683.3	683.1	682.8	682.5	682.2	682.3	682.4
140°	702.0	702.3	702.6	702.8	702.9	702.8	702.7	702.5	702.3	702.7	702.9
142.5°	721.4	721.6	721.8	721.9	722.1	722.4	722.6	722.7	723.0	723.0	723.1
145°	750.2	750.6	750.8	751.1	751.3	751.3	751.3	751.3	751.3	751.4	751.5
147.5°	775.0	774.9	774.9	774.8	774.9	775.1	775.2	775.3	775.5	775.7	775.9
150°	790.6	790.3	790.0	789.7	789.7	790.0	790.3	790.6	790.9	791.2	791.5
152.5°	805.6	804.9	804.3	803.6	803.4	803.8	804.1	804.3	804.6	804.9	805.2
155°	825.0	824.1	823.2	822.4	822.1	822.4	822.7	823.0	823.2	823.7	824.1
157.5°	840.6	840.1	839.5	839.0	838.7	838.7	838.8	838.8	838.8	839.4	839.8
160°	850.8	849.9	849.0	848.2	847.7	847.9	848.1	848.2	848.4	849.0	849.5
162.5°	859.3	858.4	857.5	856.6	856.2	856.4	856.6	856.7	856.8	857.6	858.4
165°	870.6	869.8	868.9	868.0	867.6	867.7	867.9	868.1	868.2	869.1	870.0
167.5°	879.0	878.2	877.3	876.3	875.9	876.1	876.2	876.4	876.6	877.5	878.6
170°	883.7	882.6	881.6	880.6	880.1	880.3	880.5	880.6	880.7	881.9	883.1
172.5°	886.9	885.8	884.8	883.8	883.4	883.7	884.0	884.2	884.5	885.5	886.5
175°	890.5	889.6	888.7	887.8	887.4	887.6	887.7	887.9	888.1	889.2	890.4
177.5°	892.2	891.5	890.8	890.1	889.7	889.9	890.0	890.1	890.3	891.1	891.9
180°	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4



TEST NUMBER: P333724-940

CATALOG NUMBER: S125RDIW-S1270D770U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3	1693.3
2.5°	1767.2	1767.2	1776.6	1776.1	1782.3	1780.0	1781.1
5°	1899.7	1911.6	1922.0	1928.9	1939.3	1942.1	1940.7
7.5°	2037.0	2063.3	2076.1	2093.6	2096.9	2106.0	2105.1
10°	2122.2	2147.9	2167.3	2182.6	2190.2	2200.0	2200.7
12.5°	2188.9	2210.7	2227.9	2242.1	2251.4	2254.5	2256.3
15°	2241.0	2265.3	2285.5	2305.6	2317.5	2326.5	2331.4
17.5°	2293.6	2331.1	2366.7	2394.1	2410.5	2424.4	2424.2
20°	2334.1	2377.2	2421.7	2453.0	2485.0	2498.8	2501.0
22.5°	2377.5	2443.4	2500.7	2549.2	2591.2	2605.7	2611.1
25°	2467.6	2553.8	2642.0	2710.2	2758.9	2787.3	2791.5
27.5°	2576.4	2693.1	2786.0	2848.8	2889.2	2910.4	2915.0
30°	2653.2	2760.9	2844.4	2891.6	2910.4	2913.1	2902.7
32.5°	2687.7	2768.1	2801.5	2798.7	2761.9	2737.5	2728.1
35°	2645.5	2628.9	2547.5	2450.2	2375.9	2328.6	2316.0
37.5°	2407.5	2263.7	2114.1	1967.0	1888.7	1849.0	1780.6
40°	2172.9	1967.8	1812.1	1688.4	1600.1	1529.2	1512.5
42.5°	1908.2	1696.5	1540.8	1434.9	1364.3	1315.7	1294.6
45°	1533.4	1351.3	1222.7	1141.4	1087.2	1051.7	1035.7
47.5°	1226.5	1085.5	991.8	931.6	890.3	859.4	850.8
50°	1057.9	945.3	866.1	815.4	784.1	760.5	750.7
52.5°	918.9	828.0	767.1	725.2	695.6	680.9	672.9
55°	758.3	679.8	636.1	602.6	585.9	574.2	568.6
57.5°	620.2	563.5	531.5	508.4	492.9	485.4	482.7
60°	542.9	498.4	469.2	451.1	440.7	431.0	428.2
62.5°	474.5	439.4	417.0	401.1	390.7	386.5	384.8
65°	382.3	359.4	342.7	333.0	324.6	323.2	322.5
67.5°	303.9	290.4	281.7	271.5	268.6	263.7	262.8
70°	259.9	250.9	240.5	237.0	233.5	228.7	229.3
72.5°	220.5	211.4	204.4	199.7	198.5	196.4	198.2
75°	161.2	158.5	155.7	152.2	150.9	150.9	150.2
77.5°	115.1	112.7	109.7	107.6	107.2	104.2	105.4
80°	83.4	79.9	78.6	79.3	77.1	76.4	76.4
82.5°	61.7	60.5	59.1	59.2	58.8	58.1	58.7
85°	34.1	33.3	33.3	32.6	32.6	32.0	32.0
87.5°	14.8	15.5	14.5	14.0	14.1	14.8	15.4
90°	12.8	13.5	14.1	14.5	15.0	15.4	15.9
92.5°	12.8	13.5	14.0	14.2	14.4	14.6	14.8
95°	12.8	13.5	13.9	13.9	13.9	13.9	13.9
97.5°	20.1	16.0	13.9	13.9	13.9	13.9	13.9
100°	49.3	27.5	16.2	15.6	15.1	14.4	13.9
102.5°	134.3	130.1	123.1	113.1	103.1	93.1	83.1
105°	196.9	196.9	196.8	196.7	196.5	196.4	196.3
107.5°	249.3	249.3	249.1	248.7	248.3	247.8	247.4
110°	282.8	282.3	282.2	282.3	282.5	282.7	282.8



TEST NUMBER: P333724-940

CATALOG NUMBER: S125RDIW-S1270D770U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	316.3	315.7	315.3	315.1	315.0	314.7	314.5
115°	366.9	366.3	365.6	364.7	363.8	362.9	362.0
117.5°	415.7	414.9	414.4	413.9	413.6	413.2	412.9
120°	447.7	447.5	446.9	446.2	445.5	444.8	444.0
122.5°	477.9	477.6	477.0	476.2	475.3	474.5	473.6
125°	521.6	520.9	520.4	520.0	519.5	519.2	518.7
127.5°	562.0	561.7	561.0	559.8	558.7	557.7	556.6
130°	588.1	587.6	587.0	586.3	585.6	584.8	584.1
132.5°	612.9	612.8	612.4	611.6	610.9	610.2	609.5
135°	648.6	648.4	647.7	646.8	646.0	645.1	644.2
137.5°	682.4	682.5	682.2	681.4	680.6	679.8	679.1
140°	703.2	703.6	703.2	702.3	701.5	700.6	699.7
142.5°	723.2	723.2	722.8	721.9	721.0	720.1	719.3
145°	751.7	751.8	751.4	750.6	749.7	748.9	748.0
147.5°	776.1	776.2	775.8	774.8	773.7	772.7	771.6
150°	791.8	792.1	791.7	790.4	789.3	788.1	786.9
152.5°	805.5	805.8	805.4	804.3	803.3	802.3	801.2
155°	824.6	825.0	824.7	823.5	822.3	821.2	819.9
157.5°	840.3	840.7	840.3	839.2	838.0	836.9	835.7
160°	850.2	850.7	850.4	849.3	848.1	846.9	845.7
162.5°	859.3	860.1	859.9	858.6	857.3	856.0	854.7
165°	870.8	871.7	871.6	870.4	869.2	868.1	866.8
167.5°	879.7	880.7	880.7	879.3	878.0	876.6	875.3
170°	884.3	885.5	885.4	884.0	882.7	881.4	880.1
172.5°	887.6	888.7	888.5	887.3	885.9	884.6	883.2
175°	891.5	892.7	892.6	891.4	890.0	888.7	887.3
177.5°	892.7	893.6	893.5	892.5	891.6	890.6	889.7
180°	891.4	891.4	891.4	891.4	891.4	891.4	891.4

(END OF REPORT)