

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P402096

Luminaire Tested: **LA1MR022D010 EA1M22509035SC1MW**

Issue Date: 6/3/2020

Test Information

Test Method: LM-41-14
Report Number: P402096
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1912-604-8)
Test Lab: INNOVATION CENTER (G3)
Issue Date: 6/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LA1MR022D010 EA1M22509035SC1MW
Description: 1 INCH 50° OPTIC WITH SPECULAR CLEAR BAFFLE
Light Source: HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 451.7 lumens
Efficiency: N/A
Efficacy: 79.2 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.71
Luminous Opening: Rectangular (W 0.1' x L: 1.29' x H: 0')
CIE Type: Direct

Input Watts (W): 5.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P402096

CATALOG NUMBER: LA1MR022D010 EA1M22509035SC1MW

Luminous Intensity Polar Plot





TEST NUMBER: P402096

CATALOG NUMBER: LA1MR022D010 EA1M22509035SC1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100				
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95				95				
2	110	105	102	99	107	104	100	98	100	98	96	98	95	94	95	93	92	90				90				
3	105	99	95	92	103	98	94	91	96	92	90	93	90	88	91	89	87	85				85				
4	101	94	89	86	99	93	89	85	91	87	84	89	86	83	87	85	82	81				81				
5	97	89	84	81	95	89	84	80	87	83	80	85	82	79	84	81	78	77				77				
6	93	85	80	76	91	84	79	76	83	79	75	82	78	75	80	77	75	73				73				
7	89	81	76	72	88	80	76	72	79	75	72	78	74	71	77	74	71	70				70				
8	85	77	72	69	84	77	72	69	76	71	68	75	71	68	74	70	68	67				67				
9	82	74	69	65	81	73	69	65	73	68	65	72	68	65	71	67	65	64				64				
10	79	71	66	62	78	70	66	62	70	65	62	69	65	62	68	64	62	61				61				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	64024	64024	64024
5°	62397	62486	62446
10°	57782	57692	57603
15°	52667	52724	52799
20°	45172	45317	45138
25°	30621	31000	30948
30°	15168	15270	15214
35°	5069	5098	4795
40°	1159	1128	971
45°	453	498	419
50°	373	386	336
55°	335	335	293
60°	256	288	240
65°	170	189	133
70°	0	23	0
75°	0	0	0
80°	0	0	0
85°	0	0	0



TEST NUMBER: P402096

CATALOG NUMBER: LA1MR022D010 EA1M22509035SC1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.0	15.9
10°-20°	176.6	39.1
20°-30°	157.2	34.8
30°-40°	39.2	8.7
40°-50°	3.7	0.8
50°-60°	2.1	0.5
60°-70°	0.8	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	405.8	89.9
0°-40°	445.1	98.5
0°-60°	450.9	99.8
0°-90°	451.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	451.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	800	800	800	800	800	
5°	777	780	778	778	778	72
15°	636	639	637	635	638	177
25°	347	351	351	354	351	157
35°	52	54	52	51	49	39
45°	4	4	4	4	4	4
55°	2	2	2	2	2	2
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P402096

CATALOG NUMBER: LA1MR022D010 EA1M22509035SC1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	800.3	800.3	800.3	800.3	800.3
2.5°	795.7	799.2	796.7	796.9	797.0
5°	777.0	779.9	778.1	777.5	777.6
7.5°	745.6	748.1	745.3	746.3	745.1
10°	711.3	713.8	710.2	710.2	709.1
12.5°	676.4	679.0	674.8	674.3	677.1
15°	635.9	639.1	636.6	635.4	637.5
17.5°	594.9	594.5	593.0	592.3	591.5
20°	530.6	533.3	532.3	527.8	530.2
22.5°	446.1	446.2	447.7	448.5	446.5
25°	346.9	350.8	351.2	353.6	350.6
27.5°	257.0	257.8	253.8	254.1	256.9
30°	164.2	166.4	165.3	166.4	164.7
32.5°	94.7	96.7	95.9	96.8	97.0
35°	51.9	53.8	52.2	51.4	49.1
37.5°	25.7	25.7	26.3	24.2	23.1
40°	11.1	11.4	10.8	10.2	9.3
42.5°	5.6	5.6	5.9	5.0	4.9
45°	4.0	4.0	4.4	3.8	3.7
47.5°	3.4	3.4	3.7	3.3	3.1
50°	3.0	3.0	3.1	2.8	2.7
52.5°	2.7	2.7	2.8	2.5	2.4
55°	2.4	2.4	2.4	2.2	2.1
57.5°	1.9	2.1	2.1	1.9	1.8
60°	1.6	1.6	1.8	1.6	1.5
62.5°	1.3	1.3	1.3	1.3	1.2
65°	0.9	0.9	1.0	0.9	0.7
67.5°	0.1	0.3	0.7	0.0	0.0
70°	0.0	0.0	0.1	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)