

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333670-940

Luminaire Tested: **S125RDIW-S610D1050U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333670-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S610D1050U940-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5857.7 lumens
Efficiency: N/A
Efficacy: 129.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333670-940

CATALOG NUMBER: S125RDIW-S610D1050U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333670-940

CATALOG NUMBER: S125RDIW-S610D1050U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	104	104	104	104	94	94	94	94	76	76	76		59	59	59		43	43	43	36
1	95	91	87	84	86	82	79	76	66	64	62		52	51	49		39	38	37	31
2	86	79	73	68	78	72	67	63	58	55	52		46	43	41		34	33	31	26
3	79	70	63	57	71	63	57	53	52	47	44		41	38	35		30	28	27	22
4	72	62	54	48	65	56	50	45	46	41	37		36	33	30		27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32		33	29	26		25	22	20	17
6	61	49	41	36	55	45	38	33	37	32	28		29	26	23		22	20	18	15
7	56	44	37	31	51	41	34	29	33	28	25		27	23	20		20	18	16	13
8	52	40	33	28	47	37	30	26	30	25	22		24	21	18		19	16	14	12
9	49	37	29	25	44	34	27	23	28	23	19		22	19	16		17	15	13	11
10	45	34	27	22	41	31	25	20	26	21	18		21	17	15		16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5794	5794	5794
5°	5806	5741	5776
10°	5762	5687	5687
15°	5695	5572	5526
20°	5606	5411	5346
25°	5504	5253	5137
30°	5376	5068	4906
35°	5245	4877	4647
40°	5123	4678	4392
45°	4975	4455	4116
50°	4827	4214	3826
55°	4654	3983	3518
60°	4481	3702	3185
65°	4276	3376	2806
70°	4043	2968	2417
75°	3721	2500	2011
80°	3277	1967	1689
85°	2764	1608	1504



TEST NUMBER: P333670-940

CATALOG NUMBER: S125RDIW-S610D1050U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.3	1.4
10°-20°	235.7	4.0
20°-30°	341.8	5.8
30°-40°	389.6	6.7
40°-50°	379.7	6.5
50°-60°	319.6	5.5
60°-70°	224.1	3.8
70°-80°	115.2	2.0
80°-90°	31.6	0.5
90°-100°	44.2	0.8
100°-110°	272.5	4.7
110°-120°	494.2	8.4
120°-130°	634.2	10.8
130°-140°	682.1	11.6
140°-150°	640.3	10.9
150°-160°	517.9	8.8
160°-170°	335.0	5.7
170°-180°	115.5	2.0
0°-30°	661.9	11.3
0°-40°	1051.5	18.0
0°-60°	1750.9	29.9
0°-90°	2121.7	36.2
90°-120°	810.9	13.8
90°-150°	2767.5	47.2
90°-180°	3736.0	63.8
0°-180°	5857.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	897	897	897	897	897	
5°	896	893	886	892	891	85
15°	852	847	833	832	826	240
25°	772	761	737	728	721	355
35°	665	648	619	600	589	416
45°	545	524	488	462	451	420
55°	413	391	354	324	312	370
65°	280	256	221	195	184	277
75°	149	128	100	86	81	158
85°	37	26	22	21	20	42
90°	1	8	14	19	22	4
95°	51	47	14	19	19	66
105°	265	269	269	269	268	281
115°	498	502	503	500	494	493
125°	708	714	714	711	708	632
135°	883	888	886	884	879	680
145°	1024	1025	1025	1026	1021	640
155°	1127	1122	1124	1126	1119	519
165°	1190	1184	1185	1190	1183	336
175°	1217	1212	1212	1218	1211	116
180°	1217	1217	1217	1217	1217	



TEST NUMBER: P333670-940

CATALOG NUMBER: S125RDIW-S610D1050U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1
2.5°	898.7	898.3	898.0	897.6	897.2	896.4	895.2	894.0	892.8	891.6	892.8
5°	895.6	895.1	894.5	893.9	893.2	892.2	890.5	888.9	887.2	885.5	887.0
7.5°	886.9	886.3	885.7	885.1	884.6	883.3	881.3	879.3	877.4	875.3	876.4
10°	878.7	878.2	877.8	877.4	876.9	875.7	873.5	871.5	869.3	867.2	867.6
12.5°	869.5	869.0	868.3	867.8	867.2	865.5	862.7	859.9	857.0	854.2	854.5
15°	851.7	850.7	849.8	848.9	848.0	846.0	842.8	839.6	836.5	833.3	833.2
17.5°	831.4	830.1	828.7	827.3	825.9	823.2	819.2	815.3	811.3	807.4	806.6
20°	815.7	814.2	812.7	811.2	809.7	806.6	801.7	796.9	792.1	787.3	786.5
22.5°	798.3	796.8	795.4	793.9	792.4	789.1	784.0	779.0	773.9	768.8	767.4
25°	772.4	770.1	767.9	765.6	763.3	759.4	753.9	748.2	742.7	737.1	735.2
27.5°	742.5	739.9	737.1	734.3	731.6	727.3	721.3	715.3	709.4	703.4	700.6
30°	720.9	718.0	715.2	712.3	709.4	704.8	698.5	692.2	685.9	679.6	676.1
32.5°	699.7	696.4	693.0	689.7	686.3	681.4	675.0	668.6	662.1	655.7	651.8
35°	665.3	661.7	658.1	654.5	650.9	645.7	638.9	632.1	625.4	618.6	614.2
37.5°	631.6	627.1	622.8	618.4	614.0	608.3	601.3	594.3	587.4	580.3	575.2
40°	607.7	603.2	598.7	594.1	589.7	583.8	576.6	569.4	562.1	554.9	549.2
42.5°	582.8	578.2	573.5	568.9	564.3	558.2	550.7	543.2	535.8	528.3	522.8
45°	544.7	540.4	536.0	531.6	527.3	520.9	512.6	504.4	496.1	487.8	481.8
47.5°	505.3	500.7	496.1	491.5	486.9	480.4	472.1	463.7	455.4	447.0	440.9
50°	480.4	475.4	470.4	465.5	460.5	453.7	445.1	436.6	427.9	419.4	413.0
52.5°	453.3	448.2	443.1	438.0	432.9	426.3	418.2	410.1	402.0	393.9	387.1
55°	413.3	408.5	403.7	398.9	394.0	387.4	379.0	370.5	362.1	353.7	346.9
57.5°	372.9	367.7	362.6	357.5	352.3	345.6	337.5	329.4	321.3	313.2	306.5
60°	346.9	341.6	336.4	331.1	325.8	319.1	310.9	302.8	294.7	286.6	280.0
62.5°	319.2	314.2	309.2	304.2	299.2	292.5	284.3	276.0	267.8	259.5	253.3
65°	279.8	274.7	269.6	264.5	259.3	252.8	244.8	236.8	228.8	220.9	214.8
67.5°	240.7	235.5	230.4	225.3	220.2	213.8	206.2	198.5	190.8	183.2	177.7
70°	214.1	209.0	203.8	198.8	193.6	187.3	179.8	172.3	164.7	157.2	152.5
72.5°	188.1	183.1	178.1	173.1	168.1	162.0	155.0	147.9	140.9	133.8	129.6
75°	149.1	144.5	140.0	135.5	131.0	125.6	119.2	112.9	106.6	100.2	96.9
77.5°	110.3	106.6	103.1	99.4	95.9	91.5	86.4	81.4	76.3	71.2	68.9
80°	88.1	84.4	80.9	77.2	73.7	69.7	65.5	61.3	57.1	52.9	51.5
82.5°	66.4	63.1	59.9	56.6	53.4	50.3	47.4	44.5	41.6	38.8	38.2
85°	37.3	34.5	31.8	29.2	26.4	24.7	23.9	23.2	22.5	21.7	21.5
87.5°	12.7	12.1	11.6	11.1	10.5	10.3	10.5	10.7	10.9	11.1	11.2
90°	0.9	2.5	4.1	5.7	7.3	8.8	10.3	11.6	13.0	14.4	15.4
92.5°	13.9	12.8	11.7	10.5	9.4	9.5	10.7	11.9	13.2	14.4	15.4
95°	51.4	50.8	50.2	49.6	49.0	44.9	37.3	29.7	22.0	14.4	15.4
97.5°	107.4	108.4	109.5	110.6	111.6	104.7	89.6	74.5	59.5	44.4	38.7
100°	150.6	151.2	151.8	152.4	153.0	153.7	154.5	155.3	156.1	156.9	127.1
102.5°	194.7	195.4	196.2	196.9	197.7	198.3	198.8	199.2	199.7	200.2	194.6
105°	265.1	265.9	266.7	267.5	268.3	268.8	268.8	268.8	268.8	268.8	268.8
107.5°	338.4	338.4	338.4	338.4	338.4	338.6	338.9	339.4	339.7	340.2	340.2
110°	386.0	386.0	386.0	386.0	386.0	386.2	386.6	387.0	387.4	387.8	387.2



TEST NUMBER: P333670-940

CATALOG NUMBER: S125RDIW-S610D1050U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	430.7	431.2	431.7	432.1	432.7	433.0	433.3	433.5	433.7	434.0	433.2
115°	497.8	498.8	499.8	500.8	501.9	502.4	502.7	502.8	503.0	503.2	502.4
117.5°	567.3	567.2	567.2	567.1	567.1	567.5	568.2	569.0	569.7	570.5	569.4
120°	610.6	610.4	610.1	609.9	609.8	609.9	610.6	611.2	611.7	612.3	612.0
122.5°	648.8	649.5	650.3	651.0	651.8	652.4	652.6	652.9	653.2	653.4	653.1
125°	707.9	709.4	710.8	712.1	713.5	714.3	714.3	714.3	714.3	714.3	713.5
127.5°	764.4	765.4	766.4	767.4	768.4	768.8	768.7	768.7	768.5	768.4	767.9
130°	799.1	800.0	801.0	802.0	803.1	803.6	803.9	804.1	804.2	804.4	803.9
132.5°	833.7	834.8	836.0	837.1	838.3	838.7	838.2	837.8	837.3	837.0	836.8
135°	882.9	884.1	885.3	886.5	887.7	888.1	887.7	887.3	886.9	886.5	886.1
137.5°	928.2	929.3	930.2	931.3	932.4	932.7	932.4	932.0	931.6	931.2	931.3
140°	957.8	958.1	958.6	958.9	959.4	959.5	959.3	959.0	958.9	958.7	959.0
142.5°	984.4	984.7	985.0	985.2	985.4	985.7	986.0	986.2	986.5	986.8	986.9
145°	1023.6	1024.0	1024.4	1024.8	1025.2	1025.4	1025.4	1025.4	1025.4	1025.4	1025.6
147.5°	1057.8	1057.8	1057.7	1057.7	1057.6	1057.7	1057.8	1058.1	1058.4	1058.5	1058.8
150°	1079.5	1079.1	1078.7	1078.3	1077.9	1077.9	1078.3	1078.7	1079.1	1079.5	1080.0
152.5°	1100.5	1099.6	1098.7	1097.8	1096.9	1096.7	1097.1	1097.5	1097.9	1098.2	1098.7
155°	1127.3	1126.1	1124.9	1123.7	1122.5	1122.1	1122.5	1122.9	1123.3	1123.7	1124.3
157.5°	1148.1	1147.4	1146.7	1145.9	1145.1	1144.9	1144.9	1144.9	1145.0	1145.0	1145.7
160°	1162.5	1161.3	1160.1	1158.9	1157.7	1157.2	1157.4	1157.6	1157.8	1158.0	1158.8
162.5°	1174.0	1172.9	1171.6	1170.5	1169.2	1168.7	1168.9	1169.1	1169.3	1169.5	1170.6
165°	1189.5	1188.4	1187.1	1186.0	1184.7	1184.2	1184.5	1184.6	1184.8	1185.0	1186.2
167.5°	1201.0	1199.9	1198.6	1197.4	1196.1	1195.6	1195.8	1196.0	1196.2	1196.4	1197.8
170°	1207.6	1206.2	1204.8	1203.4	1201.9	1201.4	1201.6	1201.8	1201.9	1202.2	1203.8
172.5°	1211.9	1210.5	1209.1	1207.7	1206.3	1205.8	1206.1	1206.5	1206.8	1207.2	1208.6
175°	1216.6	1215.4	1214.2	1213.0	1211.7	1211.3	1211.5	1211.7	1211.9	1212.1	1213.7
177.5°	1218.8	1217.8	1216.8	1215.8	1215.0	1214.5	1214.7	1214.9	1215.0	1215.1	1216.3
180°	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6



TEST NUMBER: P333670-940

CATALOG NUMBER: S125RDIW-S610D1050U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1
2.5°	894.0	895.2	896.4	897.0	896.9	896.7	896.6	896.5
5°	888.5	890.0	891.5	892.2	891.8	891.5	891.3	890.9
7.5°	877.4	878.5	879.6	879.9	879.6	879.2	879.0	878.6
10°	868.1	868.5	869.1	869.1	868.5	868.1	867.6	867.2
12.5°	854.9	855.2	855.5	855.3	854.6	854.0	853.3	852.6
15°	833.0	832.9	832.8	832.0	830.6	829.3	828.0	826.5
17.5°	805.8	805.0	804.3	803.3	802.3	801.1	800.0	798.9
20°	785.8	785.0	784.3	783.2	781.9	780.5	779.2	777.8
22.5°	765.9	764.4	762.9	761.6	760.5	759.4	758.3	757.2
25°	733.3	731.3	729.3	727.5	725.9	724.2	722.6	720.9
27.5°	697.9	695.2	692.4	690.3	688.7	687.1	685.5	683.9
30°	672.6	669.1	665.7	663.3	661.9	660.6	659.2	657.9
32.5°	648.0	644.3	640.4	637.7	635.9	634.2	632.5	630.8
35°	609.8	605.5	601.1	597.9	595.8	593.6	591.6	589.4
37.5°	569.9	564.6	559.4	555.7	553.7	551.7	549.7	547.6
40°	543.4	537.7	532.0	528.2	526.5	524.6	522.8	521.0
42.5°	517.4	511.8	506.4	502.3	499.7	497.0	494.4	491.8
45°	475.7	469.8	463.7	459.6	457.4	455.0	452.8	450.6
47.5°	434.6	428.4	422.2	417.9	415.4	412.9	410.4	407.9
50°	406.7	400.4	394.0	389.8	387.5	385.3	383.0	380.8
52.5°	380.3	373.4	366.7	362.1	359.9	357.7	355.3	353.1
55°	340.1	333.3	326.5	322.0	319.6	317.2	314.8	312.4
57.5°	299.9	293.3	286.7	282.2	280.1	277.9	275.9	273.8
60°	273.3	266.7	260.1	255.7	253.4	251.1	248.9	246.6
62.5°	247.2	241.0	234.9	230.7	228.5	226.2	223.9	221.7
65°	208.8	202.8	196.8	192.6	190.4	188.2	185.8	183.6
67.5°	172.2	166.7	161.1	157.5	155.7	153.9	152.0	150.3
70°	147.8	143.2	138.5	135.3	133.5	131.7	129.8	128.0
72.5°	125.3	120.9	116.6	113.9	112.7	111.5	110.3	109.1
75°	93.6	90.3	87.0	84.8	83.8	82.8	81.7	80.6
77.5°	66.6	64.3	62.0	60.5	59.7	58.9	58.1	57.3
80°	50.1	48.8	47.4	46.6	46.3	46.0	45.7	45.4
82.5°	37.5	36.8	36.2	35.8	35.7	35.5	35.3	35.1
85°	21.4	21.2	21.0	21.0	20.8	20.6	20.5	20.3
87.5°	11.4	11.6	11.9	11.9	11.9	11.9	11.9	11.9
90°	16.4	17.5	18.5	19.3	19.9	20.4	21.0	21.7
92.5°	16.4	17.5	18.5	19.1	19.4	19.6	19.9	20.2
95°	16.4	17.5	18.5	18.9	18.9	18.9	18.9	18.9
97.5°	33.1	27.4	21.8	18.9	18.9	18.9	18.9	18.9
100°	97.2	67.3	37.5	22.1	21.3	20.5	19.7	18.9
102.5°	188.9	183.2	177.6	168.0	154.4	140.7	127.1	113.4
105°	268.8	268.8	268.8	268.7	268.5	268.2	268.0	267.9
107.5°	340.3	340.3	340.4	340.1	339.5	338.9	338.2	337.7
110°	386.6	386.0	385.4	385.2	385.4	385.6	385.8	386.0



TEST NUMBER: P333670-940

CATALOG NUMBER: S125RDIW-S610D1050U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	432.5	431.7	431.0	430.4	430.2	429.8	429.5	429.3
115°	501.6	500.8	500.0	499.0	497.8	496.6	495.4	494.2
117.5°	568.5	567.4	566.3	565.5	565.1	564.5	564.0	563.5
120°	611.5	611.2	610.7	610.0	609.0	608.1	607.1	606.0
122.5°	652.6	652.3	651.8	651.1	650.0	648.8	647.6	646.5
125°	712.7	711.9	711.1	710.3	709.8	709.2	708.6	707.9
127.5°	767.5	767.0	766.6	765.6	764.2	762.7	761.2	759.7
130°	803.3	802.6	802.0	801.2	800.2	799.2	798.3	797.3
132.5°	836.7	836.5	836.4	835.9	834.9	833.8	832.9	831.9
135°	885.7	885.3	884.9	884.1	882.9	881.7	880.5	879.3
137.5°	931.4	931.5	931.6	931.1	930.1	929.0	928.0	926.9
140°	959.5	959.8	960.3	959.8	958.7	957.4	956.3	955.0
142.5°	986.9	987.0	987.1	986.6	985.3	984.2	982.9	981.8
145°	1025.8	1026.0	1026.2	1025.7	1024.5	1023.3	1022.1	1020.9
147.5°	1059.1	1059.4	1059.5	1059.0	1057.5	1056.1	1054.6	1053.2
150°	1080.3	1080.8	1081.1	1080.5	1078.9	1077.3	1075.7	1074.1
152.5°	1099.0	1099.5	1099.8	1099.4	1097.9	1096.4	1095.0	1093.6
155°	1124.9	1125.5	1126.1	1125.6	1124.0	1122.4	1120.8	1119.2
157.5°	1146.3	1146.9	1147.5	1147.1	1145.5	1143.9	1142.3	1140.7
160°	1159.6	1160.4	1161.2	1160.7	1159.2	1157.6	1156.0	1154.4
162.5°	1171.8	1172.9	1174.0	1173.7	1171.9	1170.2	1168.4	1166.6
165°	1187.4	1188.7	1189.8	1189.6	1188.0	1186.4	1184.8	1183.2
167.5°	1199.3	1200.7	1202.2	1202.0	1200.2	1198.4	1196.6	1194.8
170°	1205.4	1207.0	1208.6	1208.4	1206.7	1204.9	1203.1	1201.2
172.5°	1210.1	1211.6	1213.0	1212.8	1211.0	1209.2	1207.4	1205.6
175°	1215.3	1216.9	1218.5	1218.4	1216.6	1214.8	1213.0	1211.2
177.5°	1217.4	1218.5	1219.7	1219.6	1218.3	1217.0	1215.8	1214.4
180°	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6	1216.6

(END OF REPORT)