

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333679-940

Luminaire Tested: **S125RDIW-S610D1560U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333679-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S610D1560U940-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6945.2 lumens  
Efficiency: N/A  
Efficacy: 114.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 60.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333679-940

CATALOG NUMBER: S125RDIW-S610D1560U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333679-940

CATALOG NUMBER: S125RDIW-S610D1560U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38	31
1	94	89	86	82	84	80	77	75	64	62	60	48	47	46	34	33	33	26
2	85	78	72	67	76	70	65	61	56	52	50	42	40	38	30	29	28	22
3	78	69	62	56	70	62	56	51	49	45	42	38	35	32	27	25	24	19
4	71	61	53	47	64	55	48	43	44	39	36	34	30	28	24	22	20	16
5	65	54	46	41	58	49	42	37	39	34	31	30	27	24	22	19	18	14
6	60	48	41	35	54	44	37	32	35	30	27	27	24	21	20	17	16	12
7	55	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14	11
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	16	14	12	10
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	15	13	11	9
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5794	5794	5794
5°	5806	5741	5776
10°	5762	5687	5687
15°	5695	5572	5526
20°	5606	5411	5346
25°	5504	5253	5137
30°	5376	5068	4906
35°	5245	4877	4647
40°	5123	4678	4392
45°	4975	4455	4116
50°	4827	4214	3826
55°	4654	3983	3518
60°	4481	3702	3185
65°	4276	3376	2806
70°	4043	2968	2417
75°	3721	2500	2011
80°	3277	1967	1689
85°	2764	1608	1504



TEST NUMBER: P333679-940

CATALOG NUMBER: S125RDIW-S610D1560U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	84.3	1.2
10°-20°	235.7	3.4
20°-30°	341.8	4.9
30°-40°	389.6	5.6
40°-50°	379.7	5.5
50°-60°	319.6	4.6
60°-70°	224.1	3.2
70°-80°	115.2	1.7
80°-90°	32.9	0.5
90°-100°	115.7	1.7
100°-110°	341.8	4.9
110°-120°	578.9	8.3
120°-130°	761.9	11.0
130°-140°	853.7	12.3
140°-150°	836.7	12.0
150°-160°	702.8	10.1
160°-170°	467.2	6.7
170°-180°	163.5	2.4
0°-30°	661.9	9.5
0°-40°	1051.5	15.1
0°-60°	1750.9	25.2
0°-90°	2123.0	30.6
90°-120°	1036.5	14.9
90°-150°	3488.8	50.2
90°-180°	4822.0	69.4
0°-180°	6945.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	897	897	897	897	897	
5°	896	893	886	892	891	85
15°	852	847	833	832	826	240
25°	772	761	737	728	721	355
35°	665	648	619	600	589	416
45°	545	524	488	462	451	420
55°	413	391	354	324	312	370
65°	280	256	221	195	184	277
75°	149	128	100	86	81	158
85°	37	26	22	21	20	42
90°	1	12	22	28	32	7
95°	87	91	104	113	116	93
105°	307	313	322	329	334	327
115°	580	585	588	586	585	573
125°	846	854	855	853	851	757
135°	1100	1108	1110	1109	1104	848
145°	1333	1338	1342	1342	1338	833
155°	1525	1525	1526	1531	1525	702
165°	1658	1656	1657	1661	1654	468
175°	1724	1719	1719	1726	1717	164
180°	1728	1728	1728	1728	1728	



TEST NUMBER: P333679-940

CATALOG NUMBER: S125RDIW-S610D1560U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1
2.5°	898.7	898.3	898.0	897.6	897.2	896.4	895.2	894.0	892.8	891.6	892.8
5°	895.6	895.1	894.5	893.9	893.2	892.2	890.5	888.9	887.2	885.5	887.0
7.5°	886.9	886.3	885.7	885.1	884.6	883.3	881.3	879.3	877.4	875.3	876.4
10°	878.7	878.2	877.8	877.4	876.9	875.7	873.5	871.5	869.3	867.2	867.6
12.5°	869.5	869.0	868.3	867.8	867.2	865.5	862.7	859.9	857.0	854.2	854.5
15°	851.7	850.7	849.8	848.9	848.0	846.0	842.8	839.6	836.5	833.3	833.2
17.5°	831.4	830.1	828.7	827.3	825.9	823.2	819.2	815.3	811.3	807.4	806.6
20°	815.7	814.2	812.7	811.2	809.7	806.6	801.7	796.9	792.1	787.3	786.5
22.5°	798.3	796.8	795.4	793.9	792.4	789.1	784.0	779.0	773.9	768.8	767.4
25°	772.4	770.1	767.9	765.6	763.3	759.4	753.9	748.2	742.7	737.1	735.2
27.5°	742.5	739.9	737.1	734.3	731.6	727.3	721.3	715.3	709.4	703.4	700.6
30°	720.9	718.0	715.2	712.3	709.4	704.8	698.5	692.2	685.9	679.6	676.1
32.5°	699.7	696.4	693.0	689.7	686.3	681.4	675.0	668.6	662.1	655.7	651.8
35°	665.3	661.7	658.1	654.5	650.9	645.7	638.9	632.1	625.4	618.6	614.2
37.5°	631.6	627.1	622.8	618.4	614.0	608.3	601.3	594.3	587.4	580.3	575.2
40°	607.7	603.2	598.7	594.1	589.7	583.8	576.6	569.4	562.1	554.9	549.2
42.5°	582.8	578.2	573.5	568.9	564.3	558.2	550.7	543.2	535.8	528.3	522.8
45°	544.7	540.4	536.0	531.6	527.3	520.9	512.6	504.4	496.1	487.8	481.8
47.5°	505.3	500.7	496.1	491.5	486.9	480.4	472.1	463.7	455.4	447.0	440.9
50°	480.4	475.4	470.4	465.5	460.5	453.7	445.1	436.6	427.9	419.4	413.0
52.5°	453.3	448.2	443.1	438.0	432.9	426.3	418.2	410.1	402.0	393.9	387.1
55°	413.3	408.5	403.7	398.9	394.0	387.4	379.0	370.5	362.1	353.7	346.9
57.5°	372.9	367.7	362.6	357.5	352.3	345.6	337.5	329.4	321.3	313.2	306.5
60°	346.9	341.6	336.4	331.1	325.8	319.1	310.9	302.8	294.7	286.6	280.0
62.5°	319.2	314.2	309.2	304.2	299.2	292.5	284.3	276.0	267.8	259.5	253.3
65°	279.8	274.7	269.6	264.5	259.3	252.8	244.8	236.8	228.8	220.9	214.8
67.5°	240.7	235.5	230.4	225.3	220.2	213.8	206.2	198.5	190.8	183.2	177.7
70°	214.1	209.0	203.8	198.8	193.6	187.3	179.8	172.3	164.7	157.2	152.5
72.5°	188.1	183.1	178.1	173.1	168.1	162.0	155.0	147.9	140.9	133.8	129.6
75°	149.1	144.5	140.0	135.5	131.0	125.6	119.2	112.9	106.6	100.2	96.9
77.5°	110.3	106.6	103.1	99.4	95.9	91.5	86.4	81.4	76.3	71.2	68.9
80°	88.1	84.4	80.9	77.2	73.7	69.7	65.5	61.3	57.1	52.9	51.5
82.5°	66.4	63.1	59.9	56.6	53.4	50.3	47.4	44.5	41.6	38.8	38.2
85°	37.3	34.5	31.8	29.2	26.4	24.7	23.9	23.2	22.5	21.7	21.5
87.5°	12.8	12.4	12.0	11.7	11.2	11.2	11.5	11.9	12.1	12.4	12.8
90°	1.3	3.7	6.2	8.6	10.9	13.1	15.2	17.3	19.4	21.5	23.0
92.5°	32.5	34.2	35.9	37.5	39.2	41.4	44.0	46.5	49.0	51.6	53.6
95°	87.4	88.0	88.6	89.2	89.8	91.6	94.6	97.6	100.6	103.5	105.7
97.5°	145.3	145.4	145.7	146.0	146.2	148.4	152.5	156.7	160.8	164.9	166.8
100°	188.2	188.2	188.2	188.2	188.2	190.2	194.1	198.0	201.9	205.7	208.5
102.5°	234.5	235.8	236.9	238.1	239.3	240.9	242.9	244.9	246.8	248.8	251.7
105°	306.7	308.1	309.6	311.1	312.6	314.2	316.0	317.8	319.6	321.5	323.2
107.5°	386.2	387.7	389.2	390.7	392.2	393.7	395.0	396.4	397.8	399.1	400.0
110°	441.1	442.6	444.1	445.6	447.1	448.3	449.2	450.0	450.9	451.8	452.7



TEST NUMBER: P333679-940

CATALOG NUMBER: S125RDIW-S610D1560U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	497.0	497.8	498.6	499.4	500.2	501.1	502.2	503.4	504.5	505.7	506.0
115°	579.6	580.9	582.0	583.2	584.4	585.3	585.9	586.5	587.1	587.7	587.4
117.5°	662.5	663.0	663.5	664.1	664.6	665.1	665.7	666.2	666.7	667.4	667.5
120°	714.1	715.6	717.1	718.6	720.1	720.9	721.3	721.6	721.8	722.2	722.2
122.5°	770.1	770.6	771.2	771.7	772.2	772.8	773.6	774.5	775.2	776.0	775.7
125°	845.9	847.7	849.5	851.3	853.1	854.2	854.4	854.7	855.1	855.3	854.7
127.5°	926.6	927.6	928.6	929.6	930.7	931.4	931.7	932.1	932.5	932.8	932.5
130°	975.0	976.5	978.0	979.5	981.0	982.0	982.7	983.2	983.8	984.4	984.1
132.5°	1023.4	1025.9	1028.3	1030.8	1033.2	1034.4	1034.3	1034.1	1034.0	1033.9	1033.6
135°	1100.1	1101.9	1103.7	1105.5	1107.2	1108.3	1108.6	1108.9	1109.2	1109.5	1109.5
137.5°	1172.2	1173.9	1175.6	1177.3	1179.1	1180.3	1181.0	1181.6	1182.2	1182.9	1183.3
140°	1218.4	1219.9	1221.4	1222.9	1224.4	1225.6	1226.5	1227.4	1228.3	1229.2	1229.8
142.5°	1264.7	1266.0	1267.2	1268.5	1269.7	1270.9	1272.0	1273.2	1274.3	1275.4	1275.8
145°	1332.8	1333.9	1335.2	1336.3	1337.6	1338.5	1339.4	1340.3	1341.2	1342.1	1342.1
147.5°	1395.7	1396.3	1397.0	1397.7	1398.3	1399.0	1399.7	1400.4	1401.1	1401.9	1402.6
150°	1437.6	1437.3	1437.1	1436.7	1436.5	1436.9	1438.1	1439.3	1440.5	1441.7	1441.7
152.5°	1472.0	1472.5	1472.9	1473.3	1473.7	1474.2	1474.7	1475.2	1475.6	1476.1	1476.9
155°	1525.1	1525.1	1525.1	1525.1	1525.1	1525.2	1525.5	1525.8	1526.1	1526.4	1527.6
157.5°	1572.4	1571.7	1571.1	1570.4	1569.8	1569.6	1569.9	1570.2	1570.5	1570.7	1572.0
160°	1600.4	1599.5	1598.6	1597.7	1596.8	1596.5	1596.8	1597.1	1597.4	1597.7	1598.8
162.5°	1625.1	1624.4	1623.8	1623.2	1622.5	1622.2	1622.2	1622.3	1622.4	1622.4	1623.9
165°	1658.2	1657.6	1657.0	1656.4	1655.8	1655.6	1656.0	1656.3	1656.5	1656.9	1658.0
167.5°	1686.1	1685.0	1683.8	1682.6	1681.4	1680.8	1680.8	1680.8	1680.8	1680.8	1682.6
170°	1701.2	1700.0	1698.8	1697.6	1696.5	1695.9	1695.9	1695.9	1695.9	1695.9	1697.6
172.5°	1712.0	1710.8	1709.6	1708.4	1707.2	1706.6	1706.6	1706.6	1706.6	1706.6	1708.4
175°	1724.1	1722.9	1721.7	1720.5	1719.3	1718.7	1718.7	1718.7	1718.7	1718.7	1720.5
177.5°	1730.3	1729.3	1728.4	1727.4	1726.4	1725.8	1725.6	1725.4	1725.1	1724.9	1726.4
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1



TEST NUMBER: P333679-940

CATALOG NUMBER: S125RDIW-S610D1560U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1
2.5°	894.0	895.2	896.4	897.0	896.9	896.7	896.6	896.5
5°	888.5	890.0	891.5	892.2	891.8	891.5	891.3	890.9
7.5°	877.4	878.5	879.6	879.9	879.6	879.2	879.0	878.6
10°	868.1	868.5	869.1	869.1	868.5	868.1	867.6	867.2
12.5°	854.9	855.2	855.5	855.3	854.6	854.0	853.3	852.6
15°	833.0	832.9	832.8	832.0	830.6	829.3	828.0	826.5
17.5°	805.8	805.0	804.3	803.3	802.3	801.1	800.0	798.9
20°	785.8	785.0	784.3	783.2	781.9	780.5	779.2	777.8
22.5°	765.9	764.4	762.9	761.6	760.5	759.4	758.3	757.2
25°	733.3	731.3	729.3	727.5	725.9	724.2	722.6	720.9
27.5°	697.9	695.2	692.4	690.3	688.7	687.1	685.5	683.9
30°	672.6	669.1	665.7	663.3	661.9	660.6	659.2	657.9
32.5°	648.0	644.3	640.4	637.7	635.9	634.2	632.5	630.8
35°	609.8	605.5	601.1	597.9	595.8	593.6	591.6	589.4
37.5°	569.9	564.6	559.4	555.7	553.7	551.7	549.7	547.6
40°	543.4	537.7	532.0	528.2	526.5	524.6	522.8	521.0
42.5°	517.4	511.8	506.4	502.3	499.7	497.0	494.4	491.8
45°	475.7	469.8	463.7	459.6	457.4	455.0	452.8	450.6
47.5°	434.6	428.4	422.2	417.9	415.4	412.9	410.4	407.9
50°	406.7	400.4	394.0	389.8	387.5	385.3	383.0	380.8
52.5°	380.3	373.4	366.7	362.1	359.9	357.7	355.3	353.1
55°	340.1	333.3	326.5	322.0	319.6	317.2	314.8	312.4
57.5°	299.9	293.3	286.7	282.2	280.1	277.9	275.9	273.8
60°	273.3	266.7	260.1	255.7	253.4	251.1	248.9	246.6
62.5°	247.2	241.0	234.9	230.7	228.5	226.2	223.9	221.7
65°	208.8	202.8	196.8	192.6	190.4	188.2	185.8	183.6
67.5°	172.2	166.7	161.1	157.5	155.7	153.9	152.0	150.3
70°	147.8	143.2	138.5	135.3	133.5	131.7	129.8	128.0
72.5°	125.3	120.9	116.6	113.9	112.7	111.5	110.3	109.1
75°	93.6	90.3	87.0	84.8	83.8	82.8	81.7	80.6
77.5°	66.6	64.3	62.0	60.5	59.7	58.9	58.1	57.3
80°	50.1	48.8	47.4	46.6	46.3	46.0	45.7	45.4
82.5°	37.5	36.8	36.2	35.8	35.7	35.5	35.3	35.1
85°	21.4	21.2	21.0	21.0	20.8	20.6	20.5	20.3
87.5°	13.0	13.3	13.6	13.8	13.9	13.9	14.0	14.0
90°	24.5	26.0	27.5	28.7	29.6	30.5	31.4	32.3
92.5°	55.6	57.5	59.6	60.8	61.5	62.2	62.8	63.5
95°	107.7	109.9	111.9	113.2	113.9	114.5	115.0	115.7
97.5°	168.8	170.8	172.7	174.0	174.3	174.7	175.0	175.4
100°	211.2	213.8	216.5	218.2	218.7	219.4	220.0	220.5
102.5°	254.7	257.6	260.5	262.4	263.2	264.0	264.9	265.7
105°	325.0	326.8	328.6	329.9	330.8	331.7	332.6	333.5
107.5°	400.9	401.8	402.7	403.1	403.1	403.1	403.0	402.9
110°	453.7	454.6	455.5	455.8	455.5	455.1	454.9	454.6





TEST NUMBER: P333679-940

CATALOG NUMBER: S125RDIW-S610D1560U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	506.5	506.9	507.3	507.3	506.8	506.2	505.7	505.2
115°	587.1	586.8	586.5	586.2	585.9	585.6	585.3	585.1
117.5°	667.8	668.1	668.2	667.8	666.6	665.4	664.2	663.0
120°	722.2	722.2	722.2	721.6	720.4	719.2	718.0	716.8
122.5°	775.5	775.3	775.0	774.5	773.5	772.5	771.5	770.6
125°	854.2	853.5	852.9	852.5	852.2	851.9	851.6	851.3
127.5°	932.2	931.9	931.6	931.1	930.5	930.0	929.3	928.7
130°	983.8	983.6	983.2	982.8	982.2	981.6	981.0	980.4
132.5°	1033.3	1033.0	1032.7	1032.2	1031.4	1030.5	1029.7	1028.8
135°	1109.5	1109.5	1109.5	1108.9	1107.7	1106.5	1105.3	1104.1
137.5°	1183.7	1184.0	1184.4	1183.8	1182.3	1180.8	1179.3	1177.8
140°	1230.4	1231.0	1231.5	1231.1	1229.7	1228.2	1226.6	1225.1
142.5°	1276.1	1276.5	1276.9	1276.3	1274.8	1273.4	1271.8	1270.3
145°	1342.1	1342.1	1342.1	1341.7	1340.8	1339.9	1339.0	1338.1
147.5°	1403.3	1404.0	1404.7	1404.1	1402.0	1400.0	1398.0	1396.0
150°	1441.7	1441.7	1441.7	1441.4	1440.7	1440.2	1439.6	1439.0
152.5°	1477.6	1478.3	1479.0	1478.8	1477.7	1476.7	1475.6	1474.5
155°	1528.7	1530.0	1531.2	1531.1	1529.6	1528.0	1526.5	1525.1
157.5°	1573.2	1574.4	1575.6	1575.2	1573.2	1571.2	1569.2	1567.3
160°	1600.1	1601.2	1602.5	1602.3	1600.8	1599.3	1597.9	1596.3
162.5°	1625.3	1626.7	1628.2	1628.0	1626.3	1624.5	1622.8	1621.0
165°	1659.2	1660.5	1661.6	1661.3	1659.6	1657.8	1656.0	1654.1
167.5°	1684.4	1686.1	1687.9	1687.9	1686.0	1684.3	1682.4	1680.5
170°	1699.4	1701.2	1703.0	1702.9	1700.8	1698.7	1696.6	1694.5
172.5°	1710.2	1712.0	1713.8	1713.8	1711.9	1710.0	1708.2	1706.4
175°	1722.3	1724.1	1725.9	1725.7	1723.7	1721.5	1719.5	1717.3
177.5°	1727.8	1729.2	1730.6	1730.5	1728.8	1727.2	1725.5	1723.9
180°	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1	1728.1

(END OF REPORT)