

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333666-940

Luminaire Tested: **S125RDIW-S610D770U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333666-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S610D770U940-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4858.1 lumens
Efficiency: N/A
Efficacy: 129.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333666-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333666-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44
1	97	92	89	85	88	85	81	79	70	68	66	57	55	54	45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	40	38	36	31
3	80	71	64	58	73	65	59	54	55	50	46	45	41	39	35	33	31	27
4	74	63	55	49	67	58	51	46	49	44	40	40	36	33	32	29	27	23
5	68	56	48	42	62	52	45	40	43	38	34	36	32	29	29	26	24	20
6	62	50	42	37	57	47	40	34	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19	16
8	53	41	34	29	49	38	31	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15	13
10	46	35	27	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5794	5794	5794
5°	5806	5741	5776
10°	5762	5687	5687
15°	5695	5572	5526
20°	5606	5411	5346
25°	5504	5253	5137
30°	5376	5068	4906
35°	5245	4877	4647
40°	5123	4678	4392
45°	4975	4455	4116
50°	4827	4214	3826
55°	4654	3983	3518
60°	4481	3702	3185
65°	4276	3376	2806
70°	4043	2968	2417
75°	3721	2500	2011
80°	3277	1967	1689
85°	2764	1608	1504



TEST NUMBER: P333666-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.3	1.7
10°-20°	235.7	4.9
20°-30°	341.8	7.0
30°-40°	389.6	8.0
40°-50°	379.7	7.8
50°-60°	319.6	6.6
60°-70°	224.1	4.6
70°-80°	115.2	2.4
80°-90°	30.9	0.6
90°-100°	32.4	0.7
100°-110°	199.6	4.1
110°-120°	362.0	7.5
120°-130°	464.6	9.6
130°-140°	499.8	10.3
140°-150°	469.1	9.7
150°-160°	379.5	7.8
160°-170°	245.4	5.1
170°-180°	84.6	1.7
0°-30°	661.9	13.6
0°-40°	1051.5	21.6
0°-60°	1750.9	36.0
0°-90°	2121.0	43.7
90°-120°	594.1	12.2
90°-150°	2027.6	41.7
90°-180°	2737.0	56.3
0°-180°	4858.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	897	897	897	897	897	
5°	896	893	886	892	891	85
15°	852	847	833	832	826	240
25°	772	761	737	728	721	355
35°	665	648	619	600	589	416
45°	545	524	488	462	451	420
55°	413	391	354	324	312	370
65°	280	256	221	195	184	277
75°	149	128	100	86	81	158
85°	37	26	22	21	20	42
90°	1	6	11	14	16	3
95°	38	34	11	14	14	48
105°	194	197	197	197	196	206
115°	365	368	369	366	362	361
125°	519	523	523	521	519	463
135°	647	651	650	648	644	498
145°	750	751	751	752	748	469
155°	826	822	823	825	820	380
165°	872	868	868	872	867	246
175°	891	888	888	893	887	85
180°	891	891	891	891	891	



TEST NUMBER: P333666-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1
2.5°	898.7	898.3	898.0	897.6	897.2	896.4	895.2	894.0	892.8	891.6	892.8
5°	895.6	895.1	894.5	893.9	893.2	892.2	890.5	888.9	887.2	885.5	887.0
7.5°	886.9	886.3	885.7	885.1	884.6	883.3	881.3	879.3	877.4	875.3	876.4
10°	878.7	878.2	877.8	877.4	876.9	875.7	873.5	871.5	869.3	867.2	867.6
12.5°	869.5	869.0	868.3	867.8	867.2	865.5	862.7	859.9	857.0	854.2	854.5
15°	851.7	850.7	849.8	848.9	848.0	846.0	842.8	839.6	836.5	833.3	833.2
17.5°	831.4	830.1	828.7	827.3	825.9	823.2	819.2	815.3	811.3	807.4	806.6
20°	815.7	814.2	812.7	811.2	809.7	806.6	801.7	796.9	792.1	787.3	786.5
22.5°	798.3	796.8	795.4	793.9	792.4	789.1	784.0	779.0	773.9	768.8	767.4
25°	772.4	770.1	767.9	765.6	763.3	759.4	753.9	748.2	742.7	737.1	735.2
27.5°	742.5	739.9	737.1	734.3	731.6	727.3	721.3	715.3	709.4	703.4	700.6
30°	720.9	718.0	715.2	712.3	709.4	704.8	698.5	692.2	685.9	679.6	676.1
32.5°	699.7	696.4	693.0	689.7	686.3	681.4	675.0	668.6	662.1	655.7	651.8
35°	665.3	661.7	658.1	654.5	650.9	645.7	638.9	632.1	625.4	618.6	614.2
37.5°	631.6	627.1	622.8	618.4	614.0	608.3	601.3	594.3	587.4	580.3	575.2
40°	607.7	603.2	598.7	594.1	589.7	583.8	576.6	569.4	562.1	554.9	549.2
42.5°	582.8	578.2	573.5	568.9	564.3	558.2	550.7	543.2	535.8	528.3	522.8
45°	544.7	540.4	536.0	531.6	527.3	520.9	512.6	504.4	496.1	487.8	481.8
47.5°	505.3	500.7	496.1	491.5	486.9	480.4	472.1	463.7	455.4	447.0	440.9
50°	480.4	475.4	470.4	465.5	460.5	453.7	445.1	436.6	427.9	419.4	413.0
52.5°	453.3	448.2	443.1	438.0	432.9	426.3	418.2	410.1	402.0	393.9	387.1
55°	413.3	408.5	403.7	398.9	394.0	387.4	379.0	370.5	362.1	353.7	346.9
57.5°	372.9	367.7	362.6	357.5	352.3	345.6	337.5	329.4	321.3	313.2	306.5
60°	346.9	341.6	336.4	331.1	325.8	319.1	310.9	302.8	294.7	286.6	280.0
62.5°	319.2	314.2	309.2	304.2	299.2	292.5	284.3	276.0	267.8	259.5	253.3
65°	279.8	274.7	269.6	264.5	259.3	252.8	244.8	236.8	228.8	220.9	214.8
67.5°	240.7	235.5	230.4	225.3	220.2	213.8	206.2	198.5	190.8	183.2	177.7
70°	214.1	209.0	203.8	198.8	193.6	187.3	179.8	172.3	164.7	157.2	152.5
72.5°	188.1	183.1	178.1	173.1	168.1	162.0	155.0	147.9	140.9	133.8	129.6
75°	149.1	144.5	140.0	135.5	131.0	125.6	119.2	112.9	106.6	100.2	96.9
77.5°	110.3	106.6	103.1	99.4	95.9	91.5	86.4	81.4	76.3	71.2	68.9
80°	88.1	84.4	80.9	77.2	73.7	69.7	65.5	61.3	57.1	52.9	51.5
82.5°	66.4	63.1	59.9	56.6	53.4	50.3	47.4	44.5	41.6	38.8	38.2
85°	37.3	34.5	31.8	29.2	26.4	24.7	23.9	23.2	22.5	21.7	21.5
87.5°	12.6	11.9	11.4	10.8	10.2	9.9	10.0	10.1	10.2	10.3	10.4
90°	0.6	1.9	3.0	4.2	5.4	6.4	7.5	8.6	9.5	10.6	11.3
92.5°	10.2	9.4	8.6	7.7	6.9	7.0	7.8	8.7	9.6	10.6	11.3
95°	37.6	37.2	36.7	36.4	35.9	32.9	27.3	21.8	16.1	10.6	11.3
97.5°	78.6	79.5	80.3	81.0	81.8	76.7	65.6	54.6	43.5	32.5	28.4
100°	110.3	110.8	111.2	111.6	112.1	112.6	113.2	113.8	114.4	114.9	93.1
102.5°	142.6	143.1	143.7	144.3	144.8	145.3	145.6	146.0	146.3	146.7	142.6
105°	194.2	194.8	195.5	196.0	196.6	196.9	196.9	196.9	196.9	196.9	196.9
107.5°	247.9	247.9	247.9	247.9	247.9	248.1	248.3	248.6	249.0	249.2	249.2
110°	282.8	282.8	282.8	282.8	282.8	282.9	283.2	283.6	283.8	284.1	283.7



TEST NUMBER: P333666-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	315.6	315.9	316.3	316.6	317.0	317.3	317.4	317.6	317.8	318.0	317.4
115°	364.7	365.4	366.2	366.9	367.7	368.1	368.3	368.4	368.5	368.7	368.1
117.5°	415.6	415.5	415.5	415.5	415.4	415.7	416.3	416.9	417.4	417.9	417.2
120°	447.3	447.2	447.0	446.8	446.7	446.8	447.3	447.7	448.2	448.6	448.4
122.5°	475.3	475.9	476.4	477.0	477.6	478.0	478.1	478.3	478.6	478.8	478.5
125°	518.7	519.7	520.8	521.7	522.8	523.3	523.3	523.3	523.3	523.3	522.7
127.5°	560.0	560.8	561.5	562.2	562.9	563.3	563.2	563.1	563.0	562.9	562.6
130°	585.4	586.1	586.8	587.6	588.4	588.8	588.9	589.1	589.2	589.3	588.9
132.5°	610.7	611.6	612.5	613.3	614.2	614.5	614.1	613.8	613.5	613.1	613.1
135°	646.8	647.7	648.6	649.5	650.4	650.7	650.4	650.1	649.8	649.5	649.2
137.5°	680.0	680.8	681.5	682.3	683.1	683.3	683.1	682.8	682.5	682.2	682.3
140°	701.7	702.0	702.3	702.6	702.8	702.9	702.8	702.7	702.5	702.3	702.7
142.5°	721.2	721.4	721.6	721.8	721.9	722.1	722.4	722.6	722.7	723.0	723.0
145°	749.9	750.2	750.6	750.8	751.1	751.3	751.3	751.3	751.3	751.3	751.4
147.5°	775.1	775.0	774.9	774.9	774.8	774.9	775.1	775.2	775.3	775.5	775.7
150°	790.9	790.6	790.3	790.0	789.7	789.7	790.0	790.3	790.6	790.9	791.2
152.5°	806.2	805.6	804.9	804.3	803.6	803.4	803.8	804.1	804.3	804.6	804.9
155°	825.9	825.0	824.1	823.2	822.4	822.1	822.4	822.7	823.0	823.2	823.7
157.5°	841.1	840.6	840.1	839.5	839.0	838.7	838.7	838.8	838.8	838.8	839.4
160°	851.7	850.8	849.9	849.0	848.2	847.7	847.9	848.1	848.2	848.4	849.0
162.5°	860.1	859.3	858.4	857.5	856.6	856.2	856.4	856.6	856.7	856.8	857.6
165°	871.5	870.6	869.8	868.9	868.0	867.6	867.7	867.9	868.1	868.2	869.1
167.5°	879.9	879.0	878.2	877.3	876.3	875.9	876.1	876.2	876.4	876.6	877.5
170°	884.8	883.7	882.6	881.6	880.6	880.1	880.3	880.5	880.6	880.7	881.9
172.5°	887.9	886.9	885.8	884.8	883.8	883.4	883.7	884.0	884.2	884.5	885.5
175°	891.4	890.5	889.6	888.7	887.8	887.4	887.6	887.7	887.9	888.1	889.2
177.5°	892.9	892.2	891.5	890.8	890.1	889.7	889.9	890.0	890.1	890.3	891.1
180°	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4



TEST NUMBER: P333666-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	897.1	897.1	897.1	897.1	897.1	897.1	897.1	897.1
2.5°	894.0	895.2	896.4	897.0	896.9	896.7	896.6	896.5
5°	888.5	890.0	891.5	892.2	891.8	891.5	891.3	890.9
7.5°	877.4	878.5	879.6	879.9	879.6	879.2	879.0	878.6
10°	868.1	868.5	869.1	869.1	868.5	868.1	867.6	867.2
12.5°	854.9	855.2	855.5	855.3	854.6	854.0	853.3	852.6
15°	833.0	832.9	832.8	832.0	830.6	829.3	828.0	826.5
17.5°	805.8	805.0	804.3	803.3	802.3	801.1	800.0	798.9
20°	785.8	785.0	784.3	783.2	781.9	780.5	779.2	777.8
22.5°	765.9	764.4	762.9	761.6	760.5	759.4	758.3	757.2
25°	733.3	731.3	729.3	727.5	725.9	724.2	722.6	720.9
27.5°	697.9	695.2	692.4	690.3	688.7	687.1	685.5	683.9
30°	672.6	669.1	665.7	663.3	661.9	660.6	659.2	657.9
32.5°	648.0	644.3	640.4	637.7	635.9	634.2	632.5	630.8
35°	609.8	605.5	601.1	597.9	595.8	593.6	591.6	589.4
37.5°	569.9	564.6	559.4	555.7	553.7	551.7	549.7	547.6
40°	543.4	537.7	532.0	528.2	526.5	524.6	522.8	521.0
42.5°	517.4	511.8	506.4	502.3	499.7	497.0	494.4	491.8
45°	475.7	469.8	463.7	459.6	457.4	455.0	452.8	450.6
47.5°	434.6	428.4	422.2	417.9	415.4	412.9	410.4	407.9
50°	406.7	400.4	394.0	389.8	387.5	385.3	383.0	380.8
52.5°	380.3	373.4	366.7	362.1	359.9	357.7	355.3	353.1
55°	340.1	333.3	326.5	322.0	319.6	317.2	314.8	312.4
57.5°	299.9	293.3	286.7	282.2	280.1	277.9	275.9	273.8
60°	273.3	266.7	260.1	255.7	253.4	251.1	248.9	246.6
62.5°	247.2	241.0	234.9	230.7	228.5	226.2	223.9	221.7
65°	208.8	202.8	196.8	192.6	190.4	188.2	185.8	183.6
67.5°	172.2	166.7	161.1	157.5	155.7	153.9	152.0	150.3
70°	147.8	143.2	138.5	135.3	133.5	131.7	129.8	128.0
72.5°	125.3	120.9	116.6	113.9	112.7	111.5	110.3	109.1
75°	93.6	90.3	87.0	84.8	83.8	82.8	81.7	80.6
77.5°	66.6	64.3	62.0	60.5	59.7	58.9	58.1	57.3
80°	50.1	48.8	47.4	46.6	46.3	46.0	45.7	45.4
82.5°	37.5	36.8	36.2	35.8	35.7	35.5	35.3	35.1
85°	21.4	21.2	21.0	21.0	20.8	20.6	20.5	20.3
87.5°	10.5	10.7	10.8	10.9	10.9	10.8	10.8	10.8
90°	12.0	12.8	13.5	14.1	14.5	15.0	15.4	15.9
92.5°	12.0	12.8	13.5	14.0	14.2	14.4	14.6	14.8
95°	12.0	12.8	13.5	13.9	13.9	13.9	13.9	13.9
97.5°	24.3	20.1	16.0	13.9	13.9	13.9	13.9	13.9
100°	71.2	49.3	27.5	16.2	15.6	15.1	14.4	13.9
102.5°	138.4	134.3	130.1	123.1	113.1	103.1	93.1	83.1
105°	196.9	196.9	196.9	196.8	196.7	196.5	196.4	196.3
107.5°	249.3	249.3	249.3	249.1	248.7	248.3	247.8	247.4
110°	283.2	282.8	282.3	282.2	282.3	282.5	282.7	282.8



TEST NUMBER: P333666-940

CATALOG NUMBER: S125RDIW-S610D770U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	316.8	316.3	315.7	315.3	315.1	315.0	314.7	314.5
115°	367.5	366.9	366.3	365.6	364.7	363.8	362.9	362.0
117.5°	416.4	415.7	414.9	414.4	413.9	413.6	413.2	412.9
120°	448.1	447.7	447.5	446.9	446.2	445.5	444.8	444.0
122.5°	478.1	477.9	477.6	477.0	476.2	475.3	474.5	473.6
125°	522.1	521.6	520.9	520.4	520.0	519.5	519.2	518.7
127.5°	562.3	562.0	561.7	561.0	559.8	558.7	557.7	556.6
130°	588.5	588.1	587.6	587.0	586.3	585.6	584.8	584.1
132.5°	613.0	612.9	612.8	612.4	611.6	610.9	610.2	609.5
135°	648.9	648.6	648.4	647.7	646.8	646.0	645.1	644.2
137.5°	682.4	682.4	682.5	682.2	681.4	680.6	679.8	679.1
140°	702.9	703.2	703.6	703.2	702.3	701.5	700.6	699.7
142.5°	723.1	723.2	723.2	722.8	721.9	721.0	720.1	719.3
145°	751.5	751.7	751.8	751.4	750.6	749.7	748.9	748.0
147.5°	775.9	776.1	776.2	775.8	774.8	773.7	772.7	771.6
150°	791.5	791.8	792.1	791.7	790.4	789.3	788.1	786.9
152.5°	805.2	805.5	805.8	805.4	804.3	803.3	802.3	801.2
155°	824.1	824.6	825.0	824.7	823.5	822.3	821.2	819.9
157.5°	839.8	840.3	840.7	840.3	839.2	838.0	836.9	835.7
160°	849.5	850.2	850.7	850.4	849.3	848.1	846.9	845.7
162.5°	858.4	859.3	860.1	859.9	858.6	857.3	856.0	854.7
165°	870.0	870.8	871.7	871.6	870.4	869.2	868.1	866.8
167.5°	878.6	879.7	880.7	880.7	879.3	878.0	876.6	875.3
170°	883.1	884.3	885.5	885.4	884.0	882.7	881.4	880.1
172.5°	886.5	887.6	888.7	888.5	887.3	885.9	884.6	883.2
175°	890.4	891.5	892.7	892.6	891.4	890.0	888.7	887.3
177.5°	891.9	892.7	893.6	893.5	892.5	891.6	890.6	889.7
180°	891.4	891.4	891.4	891.4	891.4	891.4	891.4	891.4

(END OF REPORT)