

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224822

Luminaire Tested: **LSRWM2B10FL409024D010 2LBDL*B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224822
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14834)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSRWM2B10FL409024D010 2LBDL*B
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 679.1 lumens
Efficiency: N/A
Efficacy: 65.9 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224822

CATALOG NUMBER: LSRWM2B10FL409024D010 2LBDL*B

Luminous Intensity Polar Plot





TEST NUMBER: P224822

CATALOG NUMBER: LSRWM2B10FL409024D010 2LBDL*B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	106	103	100	108	104	101	99	101	99	96	98	96	94	96	94	92	91		
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87		
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83		
5	98	91	86	83	96	90	86	82	88	85	82	87	84	81	85	83	80	79		
6	94	87	82	79	93	86	82	78	85	81	78	84	80	77	82	79	77	76		
7	91	83	78	75	90	83	78	75	81	77	74	80	77	74	79	76	74	72		
8	87	80	75	72	86	79	75	71	78	74	71	77	74	71	76	73	71	69		
9	84	77	72	69	83	76	72	68	75	71	68	74	71	68	74	70	68	67		
10	82	74	69	66	81	73	69	66	73	68	65	72	68	65	71	68	65	64		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	614447
5°	603768
10°	538614
15°	425712
20°	283886
25°	164673
30°	82432
35°	38775
40°	15169
45°	6738
50°	3194
55°	1756
60°	697
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224822

CATALOG NUMBER: LSRWM2B10FL409024D010 2LBDL*B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.3	21.0
10°-20°	287.4	42.3
20°-30°	180.8	26.6
30°-40°	55.3	8.1
40°-50°	10.8	1.6
50°-60°	2.4	0.4
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	610.5	89.9
0°-40°	665.7	98.0
0°-60°	679.0	100.0
0°-90°	679.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	679.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1586	
5°	1553	142
15°	1062	287
25°	385	181
35°	82	55
45°	12	11
55°	3	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224822

CATALOG NUMBER: LSRWM2B10FL409024D010 2LBDL*B

CANDELA DISTRIBUTION (FULL):

0°	
0°	1586.3
2.5°	1582.8
5°	1552.8
7.5°	1482.2
10°	1369.4
12.5°	1228.3
15°	1061.6
17.5°	876.5
20°	688.7
22.5°	528.2
25°	385.3
27.5°	271.6
30°	184.3
32.5°	124.3
35°	82.0
37.5°	50.3
40°	30.0
42.5°	19.4
45°	12.3
47.5°	7.9
50°	5.3
52.5°	3.5
55°	2.6
57.5°	1.8
60°	0.9
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)