

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224449

Luminaire Tested: **LSRWM2B10FL409024D010 2LBDL*WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224449
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSRWM2B10FL409024D010 2LBDL*WH
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH WHEAT HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 706.2 lumens
Efficiency: N/A
Efficacy: 68.6 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224449

CATALOG NUMBER: LSRWM2B10FL409024D010 2LBDL*WH

Luminous Intensity Polar Plot





TEST NUMBER: P224449

CATALOG NUMBER: LSRWM2B10FL409024D010 2LBDL*WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95																											
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91																											
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	87																											
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	82																											
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79																											
6	94	87	82	78	93	86	81	78	85	80	77	83	80	77	82	79	76	75																											
7	90	83	78	75	89	82	78	74	81	77	74	80	76	74	79	76	73	72																											
8	87	79	75	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69																											
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66																											
10	81	73	69	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	651555
5°	626903
10°	551791
15°	433412
20°	294685
25°	172067
30°	87620
35°	41470
40°	18102
45°	7833
50°	3796
55°	2431
60°	1394
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224449

CATALOG NUMBER: LSRWM2B10FL409024D010 2LBDL*WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.3	20.9
10°-20°	293.9	41.6
20°-30°	188.7	26.7
30°-40°	59.9	8.5
40°-50°	12.8	1.8
50°-60°	3.3	0.5
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	629.8	89.2
0°-40°	689.7	97.7
0°-60°	705.7	99.9
0°-90°	706.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	706.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1682	
5°	1612	147
15°	1081	294
25°	403	189
35°	88	60
45°	14	13
55°	4	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224449

CATALOG NUMBER: LSRWM2B10FL409024D010 2LBDL*WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1682.1
2.5°	1666.0
5°	1612.3
7.5°	1524.6
10°	1402.9
12.5°	1254.4
15°	1080.8
17.5°	895.6
20°	714.9
22.5°	545.8
25°	402.6
27.5°	287.2
30°	195.9
32.5°	131.5
35°	87.7
37.5°	58.2
40°	35.8
42.5°	22.4
45°	14.3
47.5°	9.8
50°	6.3
52.5°	4.5
55°	3.6
57.5°	2.7
60°	1.8
62.5°	0.9
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)