

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223927

Luminaire Tested: **LSSQWM2B10SP159024D010 2LBDLC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223927
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (150)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B10SP159024D010 2LBDLC*MMS
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
SPOT OPTIC
LENSED CAST ROUND TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 364.2 lumens
Efficiency: N/A
Efficacy: 35.4 lumens/watt
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.23
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223927

CATALOG NUMBER: LSSQWM2B10SP159024D010 2LBDLC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P223927

CATALOG NUMBER: LSSQWM2B10SP159024D010 2LBDLC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | 100 |
| 1 | 116 | 114 | 112 | 111 | 113 | 112 | 110 | 109 | 108 | 107 | 106 | 104 | 103 | 103 | 101 | 100 | 100 | 98 | | | 98 |
| 2 | 113 | 110 | 107 | 105 | 111 | 108 | 106 | 104 | 105 | 103 | 102 | 102 | 101 | 100 | 100 | 99 | 98 | 96 | | | 96 |
| 3 | 110 | 106 | 103 | 101 | 108 | 105 | 102 | 100 | 102 | 100 | 98 | 100 | 99 | 97 | 98 | 97 | 96 | 94 | | | 94 |
| 4 | 108 | 103 | 100 | 97 | 106 | 102 | 99 | 97 | 100 | 98 | 96 | 98 | 96 | 95 | 97 | 95 | 94 | 93 | | | 93 |
| 5 | 105 | 101 | 97 | 95 | 104 | 100 | 97 | 94 | 98 | 96 | 94 | 97 | 95 | 93 | 95 | 94 | 92 | 91 | | | 91 |
| 6 | 103 | 98 | 95 | 93 | 102 | 98 | 95 | 92 | 96 | 94 | 92 | 95 | 93 | 91 | 94 | 92 | 91 | 90 | | | 90 |
| 7 | 101 | 96 | 93 | 91 | 100 | 96 | 93 | 90 | 95 | 92 | 90 | 94 | 91 | 90 | 93 | 91 | 89 | 88 | | | 88 |
| 8 | 100 | 94 | 91 | 89 | 99 | 94 | 91 | 89 | 93 | 90 | 89 | 92 | 90 | 88 | 92 | 90 | 88 | 87 | | | 87 |
| 9 | 98 | 93 | 90 | 88 | 97 | 92 | 89 | 87 | 92 | 89 | 87 | 91 | 89 | 87 | 90 | 88 | 87 | 86 | | | 86 |
| 10 | 96 | 91 | 88 | 86 | 96 | 91 | 88 | 86 | 90 | 88 | 86 | 90 | 87 | 86 | 89 | 87 | 86 | 85 | | | 85 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 1750068 |
| 5° | 1265122 |
| 10° | 368306 |
| 15° | 129246 |
| 20° | 55318 |
| 25° | 24874 |
| 30° | 9616 |
| 35° | 4776 |
| 40° | 3186 |
| 45° | 2082 |
| 50° | 1145 |
| 55° | 878 |
| 60° | 465 |
| 65° | 0 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P223927

CATALOG NUMBER: LSSQWM2B10SP159024D010 2LBDLC*MMS

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 230.2 | 63.2 |
| 10°-20° | 93.7 | 25.7 |
| 20°-30° | 28.7 | 7.9 |
| 30°-40° | 7.1 | 1.9 |
| 40°-50° | 3.0 | 0.8 |
| 50°-60° | 1.3 | 0.4 |
| 60°-70° | 0.2 | 0.1 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 352.7 | 96.8 |
| 0°-40° | 359.7 | 98.8 |
| 0°-60° | 364.0 | 99.9 |
| 0°-90° | 364.2 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 364.2 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 4518 | |
| 5° | 3254 | 230 |
| 15° | 322 | 94 |
| 25° | 58 | 29 |
| 35° | 10 | 7 |
| 45° | 4 | 3 |
| 55° | 1 | 1 |
| 65° | 0 | 0 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P223927

CATALOG NUMBER: LSSQWM2B10SP159024D010 2LBDLC*MMS

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 4518.1 |
| 1° | 4449.1 |
| 2° | 4280.6 |
| 3° | 4012.2 |
| 4° | 3661.4 |
| 5° | 3253.7 |
| 6° | 2794.0 |
| 7° | 2295.1 |
| 8° | 1789.2 |
| 9° | 1316.3 |
| 10° | 936.4 |
| 11° | 671.1 |
| 12° | 504.6 |
| 13° | 410.9 |
| 14° | 359.6 |
| 15° | 322.3 |
| 17.5° | 198.8 |
| 20° | 134.2 |
| 22.5° | 89.9 |
| 25° | 58.2 |
| 27.5° | 35.5 |
| 30° | 21.5 |
| 32.5° | 13.9 |
| 35° | 10.1 |
| 37.5° | 8.2 |
| 40° | 6.3 |
| 42.5° | 5.1 |
| 45° | 3.8 |
| 47.5° | 2.5 |
| 50° | 1.9 |
| 52.5° | 1.9 |
| 55° | 1.3 |
| 57.5° | 1.3 |
| 60° | 0.6 |
| 62.5° | 0.6 |
| 65° | 0.0 |
| 67.5° | 0.0 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |



TEST NUMBER: P223927

CATALOG NUMBER: LSSQWM2B10SP159024D010 2LBDLC*MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







| | | |
|-------|--|-----|
| 85° | | 0.0 |
| 87.5° | | 0.0 |



(END OF REPORT)