

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225001

Luminaire Tested: **LSR2B10FL408035D010 2LBDL*LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225001
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (152)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B10FL408035D010 2LBDL*LI
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 978.0 lumens
Efficiency: N/A
Efficacy: 95.0 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.58
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225001

CATALOG NUMBER: LSR2B10FL408035D010 2LBDL*LI

Luminous Intensity Polar Plot





TEST NUMBER: P225001

CATALOG NUMBER: LSR2B10FL408035D010 2LBDL*LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	105	103	102	101	100	99	98	97	96	96	96	96
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	91	91
3	106	101	96	93	104	99	95	92	97	94	91	94	92	90	92	90	88	87	87	87	87
4	102	96	91	88	100	95	90	87	93	89	86	91	88	85	89	86	84	83	83	83	83
5	98	91	86	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79	79	79	79
6	94	87	82	79	93	86	82	79	85	81	78	84	80	78	83	79	77	76	76	76	76
7	91	83	79	75	90	83	78	75	82	78	75	81	77	74	80	76	74	73	73	73	73
8	88	80	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	70	70	70	70
9	85	77	72	69	84	76	72	69	76	71	69	75	71	68	74	71	68	67	67	67	67
10	82	74	69	66	81	74	69	66	73	69	66	72	68	66	72	68	66	65	65	65	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	938152
5°	901531
10°	784794
15°	612824
20°	407547
25°	233397
30°	116021
35°	53339
40°	21389
45°	9805
50°	4520
55°	2566
60°	1472
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225001

CATALOG NUMBER: LSR2B10FL408035D010 2LBDL*LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	211.0	21.6
10°-20°	414.4	42.4
20°-30°	256.5	26.2
30°-40°	76.8	7.8
40°-50°	15.4	1.6
50°-60°	3.7	0.4
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	881.9	90.2
0°-40°	958.7	98.0
0°-60°	977.8	100.0
0°-90°	978.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	978.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2422	
5°	2319	211
15°	1528	414
25°	546	256
35°	113	77
45°	18	15
55°	4	4
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225001

CATALOG NUMBER: LSR2B10FL408035D010 2LBDL*LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2422.0
1°	2408.9
2°	2396.6
3°	2372.2
4°	2349.6
5°	2318.6
6°	2276.3
7°	2222.8
8°	2154.1
9°	2076.1
10°	1995.3
11°	1911.7
12°	1822.4
13°	1729.3
14°	1629.7
15°	1528.2
17.5°	1260.3
20°	988.7
22.5°	748.1
25°	546.1
27.5°	383.5
30°	259.4
32.5°	171.1
35°	112.8
37.5°	70.5
40°	42.3
42.5°	27.3
45°	17.9
47.5°	11.3
50°	7.5
52.5°	5.6
55°	3.8
57.5°	2.8
60°	1.9
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P225001

CATALOG NUMBER: LSR2B10FL408035D010 2LBDL*LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)