

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223299

Luminaire Tested: **LSSQ2B10NFL258035D010 2LBDC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223299
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B10NFL258035D010 2LBDC*MB
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
NARROW FLOOD OPTIC
CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1014.0 lumens
Efficiency: N/A
Efficacy: 98.4 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223299

CATALOG NUMBER: LSSQ2B10NFL258035D010 2LBDC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P223299

CATALOG NUMBER: LSSQ2B10NFL258035D010 2LBDC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	97
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	96	95
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95	95	94	92
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92	92	91	90
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90	89	88	86
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88	87	86	84
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86	85	84	82
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	86	85	84	83	82	80
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82	81	80	79
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80	79	78	77
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	78	77	76	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2330157
5°	2151489
10°	1456273
15°	495448
20°	181989
25°	96462
30°	49602
35°	23123
40°	7585
45°	3835
50°	1808
55°	675
60°	775
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223299

CATALOG NUMBER: LSSQ2B10NFL258035D010 2LBDC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	470.7	46.4
10°-20°	395.8	39.0
20°-30°	108.6	10.7
30°-40°	31.7	3.1
40°-50°	5.9	0.6
50°-60°	1.3	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	975.0	96.2
0°-40°	1006.7	99.3
0°-60°	1013.9	100.0
0°-90°	1014.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1014.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6016	
5°	5533	471
15°	1236	396
25°	226	109
35°	49	32
45°	7	6
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223299

CATALOG NUMBER: LSSQ2B10NFL258035D010 2LBDC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	6015.7
1°	5980.7
2°	5918.8
3°	5829.9
4°	5708.1
5°	5533.3
6°	5294.6
7°	4995.9
8°	4631.4
9°	4200.9
10°	3702.5
11°	3156.2
12°	2587.9
13°	2045.5
14°	1583.1
15°	1235.5
17.5°	697.2
20°	441.5
22.5°	314.6
25°	225.7
27.5°	159.8
30°	110.9
32.5°	77.9
35°	48.9
37.5°	20.0
40°	15.0
42.5°	11.0
45°	7.0
47.5°	4.0
50°	3.0
52.5°	2.0
55°	1.0
57.5°	1.0
60°	1.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223299

CATALOG NUMBER: LSSQ2B10NFL258035D010 2LBDC*MB

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)