

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224661

Luminaire Tested: **LSR2B10FL409035D010 2LBDLC\*MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P224661  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR2B10FL409035D010 2LBDLC\*MW  
Description: 1000 Lumen, 2inch Portfolio LED Cylinder  
FLOOD OPTIC  
LENSED CAST ROUND TRIM WITH MATTE WHITE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 795.1 lumens  
Efficiency: N/A  
Efficacy: 77.2 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P224661

CATALOG NUMBER: LSR2B10FL409035D010 2LBDLC\**MW*

### Luminous Intensity Polar Plot





TEST NUMBER: P224661

CATALOG NUMBER: LSR2B10FL409035D010 2LBDLC\*MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91			91
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86			86
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82			82
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79			79
6	94	87	82	78	93	86	81	78	84	80	77	83	80	77	82	79	76	75			75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72			72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69			69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66			66
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64			64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	719921
5°	706807
10°	628292
15°	494125
20°	328816
25°	188778
30°	95358
35°	44875
40°	18052
45°	8929
50°	4941
55°	3444
60°	3176
65°	1833
70°	2265
75°	1497
80°	2231
85°	0



TEST NUMBER: P224661

CATALOG NUMBER: LSR2B10FL409035D010 2LBDLC\*MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	166.5	20.9
10°-20°	333.8	42.0
20°-30°	207.7	26.1
30°-40°	63.8	8.0
40°-50°	14.0	1.8
50°-60°	5.0	0.6
60°-70°	2.5	0.3
70°-80°	1.4	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	707.9	89.0
0°-40°	771.8	97.1
0°-60°	790.8	99.5
0°-90°	795.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	795.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1859	
5°	1818	166
15°	1232	334
25°	442	208
35°	95	64
45°	16	14
55°	5	5
65°	2	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P224661

CATALOG NUMBER: LSR2B10FL409035D010 2LBDLC\*MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1858.6
2.5°	1850.4
5°	1817.8
7.5°	1735.1
10°	1597.4
12.5°	1432.2
15°	1232.2
17.5°	1013.9
20°	797.7
22.5°	604.9
25°	441.7
27.5°	311.1
30°	213.2
32.5°	143.8
35°	94.9
37.5°	57.1
40°	35.7
42.5°	24.5
45°	16.3
47.5°	11.2
50°	8.2
52.5°	7.1
55°	5.1
57.5°	4.1
60°	4.1
62.5°	3.1
65°	2.0
67.5°	2.0
70°	2.0
72.5°	2.0
75°	1.0
77.5°	1.0
80°	1.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)