

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225044

Luminaire Tested: **LSSQWM2B10FL409035D010 2LBD*WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225044
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14830)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B10FL409035D010 2LBD*WMH
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH WHEAT METALLIC HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 804.5 lumens
Efficiency: N/A
Efficacy: 78.1 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225044

CATALOG NUMBER: LSSQWM2B10FL409035D010 2LBD*WMH

Luminous Intensity Polar Plot





TEST NUMBER: P225044

CATALOG NUMBER: LSSQWM2B10FL409035D010 2LBD*WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95				95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91				91
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	87				87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	83				83
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79				79
6	94	87	82	78	93	86	81	78	85	81	77	83	80	77	82	79	77	75				75
7	91	83	78	75	89	82	78	74	81	77	74	80	76	74	79	76	73	72				72
8	87	79	75	71	86	79	74	71	78	74	71	77	73	71	76	73	70	69				69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66				66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64				64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	730031
5°	714972
10°	633365
15°	497734
20°	334628
25°	194419
30°	97147
35°	45820
40°	21642
45°	9477
50°	4941
55°	2769
60°	1549
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225044

CATALOG NUMBER: LSSQWM2B10FL409035D010 2LBD*WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.2	20.9
10°-20°	336.6	41.8
20°-30°	212.8	26.5
30°-40°	66.6	8.3
40°-50°	15.4	1.9
50°-60°	4.1	0.5
60°-70°	0.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	717.7	89.2
0°-40°	784.2	97.5
0°-60°	803.8	99.9
0°-90°	804.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	804.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1885	
5°	1839	168
15°	1241	337
25°	455	213
35°	97	67
45°	17	15
55°	4	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225044

CATALOG NUMBER: LSSQWM2B10FL409035D010 2LBD*WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1884.7
2.5°	1875.5
5°	1838.8
7.5°	1752.1
10°	1610.3
12.5°	1442.1
15°	1241.2
17.5°	1021.9
20°	811.8
22.5°	618.0
25°	454.9
27.5°	321.3
30°	217.2
32.5°	144.8
35°	96.9
37.5°	65.3
40°	42.8
42.5°	26.5
45°	17.3
47.5°	12.2
50°	8.2
52.5°	6.1
55°	4.1
57.5°	3.1
60°	2.0
62.5°	2.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)