

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223759

Luminaire Tested: **LSSQWM2B10SP159035D010 2LBD\*WH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P223759  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA ( 150)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSSQWM2B10SP159035D010 2LBD\*WH  
Description: 1000 Lumen, 2inch Portfolio LED Cylinder  
SPOT OPTIC  
SPUN ROUND TRIM WITH WHEAT HAZE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 477.6 lumens  
Efficiency: N/A  
Efficacy: 46.4 lumens/watt  
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.23  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P223759

CATALOG NUMBER: LSSQWM2B10SP159035D010 2LBD\*WH

### Luminous Intensity Polar Plot





TEST NUMBER: P223759

CATALOG NUMBER: LSSQWM2B10SP159035D010 2LBD\*WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98			98																
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	96			96																
3	110	106	103	101	108	105	102	100	102	100	98	100	98	97	98	97	96	94			94																
4	108	103	100	97	106	102	99	97	100	98	96	98	96	95	97	95	94	93			93																
5	105	101	97	95	104	100	97	94	98	96	94	97	95	93	95	94	92	91			91																
6	103	98	95	93	102	98	95	92	96	94	92	95	93	91	94	92	91	90			90																
7	101	96	93	91	100	96	93	90	95	92	90	94	91	90	93	91	89	88			88																
8	100	94	91	89	99	94	91	89	93	90	89	92	90	88	92	90	88	87			87																
9	98	93	90	88	97	92	89	87	92	89	87	91	89	87	90	88	87	86			86																
10	96	91	88	86	96	91	88	86	90	88	86	90	87	86	89	87	86	85			85																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2294948
5°	1659041
10°	482999
15°	169467
20°	72548
25°	32653
30°	12613
35°	6289
40°	4197
45°	2739
50°	1507
55°	1148
60°	620
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223759

CATALOG NUMBER: LSSQWM2B10SP159035D010 2LBD\*WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	301.9	63.2
10°-20°	122.8	25.7
20°-30°	37.7	7.9
30°-40°	9.3	1.9
40°-50°	3.9	0.8
50°-60°	1.7	0.4
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	462.5	96.8
0°-40°	471.8	98.8
0°-60°	477.3	99.9
0°-90°	477.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	477.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5925	
5°	4267	302
15°	423	123
25°	76	38
35°	13	9
45°	5	4
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223759

CATALOG NUMBER: LSSQWM2B10SP159035D010 2LBD\*WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5924.8
1°	5834.3
2°	5613.5
3°	5261.5
4°	4801.5
5°	4266.8
6°	3664.0
7°	3009.8
8°	2346.4
9°	1726.1
10°	1228.0
11°	880.1
12°	661.7
13°	538.8
14°	471.6
15°	422.6
17.5°	260.7
20°	176.0
22.5°	117.9
25°	76.4
27.5°	46.5
30°	28.2
32.5°	18.3
35°	13.3
37.5°	10.8
40°	8.3
42.5°	6.6
45°	5.0
47.5°	3.3
50°	2.5
52.5°	2.5
55°	1.7
57.5°	1.7
60°	0.8
62.5°	0.8
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223759

CATALOG NUMBER: LSSQWM2B10SP159035D010 2LBD\*WH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)