

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223994

Luminaire Tested: **LSRWM2B10SP158050D010 2LBDC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223994
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (150)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSRWM2B10SP158050D010 2LBDC*MMS
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
SPOT OPTIC
CAST ROUND TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 620.4 lumens
Efficiency: N/A
Efficacy: 60.2 lumens/watt
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.23
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223994

CATALOG NUMBER: LSRWM2B10SP158050D010 2LBDC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P223994

CATALOG NUMBER: LSRWM2B10SP158050D010 2LBDC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98	98	98	98
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	96	96	96	96
3	110	106	103	101	108	105	102	100	102	100	98	100	98	97	98	97	96	94	94	94	94
4	108	103	100	97	106	102	99	97	100	98	96	98	96	95	97	95	94	93	93	93	93
5	105	101	97	95	104	100	97	94	98	96	94	97	95	93	95	94	92	91	91	91	91
6	103	98	95	93	102	98	95	92	96	94	92	95	93	91	94	92	91	90	90	90	90
7	101	96	93	91	100	96	93	90	95	92	90	94	91	90	93	91	89	88	88	88	88
8	100	94	91	89	99	94	91	89	93	90	89	92	90	88	92	90	88	87	87	87	87
9	98	93	90	88	97	92	89	87	92	89	87	91	89	87	90	88	87	86	86	86	86
10	96	91	88	86	96	91	88	86	90	88	86	90	87	86	89	87	86	85	85	85	85

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2981131
5°	2155066
10°	627387
15°	220155
20°	94230
25°	42397
30°	16415
35°	8181
40°	5461
45°	3561
50°	1928
55°	1486
60°	852
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223994

CATALOG NUMBER: LSRWM2B10SP158050D010 2LBDC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	392.2	63.2
10°-20°	159.6	25.7
20°-30°	49.0	7.9
30°-40°	12.1	1.9
40°-50°	5.0	0.8
50°-60°	2.2	0.3
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	600.7	96.8
0°-40°	612.8	98.8
0°-60°	620.0	99.9
0°-90°	620.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	620.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7696	
5°	5542	392
15°	549	160
25°	99	49
35°	17	12
45°	6	5
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223994

CATALOG NUMBER: LSRWM2B10SP158050D010 2LBDC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	7696.3
1°	7578.8
2°	7291.9
3°	6834.6
4°	6237.1
5°	5542.5
6°	4759.5
7°	3909.7
8°	3047.9
9°	2242.3
10°	1595.1
11°	1143.2
12°	859.6
13°	700.0
14°	612.6
15°	549.0
17.5°	338.7
20°	228.6
22.5°	153.2
25°	99.2
27.5°	60.4
30°	36.7
32.5°	23.7
35°	17.3
37.5°	14.0
40°	10.8
42.5°	8.6
45°	6.5
47.5°	4.3
50°	3.2
52.5°	3.2
55°	2.2
57.5°	2.2
60°	1.1
62.5°	1.1
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223994

CATALOG NUMBER: LSRWM2B10SP158050D010 2LBDC*MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)