

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P436694

Luminaire Tested: **LSSQ1B08209027D010TExxSL**

Issue Date: 12/2/2020

Test Information

Test Method: LM-41-14
Report Number: P436694
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2010-014-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 12/2/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSSQ1B08209027D010TExxSL
Description: PORTFOLIO 1INCH CYLINDER, 20 DEG REFLECTOR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 996.0 lumens
Efficiency: N/A
Efficacy: 60.4 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.32
Luminous Opening: Rectangular (W 0.08' x L: 0.08' x H: 0')
CIE Type: Direct


Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P436694

CATALOG NUMBER: LSSQ1B08209027D010TExxSL

Luminous Intensity Polar Plot





TEST NUMBER: P436694

CATALOG NUMBER: LSSQ1B08209027D010TExxSL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	113	111	109	112	111	109	107	107	105	104	103	102	101	99	99	98	96			
2	111	107	104	102	109	106	103	101	103	100	98	100	98	96	97	96	94	93			
3	108	103	99	96	106	102	98	96	99	96	94	97	95	93	95	93	91	90			
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	93	90	89	87			
5	102	96	92	89	100	95	91	88	93	90	88	92	89	87	90	88	86	85			
6	99	93	89	86	98	92	88	86	91	88	85	90	87	85	89	86	84	83			
7	96	90	86	83	95	90	86	83	89	85	83	88	85	82	87	84	82	81			
8	94	88	84	81	93	87	84	81	87	83	81	86	83	81	85	82	80	79			
9	92	86	82	79	91	85	82	79	85	81	79	84	81	79	83	81	79	78			
10	90	84	80	78	89	83	80	77	83	80	77	82	79	77	82	79	77	76			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	11094379
5°	8985006
10°	4684860
15°	2081685
20°	941119
25°	301701
30°	84797
35°	57223
40°	44873
45°	41984
50°	43754
55°	43586
60°	46874
65°	44366
70°	45684
75°	48296
80°	44990
85°	53782



TEST NUMBER: P436694

CATALOG NUMBER: LSSQ1B08209027D010TExxSL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	452.9	45.5
10°-20°	374.5	37.6
20°-30°	96.8	9.7
30°-40°	19.4	1.9
40°-50°	15.1	1.5
50°-60°	14.4	1.4
60°-70°	12.0	1.2
70°-80°	8.0	0.8
80°-90°	2.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	924.2	92.8
0°-40°	943.6	94.7
0°-60°	973.1	97.7
0°-90°	996.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	996.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7100	
5°	5729	453
15°	1287	374
25°	175	97
35°	30	19
45°	19	15
55°	16	14
65°	12	12
75°	8	8
85°	3	3
90°	0	



TEST NUMBER: P436694

CATALOG NUMBER: LSSQ1B08209027D010TExxSL

CANDELA DISTRIBUTION (FULL):

	0°
0°	7100.5
1°	7006.5
2°	6813.5
3°	6545.5
4°	6187.5
5°	5728.6
6°	5216.6
7°	4663.7
8°	4062.7
9°	3470.7
10°	2952.8
11°	2501.8
12°	2119.8
13°	1792.9
14°	1517.9
15°	1286.9
16°	1087.9
17°	924.9
18°	784.9
19°	666.0
20°	566.0
21°	477.0
22°	398.0
23°	319.0
24°	241.0
25°	175.0
26°	125.0
27°	91.0
28°	69.0
29°	56.0
30°	47.0
32.5°	36.0
35°	30.0
37.5°	25.0
40°	22.0
42.5°	21.0
45°	19.0
47.5°	18.0
50°	18.0
52.5°	17.0
55°	16.0
57.5°	15.0
60°	15.0



TEST NUMBER: P436694

CATALOG NUMBER: LSSQ1B08209027D010TExxSL

CANDELA DISTRIBUTION (continued):

	0°
67.5°	11.0
70°	10.0
72.5°	9.0
75°	8.0
77.5°	6.0
80°	5.0
82.5°	4.0
85°	3.0
87.5°	1.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







62.5°		13.0
65°		12.0



(END OF REPORT)