

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P436702

Luminaire Tested: **LSSQ1B08209030D010TExxMW**

Issue Date: 12/2/2020

Test Information

Test Method: LM-41-14
Report Number: P436702
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2010-014-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 12/2/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSSQ1B08209030D010TExxMW
Description: PORTFOLIO 1INCH CYLINDER, 20 DEG REFLECTOR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1002.0 lumens
Efficiency: N/A
Efficacy: 60.7 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.32
Luminous Opening: Rectangular (W 0.08' x L: 0.08' x H: 0')
CIE Type: Direct


Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P436702

CATALOG NUMBER: LSSQ1B08209030D010TExxMW

Luminous Intensity Polar Plot





TEST NUMBER: P436702

CATALOG NUMBER: LSSQ1B08209030D010TExxMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	111	109	107	107	105	104	103	102	101	99	99	98	96																			
2	111	107	104	102	109	106	103	101	103	100	98	100	98	96	97	96	94	93																			
3	108	103	99	96	106	102	98	96	99	96	94	97	95	93	95	93	91	90																			
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	93	90	89	87																			
5	102	96	92	89	100	95	91	88	93	90	88	92	89	87	90	88	86	85																			
6	99	93	89	86	98	92	88	86	91	88	85	90	87	85	89	86	84	83																			
7	96	90	86	83	95	90	86	83	89	85	83	88	85	82	87	84	82	81																			
8	94	88	84	81	93	87	84	81	87	83	81	86	83	81	85	82	80	79																			
9	92	86	82	79	91	85	82	79	85	81	79	84	81	79	83	81	79	78																			
10	90	84	80	78	89	84	80	77	83	80	77	82	79	77	82	79	77	76																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	11161097
5°	9039117
10°	4713102
15°	2094303
20°	946773
25°	303425
30°	85338
35°	57605
40°	45077
45°	42205
50°	43997
55°	43858
60°	47187
65°	44735
70°	46141
75°	48296
80°	44990
85°	53782



TEST NUMBER: P436702

CATALOG NUMBER: LSSQ1B08209030D010TExxMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	455.6	45.5
10°-20°	376.7	37.6
20°-30°	97.4	9.7
30°-40°	19.5	1.9
40°-50°	15.1	1.5
50°-60°	14.5	1.4
60°-70°	12.1	1.2
70°-80°	8.1	0.8
80°-90°	2.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	929.8	92.8
0°-40°	949.3	94.7
0°-60°	978.9	97.7
0°-90°	1002.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1002.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7143	
5°	5763	456
15°	1295	377
25°	176	97
35°	30	20
45°	19	15
55°	16	15
65°	12	12
75°	8	8
85°	3	3
90°	0	



TEST NUMBER: P436702

CATALOG NUMBER: LSSQ1B08209030D010TExxMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	7143.2
1°	7048.7
2°	6854.5
3°	6584.9
4°	6224.8
5°	5763.1
6°	5248.0
7°	4691.7
8°	4087.2
9°	3491.7
10°	2970.6
11°	2516.9
12°	2132.6
13°	1803.7
14°	1527.0
15°	1294.7
16°	1094.5
17°	930.5
18°	789.7
19°	670.0
20°	569.4
21°	479.8
22°	400.4
23°	320.9
24°	242.4
25°	176.0
26°	125.7
27°	91.5
28°	69.4
29°	56.3
30°	47.3
32.5°	36.2
35°	30.2
37.5°	25.1
40°	22.1
42.5°	21.1
45°	19.1
47.5°	18.1
50°	18.1
52.5°	17.1
55°	16.1
57.5°	15.1
60°	15.1



TEST NUMBER: P436702

CATALOG NUMBER: LSSQ1B08209030D010TExxMW

CANDELA DISTRIBUTION (continued):

	0°
67.5°	11.1
70°	10.1
72.5°	9.1
75°	8.0
77.5°	6.0
80°	5.0
82.5°	4.0
85°	3.0
87.5°	1.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







62.5°		13.1
65°		12.1



(END OF REPORT)