

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225137

Luminaire Tested: **LSR2B10FL409050D010 2LBD*GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225137
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B10FL409050D010 2LBD*GPH
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH GRAPHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 908.6 lumens
Efficiency: N/A
Efficacy: 88.2 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225137

CATALOG NUMBER: LSR2B10FL409050D010 2LBD*GPH

Luminous Intensity Polar Plot





TEST NUMBER: P225137

CATALOG NUMBER: LSR2B10FL409050D010 2LBD*GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95																											
2	110	106	102	100	108	104	101	98	101	99	96	98	96	94	95	94	92	91																											
3	106	100	96	93	104	99	95	92	96	93	91	94	92	89	92	90	88	87																											
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83																											
5	98	91	86	83	96	90	85	82	88	84	81	87	83	81	85	82	80	79																											
6	94	87	82	78	93	86	81	78	85	81	78	83	80	77	82	79	77	75																											
7	91	83	78	75	89	82	78	74	81	77	74	80	76	74	79	76	73	72																											
8	87	80	75	71	86	79	74	71	78	74	71	77	73	71	76	73	70	69																											
9	84	76	72	68	83	76	71	68	75	71	68	74	70	68	73	70	68	66																											
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	824234
5°	807591
10°	717576
15°	563018
20°	378652
25°	220319
30°	110341
35°	51495
40°	24018
45°	10134
50°	4881
55°	3106
60°	1782
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225137

CATALOG NUMBER: LSR2B10FL409050D010 2LBD*GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	190.1	20.9
10°-20°	381.1	41.9
20°-30°	241.0	26.5
30°-40°	75.0	8.3
40°-50°	16.6	1.8
50°-60°	4.2	0.5
60°-70°	0.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	812.2	89.4
0°-40°	887.1	97.6
0°-60°	908.0	99.9
0°-90°	908.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	908.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2128	
5°	2077	190
15°	1404	381
25°	516	241
35°	109	75
45°	18	17
55°	5	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225137

CATALOG NUMBER: LSR2B10FL409050D010 2LBD*GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2127.9
2.5°	2118.7
5°	2077.0
7.5°	1978.5
10°	1824.4
12.5°	1629.8
15°	1404.0
17.5°	1159.5
20°	918.6
22.5°	702.0
25°	515.5
27.5°	361.4
30°	246.7
32.5°	163.3
35°	108.9
37.5°	73.0
40°	47.5
42.5°	29.0
45°	18.5
47.5°	12.7
50°	8.1
52.5°	5.8
55°	4.6
57.5°	3.5
60°	2.3
62.5°	1.2
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)