

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225454

Luminaire Tested: **LSSQWM2B10FL409050D010 2LBDLC\*MB**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P225454  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14833)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSSQWM2B10FL409050D010 2LBDLC\*MB  
Description: 1000 Lumen, 2inch Portfolio LED Cylinder  
FLOOD OPTIC  
LENSED CAST ROUND TRIM WITH MATTE BLACK FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 823.2 lumens  
Efficiency: N/A  
Efficacy: 79.9 lumens/watt  
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.6  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P225454

CATALOG NUMBER: LSSQWM2B10FL409050D010 2LBDLC\*MB

### Luminous Intensity Polar Plot





TEST NUMBER: P225454

CATALOG NUMBER: LSSQWM2B10FL409050D010 2LBDLC\*MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95				95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90				90
3	105	100	95	92	103	98	94	91	96	92	90	93	91	88	91	89	87	86				86
4	101	94	90	86	99	93	89	86	91	87	85	89	86	84	88	85	83	81				81
5	97	90	85	81	95	89	84	81	87	83	80	85	82	79	84	81	79	77				77
6	93	85	80	77	92	85	80	76	83	79	76	82	78	75	81	77	75	74				74
7	89	81	76	73	88	81	76	73	80	75	72	79	75	72	78	74	72	70				70
8	86	78	73	69	85	77	73	69	76	72	69	75	72	69	75	71	68	67				67
9	83	75	70	66	82	74	69	66	73	69	66	72	69	66	72	68	65	64				64
10	80	72	67	63	79	71	66	63	70	66	63	70	66	63	69	65	63	62				62

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	715815
5°	690165
10°	607013
15°	475758
20°	329558
25°	203010
30°	112980
35°	60243
40°	29884
45°	15229
50°	8376
55°	5470
60°	2711
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225454

CATALOG NUMBER: LSSQWM2B10FL409050D010 2LBDLC\*MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	161.9	19.7
10°-20°	324.1	39.4
20°-30°	221.4	26.9
30°-40°	84.4	10.3
40°-50°	23.4	2.8
50°-60°	7.3	0.9
60°-70°	0.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	707.3	85.9
0°-40°	791.7	96.2
0°-60°	822.5	99.9
0°-90°	823.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	823.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1848	
5°	1775	162
15°	1186	324
25°	475	221
35°	127	84
45°	28	23
55°	8	7
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225454

CATALOG NUMBER: LSSQWM2B10FL409050D010 2LBDLC\*MB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1848.0
2.5°	1828.3
5°	1775.0
7.5°	1675.4
10°	1543.3
12.5°	1375.3
15°	1186.4
17.5°	992.9
20°	799.5
22.5°	628.0
25°	475.0
27.5°	348.7
30°	252.6
32.5°	179.6
35°	127.4
37.5°	89.2
40°	59.1
42.5°	39.4
45°	27.8
47.5°	19.7
50°	13.9
52.5°	10.4
55°	8.1
57.5°	5.8
60°	3.5
62.5°	1.2
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)