

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224732

Luminaire Tested: **LSSQWM2B15FL409024D010 2LBD*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224732
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B15FL409024D010 2LBD*MW
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 985.9 lumens
Efficiency: N/A
Efficacy: 68.9 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224732

CATALOG NUMBER: LSSQWM2B15FL409024D010 2LBD*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224732

CATALOG NUMBER: LSSQWM2B15FL409024D010 2LBD*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91	91	91	91
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86	86	86	86
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82	82	82	82
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79	79	79	79
6	94	86	82	78	93	86	81	78	84	80	77	83	79	77	82	79	76	75	75	75	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72	72	72	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66	66	66	66
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64	64	64	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	892561
5°	876296
10°	778973
15°	612623
20°	407671
25°	234038
30°	118213
35°	55609
40°	22400
45°	11065
50°	6086
55°	4254
60°	3951
65°	2291
70°	2831
75°	1946
80°	2900
85°	0



TEST NUMBER: P224732

CATALOG NUMBER: LSSQWM2B15FL409024D010 2LBD*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	206.4	20.9
10°-20°	413.8	42.0
20°-30°	257.5	26.1
30°-40°	79.1	8.0
40°-50°	17.4	1.8
50°-60°	6.2	0.6
60°-70°	3.1	0.3
70°-80°	1.8	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	877.7	89.0
0°-40°	956.8	97.0
0°-60°	980.4	99.4
0°-90°	985.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	985.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2304	
5°	2254	206
15°	1528	414
25°	548	257
35°	118	79
45°	20	17
55°	6	6
65°	2	3
75°	1	2
85°	0	1
90°	0	



TEST NUMBER: P224732

CATALOG NUMBER: LSSQWM2B15FL409024D010 2LBD*MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2304.3
2.5°	2294.1
5°	2253.7
7.5°	2151.2
10°	1980.5
12.5°	1775.6
15°	1527.7
17.5°	1257.1
20°	989.0
22.5°	750.0
25°	547.6
27.5°	385.7
30°	264.3
32.5°	178.3
35°	117.6
37.5°	70.8
40°	44.3
42.5°	30.4
45°	20.2
47.5°	13.9
50°	10.1
52.5°	8.9
55°	6.3
57.5°	5.1
60°	5.1
62.5°	3.8
65°	2.5
67.5°	2.5
70°	2.5
72.5°	2.5
75°	1.3
77.5°	1.3
80°	1.3
82.5°	1.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)