

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225355

Luminaire Tested: **LSR2B15FL408027D010 2LBDC\*MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P225355  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR2B15FL408027D010 2LBDC\*MW  
Description: 1500 Lumen, 2inch Portfolio LED Cylinder  
FLOOD OPTIC  
CAST ROUND TRIM WITH MATTE WHITE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1179.9 lumens  
Efficiency: N/A  
Efficacy: 82.5 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P225355

CATALOG NUMBER: LSR2B15FL408027D010 2LBDC\*MW

### Luminous Intensity Polar Plot





TEST NUMBER: P225355

CATALOG NUMBER: LSR2B15FL408027D010 2LBDC\*MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95																			
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91																			
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86																			
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82																			
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79																			
6	94	87	82	78	93	86	81	78	84	80	77	83	80	77	82	79	76	75																			
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72																			
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69																			
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66																			
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1068184
5°	1048701
10°	932250
15°	733207
20°	487886
25°	280111
30°	141471
35°	66579
40°	26799
45°	13257
50°	7292
55°	5132
60°	4726
65°	2750
70°	3398
75°	2245
80°	3346
85°	0



TEST NUMBER: P225355

CATALOG NUMBER: LSR2B15FL408027D010 2LBDC\*MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	247.0	20.9
10°-20°	495.3	42.0
20°-30°	308.1	26.1
30°-40°	94.7	8.0
40°-50°	20.8	1.8
50°-60°	7.4	0.6
60°-70°	3.7	0.3
70°-80°	2.2	0.2
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1050.4	89.0
0°-40°	1145.1	97.1
0°-60°	1173.4	99.4
0°-90°	1179.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1179.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2758	
5°	2697	247
15°	1828	495
25°	655	308
35°	141	95
45°	24	21
55°	8	7
65°	3	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P225355

CATALOG NUMBER: LSR2B15FL408027D010 2LBDC\*MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2757.7
2.5°	2745.6
5°	2697.1
7.5°	2574.5
10°	2370.2
12.5°	2125.0
15°	1828.4
17.5°	1504.5
20°	1183.6
22.5°	897.5
25°	655.4
27.5°	461.6
30°	316.3
32.5°	213.4
35°	140.8
37.5°	84.8
40°	53.0
42.5°	36.3
45°	24.2
47.5°	16.6
50°	12.1
52.5°	10.6
55°	7.6
57.5°	6.1
60°	6.1
62.5°	4.5
65°	3.0
67.5°	3.0
70°	3.0
72.5°	3.0
75°	1.5
77.5°	1.5
80°	1.5
82.5°	1.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)