

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSR2B15WFL558027D010 2LBD*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14810)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B15WFL558027D010 2LBD*MW
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1287.6 lumens
Efficiency: N/A
Efficacy: 90.0 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#
CATALOG NUMBER: LSR2B15WFL558027D010 2LBD*MW

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSR2B15WFL558027D010 2LBD*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100																	
	1	113	110	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93	93	93	93	93	93	93	93	93	93	93																	
	2	108	102	98	95	105	101	97	94	98	94	92	95	92	90	92	90	88	86	86	86	86	86	86	86	86	86	86	86																	
	3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	87	84	81	80	80	80	80	80	80	80	80	80	80	80																	
	4	97	89	83	79	95	88	82	78	85	81	77	83	80	76	82	78	76	74	74	74	74	74	74	74	74	74	74	74																	
	5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69	69	69	69	69	69	69	69	69	69	69																	
	6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64	64	64	64	64	64	64	64	64	64	64																	
	7	82	73	67	62	81	72	66	62	71	66	62	70	65	62	69	64	61	60	60	60	60	60	60	60	60	60	60	60																	
	8	78	69	62	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56	56	56	56	56	56	56	56	56	56	56																	
	9	74	65	59	55	73	64	58	54	63	58	54	62	57	54	61	57	54	53	53	53	53	53	53	53	53	53	53	53																	
	10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	49	49	49	49	49	49	49	49	49	49	49																	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	603989
5°	600152
10°	557926
15°	489794
20°	422222
25°	361058
30°	286520
35°	199737
40°	126361
45°	77129
50°	45617
55°	24987
60°	5423
65°	4858
70°	3964
75°	5238
80°	4015
85°	8000



TEST NUMBER: P#

CATALOG NUMBER: LSR2B15WFL558027D010 2LBD*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.2	11.1
10°-20°	340.2	26.4
20°-30°	383.8	29.8
30°-40°	265.5	20.6
40°-50°	113.2	8.8
50°-60°	32.7	2.5
60°-70°	4.8	0.4
70°-80°	3.0	0.2
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	867.2	67.3
0°-40°	1132.7	88.0
0°-60°	1278.6	99.3
0°-90°	1287.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1287.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1559	
5°	1544	143
15°	1221	340
25°	845	384
35°	422	266
45°	141	113
55°	37	33
65°	5	5
75°	4	3
85°	2	1
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSR2B15WFL558027D010 2LBD*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1559.3
2.5°	1557.6
5°	1543.5
7.5°	1496.0
10°	1418.5
12.5°	1323.5
15°	1221.4
17.5°	1115.8
20°	1024.3
22.5°	938.1
25°	844.8
27.5°	746.2
30°	640.6
32.5°	526.2
35°	422.4
37.5°	327.4
40°	249.9
42.5°	188.3
45°	140.8
47.5°	102.1
50°	75.7
52.5°	54.6
55°	37.0
57.5°	15.8
60°	7.0
62.5°	5.3
65°	5.3
67.5°	3.5
70°	3.5
72.5°	3.5
75°	3.5
77.5°	1.8
80°	1.8
82.5°	1.8
85°	1.8
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)