

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSR2B15WFL559027D010 2LBD*WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14805)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B15WFL559027D010 2LBD*WMH
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
SPUN ROUND TRIM WITH WHEAT METALLIC HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1000.3 lumens
Efficiency: N/A
Efficacy: 70.0 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.83
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#
CATALOG NUMBER: LSR2B15WFL559027D010 2LBD*WMH

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSR2B15WFL559027D010 2LBD*WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																											
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86																											
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80																											
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	78	76	74																											
5	92	83	77	73	90	82	77	72	80	75	72	79	74	71	77	73	70	69																											
6	87	78	72	67	85	77	71	67	75	70	67	74	70	66	73	69	66	64																											
7	82	73	67	63	81	72	67	62	71	66	62	70	65	62	69	65	61	60																											
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	58	56																											
9	75	65	59	55	73	64	59	55	63	58	54	62	58	54	62	57	54	53																											
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	50																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	476397
5°	470712
10°	435092
15°	381320
20°	329104
25°	280153
30°	221890
35°	154011
40°	100067
45°	60202
50°	34770
55°	19517
60°	8522
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSR2B15WFL559027D010 2LBD*WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.3	11.2
10°-20°	264.9	26.5
20°-30°	298.2	29.8
30°-40°	206.0	20.6
40°-50°	89.3	8.9
50°-60°	27.7	2.8
60°-70°	2.0	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	675.4	67.5
0°-40°	881.4	88.1
0°-60°	998.3	99.8
0°-90°	1000.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1000.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1230	
5°	1211	112
15°	951	265
25°	656	298
35°	326	206
45°	110	89
55°	29	28
65°	0	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSR2B15WFL559027D010 2LBD*WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1229.9
2.5°	1227.1
5°	1210.6
7.5°	1172.1
10°	1106.2
12.5°	1030.6
15°	950.9
17.5°	868.5
20°	798.4
22.5°	728.3
25°	655.5
27.5°	581.3
30°	496.1
32.5°	406.7
35°	325.7
37.5°	255.6
40°	197.9
42.5°	149.8
45°	109.9
47.5°	81.1
50°	57.7
52.5°	41.2
55°	28.9
57.5°	20.6
60°	11.0
62.5°	2.7
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)