

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQ2B15FL409027D010 2LBD\*LI**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P#  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29152)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSSQ2B15FL409027D010 2LBD\*LI  
Description: 1500 Lumen, 2inch Portfolio LED Cylinder  
FLOOD OPTIC  
SPUN ROUND TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1072.1 lumens  
Efficiency: N/A  
Efficacy: 75.0 lumens/watt  
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.58  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P#  
CATALOG NUMBER: LSSQ2B15FL409027D010 2LBD\*LI

### Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B15FL409027D010 2LBD\*LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1   | 114 | 112 | 110 | 108 | 112 | 110 | 108 | 106 | 106 | 105 | 103 | 102 | 101 | 100 | 99  | 98  | 97  | 96  |
| 2   | 110 | 106 | 103 | 100 | 108 | 104 | 101 | 99  | 101 | 99  | 97  | 98  | 96  | 95  | 96  | 94  | 93  | 91  |
| 3   | 106 | 101 | 96  | 93  | 104 | 99  | 95  | 92  | 97  | 94  | 91  | 94  | 92  | 90  | 92  | 90  | 88  | 87  |
| 4   | 102 | 96  | 91  | 88  | 100 | 95  | 90  | 87  | 93  | 89  | 86  | 91  | 88  | 85  | 89  | 86  | 84  | 83  |
| 5   | 98  | 91  | 86  | 83  | 97  | 90  | 86  | 83  | 89  | 85  | 82  | 87  | 84  | 81  | 86  | 83  | 81  | 79  |
| 6   | 94  | 87  | 82  | 79  | 93  | 86  | 82  | 79  | 85  | 81  | 78  | 84  | 80  | 78  | 83  | 79  | 77  | 76  |
| 7   | 91  | 83  | 79  | 75  | 90  | 83  | 78  | 75  | 82  | 78  | 75  | 81  | 77  | 74  | 80  | 76  | 74  | 73  |
| 8   | 88  | 80  | 75  | 72  | 87  | 80  | 75  | 72  | 79  | 74  | 71  | 78  | 74  | 71  | 77  | 73  | 71  | 70  |
| 9   | 85  | 77  | 72  | 69  | 84  | 76  | 72  | 69  | 76  | 71  | 69  | 75  | 71  | 68  | 74  | 71  | 68  | 67  |
| 10  | 82  | 74  | 69  | 66  | 81  | 74  | 69  | 66  | 73  | 69  | 66  | 72  | 68  | 66  | 72  | 68  | 66  | 65  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1028404 |
| 5°  | 988278  |
| 10° | 860312  |
| 15° | 671772  |
| 20° | 446789  |
| 25° | 255835  |
| 30° | 127203  |
| 35° | 58446   |
| 40° | 23462   |
| 45° | 10737   |
| 50° | 4941    |
| 55° | 2769    |
| 60° | 1627    |
| 65° | 0       |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B15FL409027D010 2LBD\*LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 231.3  | 21.6      |
| 10°-20°   | 454.3  | 42.4      |
| 20°-30°   | 281.1  | 26.2      |
| 30°-40°   | 84.1   | 7.8       |
| 40°-50°   | 16.9   | 1.6       |
| 50°-60°   | 4.1    | 0.4       |
| 60°-70°   | 0.3    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 966.8  | 90.2      |
| 0°-40°    | 1050.9 | 98.0      |
| 0°-60°    | 1071.9 | 100.0     |
| 0°-90°    | 1072.1 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1072.1 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2655 |      |
| 5°  | 2542 | 231  |
| 15° | 1675 | 454  |
| 25° | 599  | 281  |
| 35° | 124  | 84   |
| 45° | 20   | 17   |
| 55° | 4    | 4    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B15FL409027D010 2LBD\*LI

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 2655.0 |
| 1°    | 2640.6 |
| 2°    | 2627.2 |
| 3°    | 2600.4 |
| 4°    | 2575.7 |
| 5°    | 2541.7 |
| 6°    | 2495.4 |
| 7°    | 2436.6 |
| 8°    | 2361.4 |
| 9°    | 2275.9 |
| 10°   | 2187.3 |
| 11°   | 2095.6 |
| 12°   | 1997.7 |
| 13°   | 1895.7 |
| 14°   | 1786.5 |
| 15°   | 1675.2 |
| 17.5° | 1381.6 |
| 20°   | 1083.9 |
| 22.5° | 820.1  |
| 25°   | 598.6  |
| 27.5° | 420.4  |
| 30°   | 284.4  |
| 32.5° | 187.5  |
| 35°   | 123.6  |
| 37.5° | 77.3   |
| 40°   | 46.4   |
| 42.5° | 29.9   |
| 45°   | 19.6   |
| 47.5° | 12.4   |
| 50°   | 8.2    |
| 52.5° | 6.2    |
| 55°   | 4.1    |
| 57.5° | 3.1    |
| 60°   | 2.1    |
| 62.5° | 0.0    |
| 65°   | 0.0    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B15FL409027D010 2LBD\*LI

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







|       |  |     |
|-------|--|-----|
| 85°   |  | 0.0 |
| 87.5° |  | 0.0 |



(END OF REPORT)