

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224700

Luminaire Tested: **LSR2B15FL409727D010 2LBD*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224700
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B15FL409727D010 2LBD*MW
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 955.4 lumens
Efficiency: N/A
Efficacy: 66.8 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224700

CATALOG NUMBER: LSR2B15FL409727D010 2LBD*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224700

CATALOG NUMBER: LSR2B15FL409727D010 2LBD*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 114 | 112 | 110 | 108 | 112 | 110 | 108 | 106 | 106 | 104 | 103 | 102 | 101 | 100 | 99 | 98 | 97 | 95 | 95 | 95 | 95 |
| 2 | 110 | 106 | 102 | 99 | 108 | 104 | 101 | 98 | 101 | 98 | 96 | 98 | 96 | 94 | 95 | 94 | 92 | 91 | 91 | 91 | 91 |
| 3 | 105 | 100 | 96 | 93 | 104 | 99 | 95 | 92 | 96 | 93 | 90 | 94 | 91 | 89 | 92 | 90 | 88 | 86 | 86 | 86 | 86 |
| 4 | 101 | 95 | 90 | 87 | 100 | 94 | 90 | 86 | 92 | 88 | 85 | 90 | 87 | 85 | 88 | 86 | 84 | 82 | 82 | 82 | 82 |
| 5 | 98 | 91 | 86 | 82 | 96 | 90 | 85 | 82 | 88 | 84 | 81 | 86 | 83 | 80 | 85 | 82 | 80 | 79 | 79 | 79 | 79 |
| 6 | 94 | 86 | 82 | 78 | 93 | 86 | 81 | 78 | 84 | 80 | 77 | 83 | 79 | 77 | 82 | 79 | 76 | 75 | 75 | 75 | 75 |
| 7 | 90 | 83 | 78 | 74 | 89 | 82 | 77 | 74 | 81 | 77 | 74 | 80 | 76 | 73 | 79 | 76 | 73 | 72 | 72 | 72 | 72 |
| 8 | 87 | 79 | 74 | 71 | 86 | 79 | 74 | 71 | 78 | 74 | 71 | 77 | 73 | 70 | 76 | 73 | 70 | 69 | 69 | 69 | 69 |
| 9 | 84 | 76 | 71 | 68 | 83 | 76 | 71 | 68 | 75 | 71 | 68 | 74 | 70 | 67 | 73 | 70 | 67 | 66 | 66 | 66 | 66 |
| 10 | 81 | 73 | 68 | 65 | 80 | 73 | 68 | 65 | 72 | 68 | 65 | 71 | 68 | 65 | 71 | 67 | 65 | 64 | 64 | 64 | 64 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 864944 |
| 5° | 849195 |
| 10° | 754862 |
| 15° | 593695 |
| 20° | 395057 |
| 25° | 226815 |
| 30° | 114545 |
| 35° | 53906 |
| 40° | 21692 |
| 45° | 10737 |
| 50° | 5906 |
| 55° | 4119 |
| 60° | 3796 |
| 65° | 2291 |
| 70° | 2831 |
| 75° | 1796 |
| 80° | 2677 |
| 85° | 0 |



TEST NUMBER: P224700

CATALOG NUMBER: LSR2B15FL409727D010 2LBD*MW

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 200.0 | 20.9 |
| 10°-20° | 401.0 | 42.0 |
| 20°-30° | 249.5 | 26.1 |
| 30°-40° | 76.7 | 8.0 |
| 40°-50° | 16.9 | 1.8 |
| 50°-60° | 6.0 | 0.6 |
| 60°-70° | 3.1 | 0.3 |
| 70°-80° | 1.8 | 0.2 |
| 80°-90° | 0.5 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 850.5 | 89.0 |
| 0°-40° | 927.2 | 97.1 |
| 0°-60° | 950.1 | 99.4 |
| 0°-90° | 955.4 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 955.4 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 2233 | |
| 5° | 2184 | 200 |
| 15° | 1480 | 401 |
| 25° | 531 | 249 |
| 35° | 114 | 77 |
| 45° | 20 | 17 |
| 55° | 6 | 6 |
| 65° | 2 | 3 |
| 75° | 1 | 2 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P224700

CATALOG NUMBER: LSR2B15FL409727D010 2LBD*MW

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 2233.0 |
| 2.5° | 2223.2 |
| 5° | 2184.0 |
| 7.5° | 2084.7 |
| 10° | 1919.2 |
| 12.5° | 1720.7 |
| 15° | 1480.5 |
| 17.5° | 1218.2 |
| 20° | 958.4 |
| 22.5° | 726.8 |
| 25° | 530.7 |
| 27.5° | 373.8 |
| 30° | 256.1 |
| 32.5° | 172.8 |
| 35° | 114.0 |
| 37.5° | 68.6 |
| 40° | 42.9 |
| 42.5° | 29.4 |
| 45° | 19.6 |
| 47.5° | 13.5 |
| 50° | 9.8 |
| 52.5° | 8.6 |
| 55° | 6.1 |
| 57.5° | 4.9 |
| 60° | 4.9 |
| 62.5° | 3.7 |
| 65° | 2.5 |
| 67.5° | 2.5 |
| 70° | 2.5 |
| 72.5° | 2.5 |
| 75° | 1.2 |
| 77.5° | 1.2 |
| 80° | 1.2 |
| 82.5° | 1.2 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)