

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223006

Luminaire Tested: **LSR2B10NFL259024D010 2LBDLC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223006
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B10NFL259024D010 2LBDLC*MB
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
NARROW FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 676.4 lumens
Efficiency: N/A
Efficacy: 65.7 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223006

CATALOG NUMBER: LSR2B10NFL259024D010 2LBDLC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P223006

CATALOG NUMBER: LSR2B10NFL259024D010 2LBDLC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97																											
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95																											
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92																											
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90																											
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88																											
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86																											
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	86	85	84																											
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82																											
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80																											
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	79																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1554342
5°	1435155
10°	971425
15°	330513
20°	121394
25°	64365
30°	33098
35°	15415
40°	5056
45°	2575
50°	1205
55°	473
60°	542
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223006

CATALOG NUMBER: LSR2B10NFL259024D010 2LBDLC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	314.0	46.4
10°-20°	264.0	39.0
20°-30°	72.5	10.7
30°-40°	21.1	3.1
40°-50°	3.9	0.6
50°-60°	0.9	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	650.4	96.2
0°-40°	671.5	99.3
0°-60°	676.4	100.0
0°-90°	676.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	676.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4013	
5°	3691	314
15°	824	264
25°	151	72
35°	33	21
45°	5	4
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223006

CATALOG NUMBER: LSR2B10NFL259024D010 2LBDLC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	4012.8
1°	3989.5
2°	3948.2
3°	3888.9
4°	3807.6
5°	3691.0
6°	3531.8
7°	3332.6
8°	3089.4
9°	2802.2
10°	2469.8
11°	2105.4
12°	1726.3
13°	1364.5
14°	1056.0
15°	824.2
17.5°	465.0
20°	294.5
22.5°	209.9
25°	150.6
27.5°	106.6
30°	74.0
32.5°	52.0
35°	32.6
37.5°	13.3
40°	10.0
42.5°	7.3
45°	4.7
47.5°	2.7
50°	2.0
52.5°	1.3
55°	0.7
57.5°	0.7
60°	0.7
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223006

CATALOG NUMBER: LSR2B10NFL259024D010 2LBDLC*MB

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)