

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224864

Luminaire Tested: **LSSQWM2B10FL409024D010 2LBD*B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224864
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14834)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B10FL409024D010 2LBD*B
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 723.1 lumens
Efficiency: N/A
Efficacy: 70.2 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224864

CATALOG NUMBER: LSSQWM2B10FL409024D010 2LBD*B

Luminous Intensity Polar Plot





TEST NUMBER: P224864

CATALOG NUMBER: LSSQWM2B10FL409024D010 2LBD*B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95																																				
2	110	106	103	100	108	104	101	99	101	99	96	98	96	94	96	94	92	91																																				
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87																																				
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83																																				
5	98	91	86	83	96	90	86	82	88	85	82	87	84	81	85	83	80	79																																				
6	94	87	82	79	93	86	82	78	85	81	78	84	80	77	82	79	77	76																																				
7	91	83	78	75	90	83	78	75	81	77	74	80	77	74	79	76	74	72																																				
8	87	80	75	72	86	79	75	71	78	74	71	77	74	71	76	73	71	69																																				
9	84	77	72	69	83	76	72	68	75	71	68	74	71	68	74	70	68	67																																				
10	82	74	69	66	81	73	69	66	73	68	65	72	68	65	71	68	65	64																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	654266
5°	642884
10°	573502
15°	453302
20°	302270
25°	175358
30°	87754
35°	41281
40°	16130
45°	7176
50°	3375
55°	1891
60°	697
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224864

CATALOG NUMBER: LSSQWM2B10FL409024D010 2LBD*B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.6	21.0
10°-20°	306.0	42.3
20°-30°	192.5	26.6
30°-40°	58.8	8.1
40°-50°	11.5	1.6
50°-60°	2.6	0.4
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	650.0	89.9
0°-40°	708.8	98.0
0°-60°	723.0	100.0
0°-90°	723.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	723.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1689	
5°	1653	152
15°	1130	306
25°	410	192
35°	87	59
45°	13	12
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224864

CATALOG NUMBER: LSSQWM2B10FL409024D010 2LBD*B

CANDELA DISTRIBUTION (FULL):

	0°
0°	1689.1
2.5°	1685.3
5°	1653.4
7.5°	1578.3
10°	1458.1
12.5°	1307.9
15°	1130.4
17.5°	933.3
20°	733.3
22.5°	562.4
25°	410.3
27.5°	289.2
30°	196.2
32.5°	132.4
35°	87.3
37.5°	53.5
40°	31.9
42.5°	20.7
45°	13.1
47.5°	8.5
50°	5.6
52.5°	3.8
55°	2.8
57.5°	1.9
60°	0.9
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)