

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224947

Luminaire Tested: **LSR2B15FL408030D010 2LBD*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224947
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (156)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B15FL408030D010 2LBD*H
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1375.6 lumens
Efficiency: N/A
Efficacy: 96.2 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224947

CATALOG NUMBER: LSR2B15FL408030D010 2LBD*H

Luminous Intensity Polar Plot





TEST NUMBER: P224947

CATALOG NUMBER: LSR2B15FL408030D010 2LBD*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 114 | 112 | 110 | 108 | 112 | 110 | 108 | 106 | 106 | 104 | 103 | 102 | 101 | 100 | 99 | 98 | 97 | 95 | 95 | 95 | 95 |
| 2 | 110 | 106 | 103 | 100 | 108 | 104 | 101 | 99 | 101 | 99 | 97 | 98 | 96 | 94 | 96 | 94 | 93 | 91 | 91 | 91 | 91 |
| 3 | 106 | 100 | 96 | 93 | 104 | 99 | 95 | 92 | 97 | 94 | 91 | 94 | 92 | 90 | 92 | 90 | 88 | 87 | 87 | 87 | 87 |
| 4 | 102 | 96 | 91 | 88 | 100 | 94 | 90 | 87 | 92 | 89 | 86 | 91 | 88 | 85 | 89 | 86 | 84 | 83 | 83 | 83 | 83 |
| 5 | 98 | 91 | 86 | 83 | 96 | 90 | 86 | 82 | 89 | 85 | 82 | 87 | 84 | 81 | 86 | 83 | 80 | 79 | 79 | 79 | 79 |
| 6 | 94 | 87 | 82 | 79 | 93 | 86 | 82 | 78 | 85 | 81 | 78 | 84 | 80 | 77 | 82 | 79 | 77 | 76 | 76 | 76 | 76 |
| 7 | 91 | 83 | 78 | 75 | 90 | 83 | 78 | 75 | 82 | 77 | 74 | 80 | 77 | 74 | 79 | 76 | 74 | 73 | 73 | 73 | 73 |
| 8 | 88 | 80 | 75 | 72 | 87 | 79 | 75 | 72 | 78 | 74 | 71 | 77 | 74 | 71 | 77 | 73 | 71 | 70 | 70 | 70 | 70 |
| 9 | 85 | 77 | 72 | 69 | 84 | 76 | 72 | 69 | 75 | 71 | 68 | 75 | 71 | 68 | 74 | 70 | 68 | 67 | 67 | 67 | 67 |
| 10 | 82 | 74 | 69 | 66 | 81 | 73 | 69 | 66 | 73 | 69 | 66 | 72 | 68 | 66 | 71 | 68 | 65 | 64 | 64 | 64 | 64 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 1275918 |
| 5° | 1249219 |
| 10° | 1100199 |
| 15° | 863174 |
| 20° | 573212 |
| 25° | 329047 |
| 30° | 165042 |
| 35° | 76225 |
| 40° | 30996 |
| 45° | 13859 |
| 50° | 7231 |
| 55° | 4525 |
| 60° | 2092 |
| 65° | 0 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P224947

CATALOG NUMBER: LSR2B15FL408030D010 2LBD*H

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 293.4 | 21.3 |
| 10°-20° | 582.6 | 42.4 |
| 20°-30° | 362.0 | 26.3 |
| 30°-40° | 109.2 | 7.9 |
| 40°-50° | 22.3 | 1.6 |
| 50°-60° | 5.8 | 0.4 |
| 60°-70° | 0.3 | 0.0 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1238.0 | 90.0 |
| 0°-40° | 1347.2 | 97.9 |
| 0°-60° | 1375.3 | 100.0 |
| 0°-90° | 1375.6 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1375.6 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 3294 | |
| 5° | 3213 | 293 |
| 15° | 2152 | 583 |
| 25° | 770 | 362 |
| 35° | 161 | 109 |
| 45° | 25 | 22 |
| 55° | 7 | 6 |
| 65° | 0 | 0 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P224947

CATALOG NUMBER: LSR2B15FL408030D010 2LBD*H

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 3294.0 |
| 1° | 3283.4 |
| 2° | 3268.7 |
| 3° | 3258.0 |
| 4° | 3242.1 |
| 5° | 3212.8 |
| 6° | 3166.1 |
| 7° | 3102.2 |
| 8° | 3010.3 |
| 9° | 2906.4 |
| 10° | 2797.2 |
| 11° | 2681.3 |
| 12° | 2560.1 |
| 13° | 2433.5 |
| 14° | 2295.0 |
| 15° | 2152.5 |
| 17.5° | 1770.2 |
| 20° | 1390.6 |
| 22.5° | 1054.9 |
| 25° | 769.9 |
| 27.5° | 543.5 |
| 30° | 369.0 |
| 32.5° | 242.4 |
| 35° | 161.2 |
| 37.5° | 99.9 |
| 40° | 61.3 |
| 42.5° | 40.0 |
| 45° | 25.3 |
| 47.5° | 16.0 |
| 50° | 12.0 |
| 52.5° | 8.0 |
| 55° | 6.7 |
| 57.5° | 4.0 |
| 60° | 2.7 |
| 62.5° | 0.0 |
| 65° | 0.0 |
| 67.5° | 0.0 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |



TEST NUMBER: P224947

CATALOG NUMBER: LSR2B15FL408030D010 2LBD*H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







| | | |
|-------|--|-----|
| 85° | | 0.0 |
| 87.5° | | 0.0 |



(END OF REPORT)