

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224728

Luminaire Tested: **LSSQWM2B15FL408030D010 2LBD\*MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P224728  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSSQWM2B15FL408030D010 2LBD\*MW  
Description: 1500 Lumen, 2inch Portfolio LED Cylinder  
FLOOD OPTIC  
SPUN ROUND TRIM WITH MATTE WHITE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1373.8 lumens  
Efficiency: N/A  
Efficacy: 96.1 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P224728

CATALOG NUMBER: LSSQWM2B15FL408030D010 2LBD\*MW

### Luminous Intensity Polar Plot





TEST NUMBER: P224728

CATALOG NUMBER: LSSQWM2B15FL408030D010 2LBD\*MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91			91
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86			86
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82			82
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79			79
6	94	86	82	78	93	86	81	78	84	80	77	83	79	77	82	79	76	75			75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72			72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69			69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66			66
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64			64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1243729
5°	1221068
10°	1085449
15°	853670
20°	568060
25°	326141
30°	164729
35°	77502
40°	31198
45°	15448
50°	8497
55°	5943
60°	5423
65°	3208
70°	3964
75°	2694
80°	4015
85°	0



TEST NUMBER: P224728

CATALOG NUMBER: LSSQWM2B15FL408030D010 2LBD\*MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	287.6	20.9
10°-20°	576.7	42.0
20°-30°	358.8	26.1
30°-40°	110.3	8.0
40°-50°	24.2	1.8
50°-60°	8.6	0.6
60°-70°	4.3	0.3
70°-80°	2.6	0.2
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1223.0	89.0
0°-40°	1333.3	97.1
0°-60°	1366.2	99.4
0°-90°	1373.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1373.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3211	
5°	3140	288
15°	2129	577
25°	763	359
35°	164	110
45°	28	24
55°	9	9
65°	4	4
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P224728

CATALOG NUMBER: LSSQWM2B15FL408030D010 2LBD\*MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3210.9
2.5°	3196.8
5°	3140.4
7.5°	2997.6
10°	2759.7
12.5°	2474.2
15°	2128.8
17.5°	1751.7
20°	1378.1
22.5°	1045.0
25°	763.1
27.5°	537.5
30°	368.3
32.5°	248.5
35°	163.9
37.5°	98.7
40°	61.7
42.5°	42.3
45°	28.2
47.5°	19.4
50°	14.1
52.5°	12.3
55°	8.8
57.5°	7.0
60°	7.0
62.5°	5.3
65°	3.5
67.5°	3.5
70°	3.5
72.5°	3.5
75°	1.8
77.5°	1.8
80°	1.8
82.5°	1.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)