

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224114

Luminaire Tested: **LSR2B10SP158035D010 2LBDC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224114
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (150)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B10SP158035D010 2LBDC*MW
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
SPOT OPTIC
CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 604.4 lumens
Efficiency: N/A
Efficacy: 58.7 lumens/watt
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.23
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224114

CATALOG NUMBER: LSR2B10SP158035D010 2LBDC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224114

CATALOG NUMBER: LSR2B10SP158035D010 2LBDC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98																			
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	96																			
3	110	106	103	101	108	105	102	100	102	100	98	100	98	97	98	97	96	94																			
4	108	103	100	97	106	102	99	97	100	98	96	98	96	95	97	95	94	93																			
5	105	101	97	95	104	100	97	94	98	96	94	97	95	93	95	94	92	91																			
6	103	98	95	93	102	98	95	92	96	94	92	95	93	91	94	92	91	90																			
7	101	96	93	91	100	96	93	90	95	92	90	94	91	90	93	91	89	88																			
8	100	94	91	89	99	94	91	89	93	90	89	92	90	88	92	89	88	87																			
9	98	93	90	88	97	92	89	87	92	89	87	91	89	87	90	88	87	86																			
10	96	91	88	86	96	91	88	86	90	88	86	90	87	86	89	87	86	85																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2904281
5°	2099503
10°	611221
15°	214460
20°	91839
25°	41329
30°	15967
35°	7944
40°	5309
45°	3451
50°	1928
55°	1418
60°	852
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224114

CATALOG NUMBER: LSR2B10SP158035D010 2LBDC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	382.1	63.2
10°-20°	155.4	25.7
20°-30°	47.7	7.9
30°-40°	11.8	1.9
40°-50°	4.9	0.8
50°-60°	2.1	0.4
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	585.2	96.8
0°-40°	597.0	98.8
0°-60°	604.0	99.9
0°-90°	604.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	604.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7498	
5°	5400	382
15°	535	155
25°	97	48
35°	17	12
45°	6	5
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224114

CATALOG NUMBER: LSR2B10SP158035D010 2LBDC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	7497.9
1°	7383.3
2°	7103.8
3°	6658.3
4°	6076.3
5°	5399.6
6°	4636.8
7°	3808.8
8°	2969.3
9°	2184.4
10°	1554.0
11°	1113.8
12°	837.4
13°	681.9
14°	596.8
15°	534.8
17.5°	329.9
20°	222.8
22.5°	149.2
25°	96.7
27.5°	58.8
30°	35.7
32.5°	23.1
35°	16.8
37.5°	13.7
40°	10.5
42.5°	8.4
45°	6.3
47.5°	4.2
50°	3.2
52.5°	3.2
55°	2.1
57.5°	2.1
60°	1.1
62.5°	1.1
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224114

CATALOG NUMBER: LSR2B10SP158035D010 2LBDC*MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)