

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225362

Luminaire Tested: **LSSQWM2B15FL409030D010 2LBDC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225362
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B15FL409030D010 2LBDC*MW
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 969.8 lumens
Efficiency: N/A
Efficacy: 67.8 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225362

CATALOG NUMBER: LSSQWM2B15FL409030D010 2LBDC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P225362

CATALOG NUMBER: LSSQWM2B15FL409030D010 2LBDC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91			
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86			
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82			
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79			
6	94	87	82	78	93	86	81	78	84	80	77	83	80	77	82	79	76	75			
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72			
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69			
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66			
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	877958
5°	861987
10°	766269
15°	602638
20°	400993
25°	230234
30°	116290
35°	54710
40°	21996
45°	10901
50°	6026
55°	4187
60°	3873
65°	2291
70°	2831
75°	1796
80°	2677
85°	0



TEST NUMBER: P225362

CATALOG NUMBER: LSSQWM2B15FL409030D010 2LBDC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.0	20.9
10°-20°	407.1	42.0
20°-30°	253.2	26.1
30°-40°	77.9	8.0
40°-50°	17.1	1.8
50°-60°	6.1	0.6
60°-70°	3.1	0.3
70°-80°	1.8	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	863.4	89.0
0°-40°	941.2	97.1
0°-60°	964.4	99.4
0°-90°	969.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	969.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2267	
5°	2217	203
15°	1503	407
25°	539	253
35°	116	78
45°	20	17
55°	6	6
65°	2	3
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P225362

CATALOG NUMBER: LSSQWM2B15FL409030D010 2LBDC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2266.6
2.5°	2256.7
5°	2216.9
7.5°	2116.1
10°	1948.2
12.5°	1746.6
15°	1502.8
17.5°	1236.6
20°	972.8
22.5°	737.7
25°	538.7
27.5°	379.4
30°	260.0
32.5°	175.4
35°	115.7
37.5°	69.7
40°	43.5
42.5°	29.9
45°	19.9
47.5°	13.7
50°	10.0
52.5°	8.7
55°	6.2
57.5°	5.0
60°	5.0
62.5°	3.7
65°	2.5
67.5°	2.5
70°	2.5
72.5°	2.5
75°	1.2
77.5°	1.2
80°	1.2
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)