

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSR2B10WFL559035D010 2LBD*B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14809)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B10WFL559035D010 2LBD*B
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
SPUN ROUND TRIM WITH BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 807.2 lumens
Efficiency: N/A
Efficacy: 78.4 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#
CATALOG NUMBER: LSR2B10WFL559035D010 2LBD*B

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSR2B10WFL559035D010 2LBD*B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100																	
	1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93	93	93	93	93	93	93	93	93	93	93																	
	2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87	87	87	87	87	87	87	87	87	87	87																	
	3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	80	80	80	80	80	80	80	80	80	80																	
	4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75	75	75	75	75	75	75	75	75	75	75																	
	5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69	69	69	69	69	69	69	69	69	69	69																	
	6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65	65	65	65	65	65	65	65	65	65	65																	
	7	83	73	67	63	81	73	67	63	71	66	63	70	66	62	69	65	62	60	60	60	60	60	60	60	60	60	60	60																	
	8	79	69	63	59	78	69	63	59	67	62	59	66	62	58	65	61	58	57	57	57	57	57	57	57	57	57	57	57																	
	9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53	53	53	53	53	53	53	53	53	53	53																	
	10	71	62	56	52	70	61	56	52	60	55	52	60	55	52	59	55	51	50	50	50	50	50	50	50	50	50	50	50																	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	384286
5°	381788
10°	355563
15°	311825
20°	269376
25°	229123
30°	181725
35°	125403
40°	78779
45°	47000
50°	27177
55°	13709
60°	852
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSR2B10WFL559035D010 2LBD*B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.2	11.3
10°-20°	216.7	26.9
20°-30°	243.9	30.2
30°-40°	167.6	20.8
40°-50°	69.6	8.6
50°-60°	18.0	2.2
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	551.9	68.4
0°-40°	719.5	89.1
0°-60°	807.1	100.0
0°-90°	807.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	807.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	992	
5°	982	91
15°	778	217
25°	536	244
35°	265	168
45°	86	70
55°	20	18
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSR2B10WFL559035D010 2LBD*B

CANDELA DISTRIBUTION (FULL):

	0°
0°	992.1
2.5°	990.9
5°	981.9
7.5°	952.6
10°	904.0
12.5°	843.1
15°	777.6
17.5°	711.0
20°	653.5
22.5°	597.0
25°	536.1
27.5°	474.0
30°	406.3
32.5°	334.1
35°	265.2
37.5°	206.5
40°	155.8
42.5°	117.4
45°	85.8
47.5°	62.1
50°	45.1
52.5°	31.6
55°	20.3
57.5°	6.8
60°	1.1
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)