

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSR2B10WFL559035D010 2LBD*LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29153)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B10WFL559035D010 2LBD*LI
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
SPUN ROUND TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 815.2 lumens
Efficiency: N/A
Efficacy: 79.1 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.8
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#
CATALOG NUMBER: LSR2B10WFL559035D010 2LBD*LI

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSR2B10WFL559035D010 2LBD*LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	82	73	67	63	72	66	63	70	66	62	69	65	62	61																			
8	79	69	63	59	78	69	63	59	68	62	59	66	62	58	66	61	58	57																			
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53																			
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	419767
5°	402396
10°	363390
15°	318402
20°	271643
25°	227884
30°	177745
35°	122519
40°	78678
45°	47603
50°	27961
55°	15667
60°	4493
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSR2B10WFL559035D010 2LBD*LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.2	11.7
10°-20°	220.7	27.1
20°-30°	242.5	29.8
30°-40°	164.1	20.1
40°-50°	70.3	8.6
50°-60°	21.5	2.6
60°-70°	0.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	558.4	68.5
0°-40°	722.5	88.6
0°-60°	814.3	99.9
0°-90°	815.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	815.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1084	
5°	1035	95
15°	794	221
25°	533	243
35°	259	164
45°	87	70
55°	23	21
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSR2B10WFL559035D010 2LBD*LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1083.7
1°	1077.9
2°	1068.8
3°	1059.7
4°	1048.1
5°	1034.9
6°	1018.3
7°	998.5
8°	974.4
9°	949.6
10°	923.9
11°	896.6
12°	871.8
13°	846.1
14°	820.5
15°	794.0
17.5°	725.2
20°	659.0
22.5°	596.1
25°	533.2
27.5°	468.6
30°	397.4
32.5°	325.4
35°	259.1
37.5°	202.8
40°	155.6
42.5°	117.6
45°	86.9
47.5°	63.7
50°	46.4
52.5°	33.1
55°	23.2
57.5°	14.9
60°	5.8
62.5°	0.8
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P#

CATALOG NUMBER: LSR2B10WFL559035D010 2LBD*LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)