

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224781

Luminaire Tested: **LSSQWM2B15FL409730D010 2LBDL\*MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P224781  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSSQWM2B15FL409730D010 2LBDL\*MW  
Description: 1500 Lumen, 2inch Portfolio LED Cylinder  
FLOOD OPTIC  
LENSED SPUN ROUND TRIM WITH MATTE WHITE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 955.4 lumens  
Efficiency: N/A  
Efficacy: 66.8 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P224781

CATALOG NUMBER: LSSQWM2B15FL409730D010 2LBDL\*MW

### Luminous Intensity Polar Plot





TEST NUMBER: P224781

CATALOG NUMBER: LSSQWM2B15FL409730D010 2LBDL\*MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91	91	91	91
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86	86	86	86
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82	82	82	82
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79	79	79	79
6	94	86	82	78	93	86	81	78	84	80	77	83	79	77	82	79	76	75	75	75	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72	72	72	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66	66	66	66
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64	64	64	64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	864944
5°	849195
10°	754862
15°	593695
20°	395057
25°	226815
30°	114545
35°	53906
40°	21692
45°	10737
50°	5906
55°	4119
60°	3796
65°	2291
70°	2831
75°	1796
80°	2677
85°	0



TEST NUMBER: P224781

CATALOG NUMBER: LSSQWM2B15FL409730D010 2LBDL\*MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	200.0	20.9
10°-20°	401.0	42.0
20°-30°	249.5	26.1
30°-40°	76.7	8.0
40°-50°	16.9	1.8
50°-60°	6.0	0.6
60°-70°	3.1	0.3
70°-80°	1.8	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	850.5	89.0
0°-40°	927.2	97.1
0°-60°	950.1	99.4
0°-90°	955.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	955.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2233	
5°	2184	200
15°	1480	401
25°	531	249
35°	114	77
45°	20	17
55°	6	6
65°	2	3
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P224781

CATALOG NUMBER: LSSQWM2B15FL409730D010 2LBDL\*MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2233.0
2.5°	2223.2
5°	2184.0
7.5°	2084.7
10°	1919.2
12.5°	1720.7
15°	1480.5
17.5°	1218.2
20°	958.4
22.5°	726.8
25°	530.7
27.5°	373.8
30°	256.1
32.5°	172.8
35°	114.0
37.5°	68.6
40°	42.9
42.5°	29.4
45°	19.6
47.5°	13.5
50°	9.8
52.5°	8.6
55°	6.1
57.5°	4.9
60°	4.9
62.5°	3.7
65°	2.5
67.5°	2.5
70°	2.5
72.5°	2.5
75°	1.2
77.5°	1.2
80°	1.2
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)