

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224975

Luminaire Tested: **LSRWM2B15FL408040D010 2LBDL*LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224975
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (152)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSRWM2B15FL408040D010 2LBDL*LI
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1370.2 lumens
Efficiency: N/A
Efficacy: 95.8 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.58
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224975

CATALOG NUMBER: LSRWM2B15FL408040D010 2LBDL*LI

Luminous Intensity Polar Plot





TEST NUMBER: P224975

CATALOG NUMBER: LSRWM2B15FL408040D010 2LBDL*LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	105	103	102	101	100	99	98	97	96	96	96	96
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	91	91
3	106	101	96	93	104	99	95	92	97	94	91	94	92	90	92	90	88	87	87	87	87
4	102	96	91	88	100	95	90	87	93	89	86	91	88	85	89	86	84	83	83	83	83
5	98	91	86	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79	79	79	79
6	94	87	82	79	93	86	82	79	85	81	78	84	80	78	83	79	77	76	76	76	76
7	91	83	79	75	90	83	78	75	82	78	75	81	77	74	80	76	74	73	73	73	73
8	88	80	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	70	70	70	70
9	85	77	72	69	84	76	72	69	76	71	69	75	71	68	74	71	68	67	67	67	67
10	82	74	69	66	81	74	69	66	73	69	66	72	68	66	72	68	66	65	65	65	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1314381
5°	1263061
10°	1099530
15°	858603
20°	570986
25°	326953
30°	162537
35°	74712
40°	29985
45°	13695
50°	6327
55°	3579
60°	2014
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224975

CATALOG NUMBER: LSRWM2B15FL408040D010 2LBDL*LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	295.7	21.6
10°-20°	580.6	42.4
20°-30°	359.3	26.2
30°-40°	107.5	7.8
40°-50°	21.6	1.6
50°-60°	5.3	0.4
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1235.5	90.2
0°-40°	1343.1	98.0
0°-60°	1369.9	100.0
0°-90°	1370.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1370.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3393	
5°	3248	296
15°	2141	581
25°	765	359
35°	158	108
45°	25	22
55°	5	5
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224975

CATALOG NUMBER: LSRWM2B15FL408040D010 2LBDL*LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3393.3
1°	3374.9
2°	3357.7
3°	3323.5
4°	3291.9
5°	3248.4
6°	3189.2
7°	3114.1
8°	3018.0
9°	2908.7
10°	2795.5
11°	2678.3
12°	2553.2
13°	2422.8
14°	2283.3
15°	2141.1
17.5°	1765.8
20°	1385.2
22.5°	1048.1
25°	765.0
27.5°	537.2
30°	363.4
32.5°	239.7
35°	158.0
37.5°	98.8
40°	59.3
42.5°	38.2
45°	25.0
47.5°	15.8
50°	10.5
52.5°	7.9
55°	5.3
57.5°	4.0
60°	2.6
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224975

CATALOG NUMBER: LSRWM2B15FL408040D010 2LBDL*LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)