

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225458

Luminaire Tested: **LSRWM2B15FL408040D010 2LBDLC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225458
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14833)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSRWM2B15FL408040D010 2LBDLC*MB
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1327.1 lumens
Efficiency: N/A
Efficacy: 92.8 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225458

CATALOG NUMBER: LSRWM2B15FL408040D010 2LBDLC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P225458

CATALOG NUMBER: LSRWM2B15FL408040D010 2LBDLC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90			90
3	105	100	95	92	103	98	94	91	96	92	90	93	91	88	91	89	87	86			86
4	101	94	90	86	99	93	89	86	91	87	85	89	86	84	88	85	83	81			81
5	97	90	85	81	95	89	84	81	87	83	80	85	82	79	84	81	79	77			77
6	93	85	80	77	92	85	80	76	83	79	76	82	78	75	81	77	75	74			74
7	89	81	76	73	88	81	76	73	80	75	72	79	75	72	78	74	72	70			70
8	86	78	73	69	85	77	73	69	76	72	69	75	72	69	75	71	68	67			67
9	83	75	70	66	82	74	69	66	73	69	66	72	69	66	72	68	65	64			64
10	80	72	67	63	79	71	66	63	70	66	63	70	66	63	69	65	63	62			62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1153981
5°	1112663
10°	978584
15°	767012
20°	531250
25°	327295
30°	182128
35°	97173
40°	48188
45°	24541
50°	13498
55°	8847
60°	4338
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225458

CATALOG NUMBER: LSRWM2B15FL408040D010 2LBDLC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	261.0	19.7
10°-20°	522.4	39.4
20°-30°	356.9	26.9
30°-40°	136.1	10.3
40°-50°	37.8	2.8
50°-60°	11.8	0.9
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1140.3	85.9
0°-40°	1276.4	96.2
0°-60°	1326.0	99.9
0°-90°	1327.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1327.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2979	
5°	2862	261
15°	1913	522
25°	766	357
35°	206	136
45°	45	38
55°	13	12
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225458

CATALOG NUMBER: LSRWM2B15FL408040D010 2LBDLC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2979.2
2.5°	2947.5
5°	2861.6
7.5°	2700.9
10°	2488.0
12.5°	2217.1
15°	1912.7
17.5°	1600.8
20°	1288.8
22.5°	1012.4
25°	765.8
27.5°	562.2
30°	407.2
32.5°	289.5
35°	205.5
37.5°	143.8
40°	95.3
42.5°	63.5
45°	44.8
47.5°	31.8
50°	22.4
52.5°	16.8
55°	13.1
57.5°	9.3
60°	5.6
62.5°	1.9
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)