

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224766

Luminaire Tested: **LSSQWM2B10FL409035D010 2LBDL\*MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P224766  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSSQWM2B10FL409035D010 2LBDL\*MW  
Description: 1000 Lumen, 2inch Portfolio LED Cylinder  
FLOOD OPTIC  
LENSED SPUN ROUND TRIM WITH MATTE WHITE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 801.9 lumens  
Efficiency: N/A  
Efficacy: 77.9 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P224766

CATALOG NUMBER: LSSQWM2B10FL409035D010 2LBDL\*MW

### Luminous Intensity Polar Plot





TEST NUMBER: P224766

CATALOG NUMBER: LSSQWM2B10FL409035D010 2LBDL\*MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95				95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91				91
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86				86
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82				82
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79				79
6	94	86	82	78	93	86	81	78	84	80	77	83	79	77	82	79	76	75				75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72				72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69				69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66				66
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64				64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	725964
5°	712756
10°	633601
15°	498295
20°	331578
25°	190359
30°	96163
35°	45253
40°	18203
45°	9039
50°	4941
55°	3444
60°	3176
65°	1925
70°	2378
75°	1497
80°	2231
85°	0



TEST NUMBER: P224766

CATALOG NUMBER: LSSQWM2B10FL409035D010 2LBDL\*MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	167.9	20.9
10°-20°	336.6	42.0
20°-30°	209.4	26.1
30°-40°	64.4	8.0
40°-50°	14.2	1.8
50°-60°	5.0	0.6
60°-70°	2.6	0.3
70°-80°	1.5	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	713.9	89.0
0°-40°	778.3	97.1
0°-60°	797.4	99.4
0°-90°	801.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	801.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1874	
5°	1833	168
15°	1243	337
25°	445	209
35°	96	64
45°	16	14
55°	5	5
65°	2	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P224766

CATALOG NUMBER: LSSQWM2B10FL409035D010 2LBDL\*MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1874.2
2.5°	1866.0
5°	1833.1
7.5°	1749.7
10°	1610.9
12.5°	1444.2
15°	1242.6
17.5°	1022.5
20°	804.4
22.5°	610.0
25°	445.4
27.5°	313.7
30°	215.0
32.5°	145.0
35°	95.7
37.5°	57.6
40°	36.0
42.5°	24.7
45°	16.5
47.5°	11.3
50°	8.2
52.5°	7.2
55°	5.1
57.5°	4.1
60°	4.1
62.5°	3.1
65°	2.1
67.5°	2.1
70°	2.1
72.5°	2.1
75°	1.0
77.5°	1.0
80°	1.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)