

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSRWM2B15WFL558040D010 2LBD*LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29153)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSRWM2B15WFL558040D010 2LBD*LI
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
SPUN ROUND TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1379.2 lumens
Efficiency: N/A
Efficacy: 96.4 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.8
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#
CATALOG NUMBER: LSRWM2B15WFL558040D010 2LBD*LI

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSRWM2B15WFL558040D010 2LBD*LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | |
| 1 | 113 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 104 | 103 | 101 | 101 | 99 | 98 | 97 | 96 | 95 | 93 | | | | | | | | | | | | | | | | | | | |
| 2 | 108 | 103 | 99 | 95 | 106 | 101 | 97 | 94 | 98 | 95 | 92 | 95 | 92 | 90 | 92 | 90 | 88 | 87 | | | | | | | | | | | | | | | | | | | |
| 3 | 102 | 96 | 91 | 87 | 100 | 94 | 90 | 86 | 92 | 88 | 85 | 89 | 86 | 83 | 87 | 84 | 82 | 80 | | | | | | | | | | | | | | | | | | | |
| 4 | 97 | 89 | 84 | 79 | 95 | 88 | 83 | 79 | 86 | 81 | 78 | 84 | 80 | 77 | 82 | 79 | 76 | 75 | | | | | | | | | | | | | | | | | | | |
| 5 | 92 | 83 | 78 | 73 | 90 | 83 | 77 | 73 | 81 | 76 | 72 | 79 | 75 | 72 | 77 | 74 | 71 | 69 | | | | | | | | | | | | | | | | | | | |
| 6 | 87 | 78 | 72 | 68 | 86 | 77 | 72 | 68 | 76 | 71 | 67 | 74 | 70 | 67 | 73 | 69 | 66 | 65 | | | | | | | | | | | | | | | | | | | |
| 7 | 83 | 73 | 67 | 63 | 82 | 73 | 67 | 63 | 72 | 66 | 63 | 70 | 66 | 62 | 69 | 65 | 62 | 61 | | | | | | | | | | | | | | | | | | | |
| 8 | 79 | 69 | 63 | 59 | 78 | 69 | 63 | 59 | 68 | 62 | 59 | 66 | 62 | 58 | 66 | 61 | 58 | 57 | | | | | | | | | | | | | | | | | | | |
| 9 | 75 | 65 | 59 | 55 | 74 | 65 | 59 | 55 | 64 | 59 | 55 | 63 | 58 | 55 | 62 | 58 | 55 | 53 | | | | | | | | | | | | | | | | | | | |
| 10 | 72 | 62 | 56 | 52 | 71 | 61 | 56 | 52 | 61 | 55 | 52 | 60 | 55 | 52 | 59 | 55 | 52 | 50 | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 710199 |
| 5° | 680795 |
| 10° | 614840 |
| 15° | 538677 |
| 20° | 459609 |
| 25° | 385505 |
| 30° | 300699 |
| 35° | 207303 |
| 40° | 133136 |
| 45° | 80580 |
| 50° | 47244 |
| 55° | 26472 |
| 60° | 7592 |
| 65° | 0 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P#

CATALOG NUMBER: LSRWM2B15WFL558040D010 2LBD*LI

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 161.1 | 11.7 |
| 10°-20° | 373.3 | 27.1 |
| 20°-30° | 410.3 | 29.7 |
| 30°-40° | 277.6 | 20.1 |
| 40°-50° | 119.0 | 8.6 |
| 50°-60° | 36.3 | 2.6 |
| 60°-70° | 1.5 | 0.1 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 944.7 | 68.5 |
| 0°-40° | 1222.3 | 88.6 |
| 0°-60° | 1377.7 | 99.9 |
| 0°-90° | 1379.2 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1379.2 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1834 | |
| 5° | 1751 | 161 |
| 15° | 1343 | 373 |
| 25° | 902 | 410 |
| 35° | 438 | 278 |
| 45° | 147 | 119 |
| 55° | 39 | 36 |
| 65° | 0 | 2 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P#

CATALOG NUMBER: LSRWM2B15WFL558040D010 2LBD*LI

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1833.5 |
| 1° | 1823.7 |
| 2° | 1808.3 |
| 3° | 1792.9 |
| 4° | 1773.3 |
| 5° | 1750.9 |
| 6° | 1722.9 |
| 7° | 1689.2 |
| 8° | 1648.6 |
| 9° | 1606.6 |
| 10° | 1563.2 |
| 11° | 1517.0 |
| 12° | 1474.9 |
| 13° | 1431.5 |
| 14° | 1388.1 |
| 15° | 1343.3 |
| 17.5° | 1227.0 |
| 20° | 1115.0 |
| 22.5° | 1008.5 |
| 25° | 902.0 |
| 27.5° | 792.8 |
| 30° | 672.3 |
| 32.5° | 550.5 |
| 35° | 438.4 |
| 37.5° | 343.2 |
| 40° | 263.3 |
| 42.5° | 198.9 |
| 45° | 147.1 |
| 47.5° | 107.9 |
| 50° | 78.4 |
| 52.5° | 56.0 |
| 55° | 39.2 |
| 57.5° | 25.2 |
| 60° | 9.8 |
| 62.5° | 1.4 |
| 65° | 0.0 |
| 67.5° | 0.0 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |



TEST NUMBER: P#

CATALOG NUMBER: LSRWM2B15WFL558040D010 2LBD*LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







| | | |
|-------|--|-----|
| 85° | | 0.0 |
| 87.5° | | 0.0 |



(END OF REPORT)