

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224634

Luminaire Tested: **LSSQWM2B15FL408040D010 2LBDLC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224634
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14836)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B15FL408040D010 2LBDLC*MMS
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1343.3 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224634

CATALOG NUMBER: LSSQWM2B15FL408040D010 2LBDLC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P224634

CATALOG NUMBER: LSSQWM2B15FL408040D010 2LBDLC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95				95
2	110	106	102	100	108	104	101	99	101	99	96	98	96	94	95	94	92	91				91
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87				87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83				83
5	98	91	86	83	96	90	86	82	88	85	82	87	83	81	85	82	80	79				79
6	94	87	82	78	93	86	82	78	85	81	78	83	80	77	82	79	77	76				76
7	91	83	78	75	89	82	78	75	81	77	74	80	77	74	79	76	73	72				72
8	87	80	75	71	86	79	75	71	78	74	71	77	73	71	76	73	70	69				69
9	84	76	72	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67				67
10	81	74	69	66	81	73	69	66	72	68	65	72	68	65	71	68	65	64				64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1222774
5°	1199255
10°	1065311
15°	840718
20°	560722
25°	322721
30°	163477
35°	76651
40°	31401
45°	14188
50°	7292
55°	4660
60°	2634
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224634

CATALOG NUMBER: LSSQWM2B15FL408040D010 2LBDLC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	282.3	21.0
10°-20°	566.5	42.2
20°-30°	354.8	26.4
30°-40°	109.8	8.2
40°-50°	22.7	1.7
50°-60°	6.3	0.5
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1203.6	89.6
0°-40°	1313.5	97.8
0°-60°	1342.5	99.9
0°-90°	1343.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1343.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3157	
5°	3084	282
15°	2096	567
25°	755	355
35°	162	110
45°	26	23
55°	7	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224634

CATALOG NUMBER: LSSQWM2B15FL408040D010 2LBDLC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	3156.8
2.5°	3141.2
5°	3084.3
7.5°	2939.5
10°	2708.5
12.5°	2424.0
15°	2096.5
17.5°	1718.9
20°	1360.3
22.5°	1034.4
25°	755.1
27.5°	531.0
30°	365.5
32.5°	244.8
35°	162.1
37.5°	101.7
40°	62.1
42.5°	39.7
45°	25.9
47.5°	17.2
50°	12.1
52.5°	8.6
55°	6.9
57.5°	5.2
60°	3.4
62.5°	1.7
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)