

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225490

Luminaire Tested: **LSR2B15FL409040D010 2LBDL\*H**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P225490  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14832)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR2B15FL409040D010 2LBDL\*H  
Description: 1500 Lumen, 2inch Portfolio LED Cylinder  
FLOOD OPTIC  
LENSED SPUN ROUND TRIM WITH HAZE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1104.4 lumens  
Efficiency: N/A  
Efficacy: 77.2 lumens/watt  
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.6  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P225490

CATALOG NUMBER: LSR2B15FL409040D010 2LBDL\*H

### Luminous Intensity Polar Plot





TEST NUMBER: P225490

CATALOG NUMBER: LSR2B15FL409040D010 2LBDL\*H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	105	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	86	86	86
4	101	95	90	86	99	94	89	86	91	88	85	90	86	84	88	85	83	82	82	82	82
5	97	90	85	81	96	89	84	81	87	83	80	86	82	80	84	81	79	78	78	78	78
6	93	86	81	77	92	85	80	77	84	79	76	82	79	76	81	78	75	74	74	74	74
7	90	82	77	73	88	81	76	73	80	76	73	79	75	72	78	75	72	71	71	71	71
8	86	78	73	70	85	78	73	70	77	72	69	76	72	69	75	71	69	68	68	68	68
9	83	75	70	67	82	75	70	67	74	69	66	73	69	66	72	69	66	65	65	65	65
10	80	72	67	64	79	72	67	64	71	67	64	70	66	64	70	66	63	62	62	62	62

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	970805
5°	938508
10°	828060
15°	652363
20°	448314
25°	270708
30°	146749
35°	75422
40°	36861
45°	17474
50°	9160
55°	6145
60°	3564
65°	1375
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225490

CATALOG NUMBER: LSR2B15FL409040D010 2LBDL\*H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	220.5	20.0
10°-20°	442.9	40.1
20°-30°	295.9	26.8
30°-40°	107.2	9.7
40°-50°	27.7	2.5
50°-60°	8.3	0.7
60°-70°	2.0	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	959.3	86.9
0°-40°	1066.4	96.6
0°-60°	1102.4	99.8
0°-90°	1104.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1104.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2506	
5°	2414	221
15°	1627	443
25°	633	296
35°	160	107
45°	32	28
55°	9	8
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225490

CATALOG NUMBER: LSR2B15FL409040D010 2LBDL\*H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2506.3
2.5°	2483.5
5°	2413.7
7.5°	2286.1
10°	2105.3
12.5°	1883.5
15°	1626.8
17.5°	1353.4
20°	1087.6
22.5°	843.0
25°	633.4
27.5°	461.8
30°	328.1
32.5°	230.9
35°	159.5
37.5°	110.9
40°	72.9
42.5°	47.1
45°	31.9
47.5°	22.8
50°	15.2
52.5°	12.2
55°	9.1
57.5°	6.1
60°	4.6
62.5°	3.0
65°	1.5
67.5°	1.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)