

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223994

Luminaire Tested: **LSSQ2B10SP158050D010 2LBDC\*MMS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P223994  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA ( 150)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSSQ2B10SP158050D010 2LBDC\*MMS  
Description: 1000 Lumen, 2inch Portfolio LED Cylinder  
SPOT OPTIC  
CAST ROUND TRIM WITH MATTE METALLIC SILVER  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 620.4 lumens  
Efficiency: N/A  
Efficacy: 60.2 lumens/watt  
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.23  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P223994

CATALOG NUMBER: LSSQ2B10SP158050D010 2LBDC\*MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P223994

CATALOG NUMBER: LSSQ2B10SP158050D010 2LBDC\*MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	96
3	110	106	103	101	108	105	102	100	102	100	98	100	98	97	98	97	96	94
4	108	103	100	97	106	102	99	97	100	98	96	98	96	95	97	95	94	93
5	105	101	97	95	104	100	97	94	98	96	94	97	95	93	95	94	92	91
6	103	98	95	93	102	98	95	92	96	94	92	95	93	91	94	92	91	90
7	101	96	93	91	100	96	93	90	95	92	90	94	91	90	93	91	89	88
8	100	94	91	89	99	94	91	89	93	90	89	92	90	88	92	90	88	87
9	98	93	90	88	97	92	89	87	92	89	87	91	89	87	90	88	87	86
10	96	91	88	86	96	91	88	86	90	88	86	90	87	86	89	87	86	85

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2981131
5°	2155066
10°	627387
15°	220155
20°	94230
25°	42397
30°	16415
35°	8181
40°	5461
45°	3561
50°	1928
55°	1486
60°	852
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223994

CATALOG NUMBER: LSSQ2B10SP158050D010 2LBDC\*MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	392.2	63.2
10°-20°	159.6	25.7
20°-30°	49.0	7.9
30°-40°	12.1	1.9
40°-50°	5.0	0.8
50°-60°	2.2	0.3
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	600.7	96.8
0°-40°	612.8	98.8
0°-60°	620.0	99.9
0°-90°	620.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	620.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7696	
5°	5542	392
15°	549	160
25°	99	49
35°	17	12
45°	6	5
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223994

CATALOG NUMBER: LSSQ2B10SP158050D010 2LBDC\*MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7696.3
1°	7578.8
2°	7291.9
3°	6834.6
4°	6237.1
5°	5542.5
6°	4759.5
7°	3909.7
8°	3047.9
9°	2242.3
10°	1595.1
11°	1143.2
12°	859.6
13°	700.0
14°	612.6
15°	549.0
17.5°	338.7
20°	228.6
22.5°	153.2
25°	99.2
27.5°	60.4
30°	36.7
32.5°	23.7
35°	17.3
37.5°	14.0
40°	10.8
42.5°	8.6
45°	6.5
47.5°	4.3
50°	3.2
52.5°	3.2
55°	2.2
57.5°	2.2
60°	1.1
62.5°	1.1
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223994

CATALOG NUMBER: LSSQ2B10SP158050D010 2LBDC\*MMS

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)