

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSR2B15WFL559040D010 2LBDC**MW***

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14810)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B15WFL559040D010 2LBDC*MW
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1111.6 lumens
Efficiency: N/A
Efficacy: 77.7 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#
CATALOG NUMBER: LSR2B15WFL559040D010 2LBDC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSR2B15WFL559040D010 2LBDC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	110	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93																											
2	108	102	98	95	105	101	97	94	98	94	92	95	92	90	92	90	88	86																											
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	87	84	81	80																											
4	97	89	83	79	95	88	82	78	85	81	77	83	80	76	82	78	76	74																											
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69																											
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64																											
7	82	73	67	62	81	72	66	62	71	66	62	70	65	62	69	64	61	60																											
8	78	69	62	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56																											
9	74	65	59	55	73	64	58	54	63	58	54	62	57	54	61	57	54	53																											
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	49																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	521445
5°	518110
10°	481661
15°	422865
20°	364513
25°	311695
30°	247384
35°	172453
40°	109118
45°	66611
50°	39350
55°	21543
60°	4726
65°	4216
70°	3398
75°	4490
80°	3346
85°	6666



TEST NUMBER: P#

CATALOG NUMBER: LSR2B15WFL559040D010 2LBDC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.7	11.1
10°-20°	293.7	26.4
20°-30°	331.3	29.8
30°-40°	229.2	20.6
40°-50°	97.7	8.8
50°-60°	28.3	2.5
60°-70°	4.1	0.4
70°-80°	2.6	0.2
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	748.7	67.4
0°-40°	977.9	88.0
0°-60°	1103.9	99.3
0°-90°	1111.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1111.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1346	
5°	1332	124
15°	1054	294
25°	729	331
35°	365	229
45°	122	98
55°	32	28
65°	5	4
75°	3	3
85°	2	1
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSR2B15WFL559040D010 2LBDC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1346.2
2.5°	1344.7
5°	1332.5
7.5°	1291.5
10°	1224.6
12.5°	1142.6
15°	1054.5
17.5°	963.3
20°	884.3
22.5°	809.8
25°	729.3
27.5°	644.2
30°	553.1
32.5°	454.3
35°	364.7
37.5°	282.6
40°	215.8
42.5°	162.6
45°	121.6
47.5°	88.1
50°	65.3
52.5°	47.1
55°	31.9
57.5°	13.7
60°	6.1
62.5°	4.6
65°	4.6
67.5°	3.0
70°	3.0
72.5°	3.0
75°	3.0
77.5°	1.5
80°	1.5
82.5°	1.5
85°	1.5
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)