

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P222569

Luminaire Tested: **LSSQ2B15NFL259040D010 2LBD\*MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P222569  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSSQ2B15NFL259040D010 2LBD\*MW  
Description: 1500 Lumen, 2inch Portfolio LED Cylinder  
NARROW FLOOD OPTIC  
SPUN ROUND TRIM WITH MATTE WHITE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1167.2 lumens  
Efficiency: N/A  
Efficacy: 81.6 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P222569

CATALOG NUMBER: LSSQ2B15NFL259040D010 2LBD\*MW

### Luminous Intensity Polar Plot





TEST NUMBER: P222569

CATALOG NUMBER: LSSQ2B15NFL259040D010 2LBD\*MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																			
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97									97																			
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95									95																			
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92									92																			
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90									90																			
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88									88																			
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86									86																			
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	87	85	84									84																			
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82									82																			
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80									80																			
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	79									79																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2682448
5°	2476741
10°	1676454
15°	570357
20°	209483
25°	111078
30°	57071
35°	26622
40°	8697
45°	4382
50°	2049
55°	743
60°	852
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P222569

CATALOG NUMBER: LSSQ2B15NFL259040D010 2LBD\*MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	541.8	46.4
10°-20°	455.6	39.0
20°-30°	125.0	10.7
30°-40°	36.4	3.1
40°-50°	6.7	0.6
50°-60°	1.5	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1122.4	96.2
0°-40°	1158.9	99.3
0°-60°	1167.1	100.0
0°-90°	1167.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1167.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6925	
5°	6370	542
15°	1422	456
25°	260	125
35°	56	36
45°	8	7
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P222569

CATALOG NUMBER: LSSQ2B15NFL259040D010 2LBD\*MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6925.2
1°	6884.9
2°	6813.6
3°	6711.3
4°	6571.0
5°	6369.8
6°	6095.0
7°	5751.2
8°	5331.5
9°	4836.0
10°	4262.3
11°	3633.3
12°	2979.1
13°	2354.8
14°	1822.4
15°	1422.3
17.5°	802.5
20°	508.2
22.5°	362.2
25°	259.9
27.5°	184.0
30°	127.6
32.5°	89.7
35°	56.3
37.5°	23.0
40°	17.2
42.5°	12.6
45°	8.0
47.5°	4.6
50°	3.4
52.5°	2.3
55°	1.1
57.5°	1.1
60°	1.1
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P222569

CATALOG NUMBER: LSSQ2B15NFL259040D010 2LBD\*MW

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)