

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225304

Luminaire Tested: **LSR2B15FL408050D010 2LBDC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225304
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B15FL408050D010 2LBDC*MMS
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
CAST ROUND TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1447.4 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225304

CATALOG NUMBER: LSR2B15FL408050D010 2LBDC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P225304

CATALOG NUMBER: LSR2B15FL408050D010 2LBDC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91			91
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86			86
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82			82
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79			79
6	94	86	82	78	93	86	81	78	84	80	77	83	79	77	82	79	76	75			75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72			72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69			69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66			66
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1310353
5°	1286468
10°	1143621
15°	899425
20°	598480
25°	343578
30°	173540
35°	81663
40°	32867
45°	16269
50°	8979
55°	6280
60°	5733
65°	3391
70°	4190
75°	2844
80°	4238
85°	0



TEST NUMBER: P225304

CATALOG NUMBER: LSR2B15FL408050D010 2LBDC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	303.0	20.9
10°-20°	607.5	42.0
20°-30°	378.0	26.1
30°-40°	116.2	8.0
40°-50°	25.5	1.8
50°-60°	9.1	0.6
60°-70°	4.6	0.3
70°-80°	2.7	0.2
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1288.5	89.0
0°-40°	1404.7	97.1
0°-60°	1439.4	99.4
0°-90°	1447.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1447.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3383	
5°	3309	303
15°	2243	608
25°	804	378
35°	173	116
45°	30	26
55°	9	9
65°	4	5
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P225304

CATALOG NUMBER: LSR2B15FL408050D010 2LBDC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	3382.9
2.5°	3368.0
5°	3308.6
7.5°	3158.2
10°	2907.6
12.5°	2606.8
15°	2242.9
17.5°	1845.5
20°	1451.9
22.5°	1101.0
25°	803.9
27.5°	566.3
30°	388.0
32.5°	261.8
35°	172.7
37.5°	104.0
40°	65.0
42.5°	44.6
45°	29.7
47.5°	20.4
50°	14.9
52.5°	13.0
55°	9.3
57.5°	7.4
60°	7.4
62.5°	5.6
65°	3.7
67.5°	3.7
70°	3.7
72.5°	3.7
75°	1.9
77.5°	1.9
80°	1.9
82.5°	1.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)