

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223694

Luminaire Tested: **LSSQ2B10SP159050D010 2LBDC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223694
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (150)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B10SP159050D010 2LBDC*MW
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
SPOT OPTIC
CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 525.7 lumens
Efficiency: N/A
Efficacy: 51.0 lumens/watt
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.23
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223694

CATALOG NUMBER: LSSQ2B10SP159050D010 2LBDC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P223694

CATALOG NUMBER: LSSQ2B10SP159050D010 2LBDC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98			98																
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	96			96																
3	110	106	103	101	108	105	102	100	102	100	98	100	99	97	98	97	96	94			94																
4	108	103	100	97	106	102	99	97	100	98	96	98	96	95	97	95	94	93			93																
5	105	101	97	95	104	100	97	94	98	96	94	97	95	93	96	94	92	91			91																
6	103	98	95	93	102	98	95	92	96	94	92	95	93	91	94	92	91	90			90																
7	101	96	93	91	100	96	93	90	95	92	90	94	91	90	93	91	89	88			88																
8	100	94	91	89	99	94	91	89	93	90	89	92	90	88	92	90	88	87			87																
9	98	93	90	88	97	92	89	87	92	89	87	91	89	87	90	88	87	86			86																
10	96	91	88	86	96	91	88	86	90	88	86	90	87	86	89	87	86	85			85																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2526116
5°	1826119
10°	531653
15°	186550
20°	79844
25°	35943
30°	13910
35°	6904
40°	4601
45°	3013
50°	1627
55°	1216
60°	697
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223694

CATALOG NUMBER: LSSQ2B10SP159050D010 2LBDC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	332.3	63.2
10°-20°	135.2	25.7
20°-30°	41.5	7.9
30°-40°	10.2	1.9
40°-50°	4.3	0.8
50°-60°	1.8	0.3
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	509.1	96.8
0°-40°	519.3	98.8
0°-60°	525.4	99.9
0°-90°	525.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	525.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6522	
5°	4696	332
15°	465	135
25°	84	42
35°	15	10
45°	6	4
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223694

CATALOG NUMBER: LSSQ2B10SP159050D010 2LBDC*MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	6521.6
1°	6421.9
2°	6178.8
3°	5791.4
4°	5285.1
5°	4696.5
6°	4033.0
7°	3312.9
8°	2582.7
9°	1900.0
10°	1351.7
11°	968.7
12°	728.4
13°	593.1
14°	519.1
15°	465.2
17.5°	287.0
20°	193.7
22.5°	129.8
25°	84.1
27.5°	51.2
30°	31.1
32.5°	20.1
35°	14.6
37.5°	11.9
40°	9.1
42.5°	7.3
45°	5.5
47.5°	3.7
50°	2.7
52.5°	2.7
55°	1.8
57.5°	1.8
60°	0.9
62.5°	0.9
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223694

CATALOG NUMBER: LSSQ2B10SP159050D010 2LBDC*MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)